

System Accessories

Also suitable for AEG,
ELU, Holz-Her, Metabo,
Flex, Makita, Skil

Type	Length of teeth mm	Tooth spacing mm	Version	Metal	Wood	Miscellaneous	Quantity	Part no.
 T119B	67	1.9-2.3	HCS milled wavy set		Plywood boards, chipboard, wood core plywood and softwood, fibre wood boards 2-15 mm	ECONOMIC	5 3	2 608 630 037 2 608 630 878
 T119BO	56	2	HCS milled wavy set		Curve cutting saw blade, particularly narrow, for tight curves in wood, 2-15 mm	ECONOMIC	5 3	2 608 630 310 2 608 637 788
 T111C	74	3	HCS milled side set		Hard and soft wood 4-50 mm Coarse cut	ECONOMIC	5 3	2 608 630 033 2 608 630 808
 T144D	74	4-5.2	HCS side set ground		Chipboard, wood core plywood, softwood and fibre boards 5-50 mm	Quick cut	5 3	2 608 630 040 2 608 630 560
 T244D	74	4-5.2	HCS side set ground		Softwood 5-50 mm Particularly suitable for cutting curves	Quick cut	5 3	2 608 630 058 2 608 630 879
 T344D	126	4	HCS side set ground		Thick construction timber, chipboard, wood core plywood, softwood and fibre boards 5-100 mm	Quick cut	5 3	2 608 633 A34 2 608 637 944
 T101AO	56	1.4	HCS ground pointed teeth		Curve cutting saw blade, particularly narrow, for tight curves, plywood 1.5-15 mm	Clean cut	5 3	2 608 630 031 2 608 630 559
 T101B	74	2.7	HCS ground		Hardwood, softwood, plywood and fibre wood boards 3-30 mm	Clean cut	5 3	2 608 630 030 2 608 630 557
 T101BR	74	2.5	HCS, ground, reversed teething		Hardwood, softwood, plywood and especially for laminated fibre wood boards (splinter-free cuts) 3-30 mm	Clean cut	5 3	2 608 630 014 2 608 633 779
 T101D	74	4-5.2	HCS ground		Hardwood, softwood, plywood and fibre wood boards 10-45 mm	Clean cut	5 3	2 608 630 032 2 608 630 558
 T301CD	91	3	HCS ground		Hardwood, softwood, plywood and fibre wood boards 10-65 mm	Clean cut	5 3	2 608 637 590 2 608 637 591
 T144DP	74	4	HCS ground		Special blade for parallel cuts at accurate angles in hardwood, softwood, plywood and fibre wood boards 5-50 mm	Cut at accurate angles	5 3	2 608 633 A35 2 608 633 A31
 T234X	91	2-3	HCS ground		Ideal for wooden materials 2-65 mm Fast, clean, splinter-free cut	Universal for thick and thin wooden materials	5 3	2 608 633 528 2 608 633 523
 T118G	67	0.7	HSS milled wavy set	Soft steel <input type="checkbox"/> , non-ferrous metal <input type="checkbox"/> ■, 0.5-1.5 mm For metal plate thicknesses below 1 mm, saw an additional thin wooden board		ECONOMIC	5 3	2 608 631 012 2 608 631 674
 T118A	67	1.1-1.5	HSS milled wavy set	Soft steel <input type="checkbox"/> , non-ferrous metal <input type="checkbox"/> ■, 1-3 mm		ECONOMIC	5 3	2 608 631 013 2 608 631 507
 T318A	106	1.2	HSS milled wavy set	Soft steel <input type="checkbox"/> , non-ferrous metal <input type="checkbox"/> ■, Aluminium and aluminium alloys <input type="checkbox"/> ■ 1-3 mm, pipes and profiles up to 65 mm		ECONOMIC	5 3	2 608 631 319 2 608 638 698
 T118B	67	1.9-2.3	HSS milled wavy set	Soft steel <input type="checkbox"/> 2.5-6 mm, non-ferrous metal		ECONOMIC	5 3	2 608 631 014 2 608 631 673
 T318B	106	2	HSS milled wavy set	Soft steel <input type="checkbox"/> 2.5-6 mm, non-ferrous metal, aluminium and aluminium alloys, pipes and profiles up to 65 mm		ECONOMIC	5 3	2 608 631 404 2 608 638 699
 T123X	74	1.2-2.6	HSS milled	Soft steel, 1.5-10 mm Pipes and profiles up to 30 mm Aluminium profiles up to 30 mm		Universal for thick and thin metals	5 3	2 608 638 473 2 608 638 472
 T127D	74	3	HSS milled side set	Soft steel <input type="checkbox"/> 3-15 mm, non-ferrous metal, aluminium and aluminium alloys <input type="checkbox"/> ■ 3-15 mm, pipes and profiles up to 30 mm Lead and tin <input type="checkbox"/> up to 20 mm		Special for aluminium	5 3	2 608 631 017 2 608 631 508
 T227D	74	3	HSS milled side set	Soft steel <input type="checkbox"/> 3-15 mm, non-ferrous metal, aluminium and aluminium alloys <input type="checkbox"/> ■ 3-15 mm, pipes and profiles up to 30 mm Lead and tin <input type="checkbox"/> up to 20 mm. Particularly suitable for cutting curves		Special for aluminium	5 3	2 608 631 030 2 608 631 671
 T118AHM	59	1.1	Tungsten carbide	Stainless steel plate 1.5-3 mm <input type="checkbox"/> Soft steel 1.5-3 mm <input type="checkbox"/> , work without pendulum action and with reduced stroke rate		Special for Inox	3	2 608 630 663
 T118EHM	59	1.4	Tungsten carbide	Stainless steel plate 2-5 mm <input type="checkbox"/> Soft steel 2-5 mm <input type="checkbox"/> , work without pendulum action and with reduced stroke rate		Special for Inox	3	2 608 630 665
 T301CHM	91	3.3	Tungsten carbide		Glass fibre reinforced plastics, Corian up to 65 mm Clean cut		3	2 608 633 164
 T141HM	74	4.3	Tungsten carbide tipped		Glass fibre reinforced plastics, fibre cement up to 20 mm, plasterboard. Coarse, fast cut		3	2 608 633 175
 T341HM	106	4.3	Tungsten carbide tipped		Glass fibre reinforced plastics, fibre cement up to 80 mm, plasterboard. Coarse, fast cut		3	2 608 633 176
 T130Riff	59	Grit 30	Tungsten carbide coated, coarse	Riff, grit 30		Glass fibre reinforced plastics, 5-15 mm Soft ceramic wall tiles, cast iron	3 1	2 608 633 104 2 608 633 R06
 T150Riff	59	Grit 50	Tungsten carbide coated, fine	Riff, grit 50		Glass fibre reinforced plastics, 5-15 mm Soft ceramic wall tiles, cast iron	3 1	2 608 633 105 2 608 633 R07

Cooling with cutting oil or cutting oil emulsion, Cooling with turpentine or turpentine-petroleum mixture.

Saws

