

L6207

DMOS dual full bridge driver with PWM current controller

Datasheet - production data

- Thermal shutdown
- Undervoltage lockout
- Integrated fast freewheeling diodes

Applications

- Bipolar stepper motor
- Dual DC motor

Description

The L6207 device is a DMOS dual full bridge designed for motor control applications, realized in BCD technology, which combines isolated DMOS power transistors with CMOS and bipolar circuits on the same chip. The device also includes two independent constant off time PWM current controllers that perform the chopping regulation. Available in PowerSO36 and SO24 (20 + 2 + 2) packages, the L6207 device features a non-dissipative overcurrent protection on the high-side Power MOSFETs and thermal shutdown.

FowerSO36SO24
(20+2+2)Ordering numbers:L6207PD (PowerSO36)
(SO24)

Features

- Operating supply voltage from 8 to 52 V
- 5.6 A output peak current (2.8 A DC)
- R_{DS(ON)} 0.3 Ω typ. value at T_i = 25 °C
- Operating frequency up to 100 KHz
- Non-dissipative overcurrent protection
- Dual independent constant t_{OFF} PWM current controllers
- Slow decay synchronous rectification
- Cross conduction protection

October 2018

DocID7513 Rev 3

This is information on a product in full production.

1/32

Contents

1	Bloc	Block diagram						
2	Max	Maximum ratings						
3	Pin o	connections						
4	Elec	trical characteristics8						
5	Circ	uit description						
	5.1	Power stages and charge pump						
	5.2	Logic inputs						
6	PWN	A current control						
7	Slow	<i>i</i> decay mode						
	7.1	Non-dissipative overcurrent protection						
	7.2	Thermal protection						
8	App	lication information						
	8.1	Output current capability and IC power dissipation						
	8.2	Thermal management						
9	Pack	cage information						
	9.1	PowerSO36 package information						
	9.2	SO24 package information 30						
10	Revi	sion history						
11	Revi	sion history						



DocID7513 Rev 3

1 Block diagram




Figure 1. Block diagram



2 Maximum ratings

Symbol	Parameter	Test conditions	Value	Unit
Vs	Supply voltage	$V_{SA} = V_{SB} = V_S$	60	V
V _{OD}	Differential voltage between VS_A , $OUT1_A$, $OUT2_A$, $SENSE_A$ and VS_B , $OUT1_B$, $OUT2_B$, $SENSE_B$	$V_{SA} = V_{SB} = V_S = 60 V;$ $V_{SENSEA} = V_{SENSEB} = GND$	60	v
V _{BOOT}	Bootstrap peak voltage	$V_{SA} = V_{SB} = V_{S}$	V _S + 10	V
$V_{\rm IN}, V_{\rm EN}$	Input and enable voltage range	-	-0.3 to +7	V
V _{REFA} , V _{REFB}	Voltage range at pins V_{REFA} and V_{REFB}	-	-0.3 to +7	V
$V_{RCA,}V_{RCB}$	Voltage range at pins RC_{A} and RC_{B}	-	-0.3 to +7	V
V _{SENSEA,} V _{SENSEB}	Voltage range at pins $SENSE_A$ and $SENSE_B$	-	-1 to +4	V
I _{S(peak)}	Pulsed supply current (for each V _S pin), internally limited by the overcurrent protection	V _{SA} = V _{SB} = V _S ; t _{PULSE} < 1 ms	7.1	A
۱ _S	RMS supply current (for each V_S pin)	$V_{SA} = V_{SB} = V_{S}$	2.8	Α
T _{stg} , T _{OP}	Storage and operating temperature range	-	-40 to 150	°C

Table 1. Absolute maximum ratings

Table 2. Recommended operating conditions

Symbol	Parameter	Test conditions	Min.	Max.	Unit
V _S	Supply voltage	$V_{SA} = V_{SB} = V_{S}$	8	52	V
V _{OD}	Differential voltage between VS_A , $OUT1_A$, $OUT2_A$, $SENSE_A$ and VS_B , $OUT1_B$, $OUT2_B$, $SENSE_B$	V _{SA} = V _{SB} = V _S ; V _{SENSEA} = V _{SENSEB}	-	52	v
V _{REFA} , V _{REFB}	Voltage range at pins V_{REFA} and V_{REFB}	-	-0.1	5	V
V _{SENSEA,} V _{SENSEB}	Voltage range at pins $SENSE_A$ and $SENSE_B$	(pulsed t _W < t _{rr}) (DC)	-6 -1	6 1	V V
I _{OUT}	RMS output current	-	-	2.8	А
f _{sw}	Switching frequency	-	-	100	KHz



Symbol	Description	SO24	PowerSO36	Unit		
R _{th-j-pins}	Maximum thermal resistance junction pins	14	-	°C/W		
R _{th-j-case}	Maximum thermal resistance junction case	-	1	°C/W		
R _{th-j-amb1}	Maximum thermal resistance junction ambient ⁽¹⁾	51	-	°C/W		
R _{th-j-amb1}	Maximum thermal resistance junction ambient ⁽²⁾	-	35	°C/W		
R _{th-j-amb1}	Maximum thermal resistance junction ambient ⁽³⁾	-	15	°C/W		
R _{th-j-amb2}	Maximum thermal resistance junction ambient ⁽⁴⁾	77	62	°C/W		

Table 3. Thermal data

1. Mounted on a multilayer FR4 PCB with a dissipating copper surface on the bottom side of 6 cm² (with a thickness of 35 μ m).

2. Mounted on a multilayer FR4 PCB with a dissipating copper surface on the top side of 6 cm^2 (with a thickness of 35 μm).

3. Mounted on a multilayer FR4 PCB with a dissipating copper surface on the top side of 6 cm^2 (with a thickness of 35 μm), 16 via holes and a ground layer.

4. Mounted on a multilayer FR4 PCB without any heat sinking surface on the board.



3 Pin connections




Figure 2. Pin connections (top view)

1. The slug is internally connected to pins 1, 18, 19 and 36 (GND pins).

Table 4. Pin description

Pac	Package		Package			
SO24	PowerSO36	Name	Туре	Function		
Pin no.	Pin no.					
1	10	IN1 _A	Logic input	Bridge A logic input 1.		
2	11	IN2 _A	Logic input	Bridge A logic input 2.		
3	12	SENSEA	Power supply	Bridge A source pin. This pin must be connected to power ground through a sensing power resistor.		
4	13	RC _A	RC pin	RC network pin. A parallel RC network connected between this pin and ground sets the current controller OFF-time of the bridge A.		
5	15	OUT1 _A	Power output	Bridge A output 1.		



Table 4.	Pin	descri	ption	(continued)

Package				
SO24	PowerSO36	Name	Туре	Function
Pin no.	Pin no.			
6, 7, 18, 19	1, 18, 19, 36	GND	GND	Signal ground terminals. In SO package, these pins are also used for heat dissipation toward the PCB.
8	22	OUT1 _B	Power output	Bridge B output 1.
9	24	RC _B	RC pin	RC network pin. A parallel RC network connected between this pin and ground sets the current controller OFF-time of the bridge B.
10	25	SENSEB	Power supply	Bridge B source pin. This pin must be connected to power ground through a sensing power resistor.
11	26	IN1 _B	Logic input	Bridge B input 1
12	27	IN2 _B	Logic input	Bridge B input 2
13	28	VREF _B	Analog input	Bridge B current controller reference voltage. Do not leave this pin open or connect to GND.
14	29	ENB	Logic input ⁽¹⁾	Bridge B enable. LOW logic level switches OFF all Power MOSFETs of bridge B. This pin is also connected to the collector of the overcurrent and thermal protection transistor to implement overcurrent protection. If not used, it has to be connected to +5 V through a resistor.
15	30	VBOOT	Supply voltage	Bootstrap voltage needed for driving the upper Power MOSFETs of both bridge A and bridge B.
16	32	OUT2 _B	Power output	Bridge B output 2.
17	33	VS _B	Powersupply	Bridge B power supply voltage. It must be connected to the supply voltage together with pin VS _A .
20	4	VS _A	Power supply	Bridge A power supply voltage. It must be connected to the supply voltage together with pin VS _B .
21	5	OUT2 _A	Power output	Bridge A output 2.
22	7	VCP	Output	Charge pump oscillator output.
23	8	ENA	Logic input ⁽¹⁾	Bridge A enable. LOW logic level switches OFF all Power MOSFETs of bridge A. This pin is also connected to the collector of the overcurrent and thermal protection transistor to implement overcurrent protection. If not used, it has to be connected to +5 V through a resistor.
24	9	VREF _A	Analog input	Bridge A current controller reference voltage. Do not leave this pin open or connect to GND.

1. Also connected at the output drain of the overcurrent and thermal protection MOSFET. Therefore, it has to be driven putting in series a resistor with a value in the range of 2.2 K Ω - 180 K Ω , recommended 100 K Ω .



4 Electrical characteristics

Symbol	Parameter	8 V, unless otherwise specifie Test conditions	Min.	Тур.	Max.	Unit
V _{Sth(ON)}	Turn-on threshold	-	6.6	7	7.4	V
V _{Sth(OFF)}	Turn-off threshold	-	5.6	6	6.4	V
I _S	Quiescent supply current	All bridges OFF; T _j = -25 °C to 125 °C ⁽¹⁾	-	5	10	mA
T _{j(OFF)}	Thermal shutdown temperature	-	-	165	-	°C
Output DN	IOS transistors				1	
		T _j = 25 °C	-	0.34	0.4	W
_	High-side switch ON resistance	$T_j = 125 \ ^{\circ}C^{(1)}$	-	0.53	0.59	W
R _{DS(ON)}		T _j = 25 °C	-	0.28	0.34	W
	Low-side switch ON resistance	$T_j = 125 \ ^{\circ}C^{(1)}$	-	0.47	0.53	W
		EN = low; OUT = V _S	-	-	2	mA
I _{DSS}	Leakage current	EN = low; OUT = GND	-0.15	-	-	mA
Source dra	ain diodes				1	
V _{SD}	Forward ON voltage	I _{SD} = 2.8 A, EN = LOW	-	1.15	1.3	V
t _{rr}	Reverse recovery time	I _f = 2.8 A	-	300	-	ns
t _{fr}	Forward recovery time	-	-	200	-	ns
Logic inpu	it					
V _{IL}	Low level logic input voltage	-	-0.3	-	0.8	V
V _{IH}	High level logic input voltage	-	2	-	7	V
IIL	Low level logic input current	GND logic input voltage	-10	-	-	μA
I _{IH}	High level logic input current	7 V logic input voltage	-	-	10	μA
V _{th(ON)}	Turn-on input threshold	-	-	1.8	2.0	V
V _{th(OFF)}	Turn-off input threshold	-	0.8	1.3	-	V
V _{th(HYS)}	Input threshold hysteresis	-	0.25	0.5	-	V
Switching	characteristics					
t _{D(on)EN}	Enable to out turn ON delay time ⁽²⁾	I _{LOAD} = 2.8 A, resistive load	100	250	400	ns
t _{D(on)IN}	Input to out turn ON delay time	I _{LOAD} = 2.8 A, resistive load (deadtime included)	-	1.6	-	μs
t _{RISE}	Output rise time ⁽²⁾	I _{LOAD} = 2.8 A, resistive load	40	-	250	ns
t _{D(off)EN}	Enable to out turn OFF delay time ⁽²⁾	I_{LOAD} = 2.8 A, resistive load	300	550	800	ns
t _{D(off)IN}	Input to out turn OFF delay time	I _{LOAD} = 2.8 A, resistive load	-	600	-	ns

Table 5. Electrical characteristics (T_{amb} = 25 °C, V_e = 48 V, unless otherwise specified)



<u> </u>		ness otherwise specified) (col				
Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
t _{FALL}	Output fall time ⁽²⁾	I_{LOAD} = 2.8 A, resistive load	40	-	250	ns
t _{dt}	Deadtime protection	-	0.5	1	-	μs
f _{CP}	Charge pump frequency	-25 °C <t<sub>j < 125 °C</t<sub>	-	0.6	1	MHz
PWM com	parator and monostable					
$I_{RCA,} I_{RCB}$	Source current at pins RC_{A} and RC_{B}	$V_{RCA} = V_{RCB} = 2.5 V$	3.5	5.5	-	mA
V _{offset}	Offset voltage on sense comparator	V _{REFA,} V _{REFB} = 0.5 V	-	±5	-	mV
t _{PROP}	Turn OFF propagation delay ⁽³⁾	-	-	500	-	ns
t _{BLANK}	Internal blanking time on SENSE pins	-	-	1	-	μs
t _{ON(MIN)}	Minimum On time	-	-	1.5	2	μs
4	PWM recirculation time	R _{OFF} = 20 KΩ; C _{OFF} = 1 nF	-	13	-	μs
t _{OFF}		R _{OFF} = 100 KΩ; C _{OFF} = 1 nF	-	61	-	μs
I _{BIAS}	Input bias current at pins $VREF_A$ and $VREF_B$	-	-	-	10	μA
Overcurre	nt protection					
I _{SOVER}	Input supply overcurrent protection threshold	T_j = -25 °C to 125 °C ⁽¹⁾	4	5.6	7.1	А
R _{OPDR}	Open drain ON resistance	I = 4 mA	-	40	60	W
t _{OCD(ON)}	OCD turn-on delay time ⁽⁴⁾	I = 4 mA; C _{EN} < 100 pF	-	200	-	ns
t _{OCD(OFF)}	OCD turn-off delay time(10)	I = 4 mA; C _{EN} < 100 pF	-	100	-	ns


Table 5. Electrical characteristics (T_{amb} = 25 °C, V_s = 48 V, unless otherwise specified) (continued)


1. Tested at 25 °C in a restricted range and guaranteed by characterization.

2. See Figure 3: Switching characteristic definition.

3. Measured applying a voltage of 1 V to pin SENSE and a voltage drop from 2 V to 0 V to pin VREF.

4. See Figure 4: Overcurrent detection timing definition.










Figure 4. Overcurrent detection timing definition



5 Circuit description

5.1 Power stages and charge pump

The L6207 device integrates two independent power MOS full bridges. Each power MOS has an $R_{DS(ON)} = 0.3 \Omega$ (typical value at 25 °C), with intrinsic fast freewheeling diode. Cross conduction protection is achieved using a deadtime (t_d = 1 µs typical) between the switch off and switch on of two power MOS in one leg of a bridge.

Using N-channel power MOS for the upper transistors in the bridge requires a gate drive voltage above the power supply voltage. The bootstrapped (V_{BOOT}) supply is obtained through an internal oscillator and few external components to realize a charge pump circuit as shown in *Figure 5*. The oscillator output (VCP) is a square wave at 600 kHz (typical) with 10 V amplitude. Recommended values/part numbers for the charge pump circuit are shown in *Table 6*.

Component	Value
C _{BOOT}	220 nF
C _P	10 nF
R _P	100 Ω
D1	1N4148
D2	1N4148

Table 6. Charge pump external components values




Figure 5. Charge pump circuit

5.2 Logic inputs

Pins IN1_A, IN2_B, IN1_B and IN2_B are TTL/CMOS compatible logic inputs. The internal structure is shown in *Figure 6*. Typical value for turn-on and turn-off thresholds are respectively $V_{th(on)} = 1.8$ V and $V_{th(off)} = 1.3$ V.

Pins EN_A and EN_B have identical input structure with the exception that the drains of the overcurrent and thermal protection MOSFETs (one for the bridge A and one for the bridge B) are also connected to these pins. Due to these connections some care needs to be taken in driving these pins. The EN_A and EN_B inputs may be driven in one of two configurations as



shown in *Figure* 7 or 8. If driven by an open drain (collector) structure, a pull-up resistor R_{EN} and a capacitor C_{EN} are connected as shown in *Figure* 7. If the driver is a standard pushpull structure, the resistor R_{EN} and the capacitor C_{EN} are connected as shown in *Figure* 8. The resistor R_{EN} should be chosen in the range from 2.2 k Ω to 180 K Ω . Recommended values for R_{EN} and C_{EN} are respectively 100 K Ω and 5.6 nF. More information on selecting the values is found in *Section* 7.1: *Non-dissipative overcurrent protection on page* 18.




Figure 6. Logic inputs internal structure







Figure 8. EN $_{\rm A}$ and EN $_{\rm B}$ pins push-pull driving



	Inputs		Ou	tputs	(1)
EN	IN1	IN2	OUT1 OUT2		Description ⁽¹⁾
L	X ⁽²⁾	X ⁽²⁾	High Z ⁽³⁾	High Z ⁽³⁾	Disable
Н	L	L	GND	GND	Brake mode (lower path)
Н	Н	L	Vs	GND (Vs) ⁽⁴⁾	Forward
Н	L	Н	GND (Vs) ⁽⁴⁾	Vs	Reverse
Н	Н	Н	Vs	Vs	Brake mode (upper path)

Table 7. Truth table

1. Valid only in case of load connected between OUT1 and OUT2.

2. X = don't care.

3. High Z = high impedance output.

4. GND (Vs) = GND during t_{ON} , vs. during t_{OFF} .



6 **PWM** current control

The L6207 device includes a constant off time PWM current controller for each of the two bridges. The current control circuit senses the bridge current by sensing the voltage drop across an external sense resistor connected between the source of the two lower power MOS transistors and ground, as shown in *Figure 9*. As the current in the load builds up the voltage across the sense resistor increases proportionally. When the voltage drop across the sense resistor becomes greater than the voltage at the reference input (VREF_A or VREF_B), the sense comparator triggers the monostable switching the low-side MOS off. The low-side MOS remains off for the time set by the monostable and the motor current recirculates in the upper path. When the monostable times out, the bridge will again turn on. Since the internal deadtime, used to prevent cross conduction in the bridge, delays the turn on of the power MOS, the effective off time is the sum of the monostable time plus the deadtime.






Figure 10 shows the typical operating waveforms of the output current, the voltage drop across the sensing resistor, the RC pin voltage and the status of the bridge. Immediately after the low-side power MOS turns on, a high peak current flows through the sensing resistor due to the reverse recovery of the freewheeling diodes. The L6207 device provides a 1 μ s blanking time t_{BLANK} that inhibits the comparator output so that this current spike cannot prematurely retrigger the monostable.






Figure 10. Output current regulation waveforms



Figure 11 shows the magnitude of the off time t_{OFF} versus C_{OFF} and R_{OFF} values. It can be approximately calculated from the equations:

Equation 1

$$t_{RCFALL} = 0.6 \cdot R_{OFF} \cdot C_{OFF}$$

 $t_{OFF} = t_{RCFALL} + t_{DT} = 0.6 \cdot R_{OFF} \cdot C_{OFF} + t_{DT}$

where R_{OFF} and C_{OFF} are the external component values and t_{DT} is the internally generated deadtime with:

Equation 2

 $\begin{array}{l} 20 \ \text{K}\Omega \leq \text{R}_{OFF} \leq 100 \ \text{K}\Omega \\ \\ 0.47 \ \text{nF} \leq \text{C}_{OFF} \leq 100 \ \text{nF} \\ \\ t_{DT} = 1 \ \mu\text{s} \ (\text{typical value}) \end{array}$

Therefore:

Equation 3

 $t_{OFF(MIN)} = 6.6 \ \mu s$

 $t_{OFF(MAX)} = 6 \text{ ms}$

These values allow a sufficient range of t_{OFF} to implement the drive circuit for most motors.

The capacitor value chosen for C_{OFF} also affects the rise time t_{RCRISE} of the voltage at the pin RCOFF. The rise time t_{RCRISE} will only be an issue if the capacitor is not completely charged before the next time the monostable is triggered. Therefore, the on time t_{ON} , which depends by motors and supply parameters, has to be bigger than t_{RCRISE} for allowing a good current regulation by the PWM stage. Furthermore, the on time t_{ON} cannot be smaller than the minimum on time $t_{ON(MIN)}$.


Equation 4

$$\begin{cases} t_{ON} > t_{ON(MIN)} = 1.5 \mu s \text{ (typ. value)} \\ t_{ON} > t_{RCRISE} - t_{DT} \end{cases}$$


 $t_{RCRISE} = 600 \cdot C_{OFF}$

Figure 12 shows the lower limit for the on time t_{ON} for having a good PWM current regulation capacity. It has to be said that t_{ON} is always bigger than $t_{ON(MIN)}$ because the device imposes this condition, but it can be smaller than t_{RCRISE} - t_{DT} . In this last case the device continues to work but the off time t_{OFF} is not more constant.

So, small C_{OFF} value gives more flexibility for the applications (allows smaller on time and, therefore, higher switching frequency), but the smaller is the value for C_{OFF} , the more influential will be the noises on the circuit performance.










7 Slow decay mode

Figure 13 shows the operation of the bridge in the slow decay mode. At the start of the off time, the lower power MOS is switched off and the current recirculates around the upper half of the bridge. Since the voltage across the coil is low, the current decays slowly. After the deadtime the upper power MOS is operated in the synchronous rectification mode. When the monostable times out, the lower power MOS is turned on again after some delay set by the deadtime to prevent cross conduction.





7.1 Non-dissipative overcurrent protection

The L6207 device integrates an "Overcurrent Detection" circuit (OCD). This circuit provides protection against a short-circuit to ground or between two phases of the bridge. With this internal overcurrent detection, the external current sense resistor normally used and its associated power dissipation are eliminated. *Figure 14* shows a simplified schematic of the overcurrent detection circuit.

To implement the overcurrent detection, a sensing element that delivers a small but precise fraction of the output current is implemented with each high-side power MOS. Since this current is a small fraction of the output current there is very little additional power dissipation. This current is compared with an internal reference current I_{REF}. When the output current in one bridge reaches the detection threshold (typically 5.6 A), the relative OCD comparator signals a fault condition. When a fault condition is detected, the EN pin is pulled below the turn off threshold (1.3 V typical) by an internal open drain MOS with a pull down capability of 4 mA. By using an external R-C on the EN pin, the off time before recovering normal operation can be easily programmed by means of the accurate thresholds of the logic inputs.






Figure 14. Overcurrent protection simplified schematic

Figure 15 shows the overcurrent detection operation. The disable time t_{DISABLE} before recovering normal operation can be easily programmed by means of the accurate thresholds of the logic inputs. It is affected whether by C_{EN} and R_{EN} values and its magnitude is reported in *Figure 16*. The delay time t_{DELAY} before turning off the bridge when an overcurrent has been detected depends only by C_{EN} value. Its magnitude is reported in *Figure 17*.

 C_{EN} is also used for providing immunity to the pin EN against fast transient noises. Therefore the value of C_{EN} should be chosen as big as possible according to the maximum tolerable delay time and the R_{EN} value should be chosen according to the desired disable time.

The resistor R_{EN} should be chosen in the range from 2.2 K Ω to 180 K Ω . Recommended values for R_{EN} and C_{EN} are respectively 100 K Ω and 5.6 nF that allow obtaining 200 μs disable time.



I_{OUT}

ISOVER

 V_{EN}

 $V_{th(ON)}$ $V_{th(OFF)}$

 V_{DD}

ON OCD OFF

ON


OFF

t_{OCD(ON)}

t_{DELAY}

t_{EN(FALL)}

BRIDGE




tDISABLE

t_{EN(RISE)}

t_{D(ON)EN}

D02IN1400




t_{OCD(OFF)}

t_{D(OFF)EN}



20/32



7.2 Thermal protection

In addition to the overcurrent protection, the L6207 device integrates a thermal protection for preventing the device destruction in case of junction overtemperature. It works sensing the die temperature by means of a sensible element integrated in the die. The device switches-off when the junction temperature reaches 165 °C (typ. value) with 15 °C hysteresis (typ. value).

8 Application information

A typical application using the L6207 device is shown in *Figure 18*. Typical component values for the application are shown in *Table 8*. A high quality ceramic capacitor in the range of 100 to 200 nF should be placed between the power pins (VS_A and VS_B) and ground near the L6207 device to improve the high frequency filtering on the power supply and reduce high frequency transients generated by the switching. The capacitors connected from the EN_A and EN_B inputs to ground set the shutdown time for the bridge A and bridge B respectively when an overcurrent is detected (see Section 7.1: Non-dissipative overcurrent protection on page 18). The two current sensing inputs (SENSE_A and SENSE_B) should be connected to the sensing resistors with a trace length as short as possible in the layout. The sense resistors should be non-inductive resistors to minimize the di/dt transients across the resistor. To increase noise immunity, unused logic pins (except EN_A and EN_B) are best connected to 5 V (high logic level) or GND (low logic level) (see *Table 4: Pin description on page 6*). It is recommended to keep power ground and signal ground separated on the PCB.

Component	Value
C ₁	100 μF
C ₂	100 nF
C _A	1 nF
C _B	1 nF
C _{BOOT}	220 nF
C _P	10 nF
C _{ENA}	5.6 nF
C _{ENB}	5.6 nF
C _{REFA}	68 nF
C _{REFB}	68 nF
D ₁	1N4148
D ₂	1N4148
R _A	39 ΚΩ
R _B	39 ΚΩ
R _{ENA}	100 ΚΩ
R _{ENB}	100 ΚΩ
R _P	100 Ω
R _{SENSEA}	0.3 Ω
R _{SENSEB}	0.3 Ω

Table 8. Component values	for typical application
---------------------------	-------------------------








Figure 18. Typical application

8.1 Output current capability and IC power dissipation

In *Figure 19* and *Figure 20* are shown the approximate relation between the output current and the IC power dissipation using PWM current control driving two loads, for two different driving types:

- One full bridge ON at a time (*Figure 19*) in which only one load at a time is energized.
- Two full bridges ON at the same time (*Figure 20*) in which two loads at the same time are energized.

For a given output current and driving type the power dissipated by the IC can be easily evaluated, in order to establish which package should be used and how large must be the on-board copper dissipating area to guarantee a safe operating junction temperature (125 °C maximum).







Figure 19. IC Power dissipation versus output current with one full bridge ON at a time

Figure 20. IC Power dissipation versus output current with two full bridges ON at the same time








8.2 Thermal management

In most applications the power dissipation in the IC is the main factor that sets the maximum current that can be delivered by the device in a safe operating condition. Therefore, it has to be taken into account very carefully. Besides the available space on the PCB, the right package should be chosen considering the power dissipation. Heat sinking can be achieved using copper on the PCB with proper area and thickness. *Figure 22, 23* and *23* show the junction to ambient thermal resistance values for the PowerSO36 and SO24 packages.

For instance, using a PowerSO package with a copper slug soldered on a 1.5 mm copper thickness FR4 board with a 6 cm² dissipating footprint (copper thickness of 35 µm), the R_{th j-amb} is about 35 °C/W. *Figure 21* shows mounting methods for this package. Using a multilayer board with vias to a ground plane, thermal impedance can be reduced down to 15 °C/W.















Figure 23. SO24 junction ambient thermal resistance versus on-board copper area













DocID7513 Rev 3

9 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK is an ST trademark.

9.1 PowerSO36 package information








	Table 9. PowerSO36 package mechanical data Dimensions						
Symbol	mm			inch			
-	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	-	-	3.60	-	-	0.141	
a1	0.10	-	0.30	0.004	-	0.012	
a2		-	3.30	-	-	0.130	
a3	0	-	0.10	0	-	0.004	
b	0.22	-	0.38	0.008	-	0.015	
С	0.23	-	0.32	0.009	-	0.012	
D ⁽¹⁾	15.80	-	16.00	0.622	-	0.630	
D1	9.40	-	9.80	0.370	-	0.385	
E	13.90	-	14.50	0.547	-	0.570	
е	-	0.65	-	-	0.0256	-	
e3		11.05	-	-	0.435	-	
E1 ⁽¹⁾	10.90	-	11.10	0.429	-	0.437	
E2	-	-	2.90	-	-	0.114	
E3	5.80	-	6.20	0.228	-	0.244	
E4	2.90	-	3.20	0.114	-	0.126	
G	0	-	0.10	0	-	0.004	
Н	15.50	-	15.90	0.610	-	0.626	
h	-	-	1.10	-	-	0.043	
L	0.80	-	1.10	0.031	-	0.043	
N	10° (max.)						
S	8° (max.)						

Table 9. PowerSO36 package mechanical data

1. "D" and "E1" do not include mold flash or protrusions.

- Mold flash or protrusions shall not exceed 0.15 mm (0.006 inch).

- Critical dimensions are "a3", "E" and "G".

57

9.2 SO24 package information




Table 10. SO24 package mechanical data

		Dimensions				
Symbol	mm			inch		
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	2.35	-	2.65	0.093	-	0.104
A1	0.10	-	0.30	0.004	-	0.012
В	0.33	-	0.51	0.013	-	0.020
С	0.23	-	0.32	0.009	-	0.013
D ⁽¹⁾	15.20	-	15.60	0.598	-	0.614
E	7.40	-	7.60	0.291	-	0.299
е	-	1.27	-	-	0.050	-
Н	10.0	-	10.65	0.394	-	0.419
h	0.25	-	0.75	0.010	-	0.030
L	0.40	-	1.27	0.016	-	0.050
k	0° (min.), 8° (max.)					
ddd	-	-	0.10	-	-	0.004

1. "D" dimension does not include mold flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 0.15 mm per side.

DocID7513 Rev 3



10 Revision history

Date	Revision	Changes
03-Sep-2003	1	Initial release.
20-Feb-2014	2	 Updated Section : Description on page 1 (removed "MultiPower-" from "MultiPower-BCD technology"). Added Revision history on page 31. Updated Section 1: Block diagram (added section title, numbered and moved Figure 1: Block diagram from page 1 to page 3). Added title to Section 2: Maximum ratings on page 4, added numbers and titles from Table 1: Absolute maximum ratings to Table 3: Thermal data. Added title to Section 3: Pin connections on page 6, added number and title to Figure 2: Pin connections (top view), renumbered note 1 below Figure 2, added title to Table 4: Pin description, renumbered note 1 below Table 4. Added title to Section 4: Electrical characteristics on page 8, added title and number to Table 5, renumbered notes 1 to 4 below Table 5. Renumbered Figure 3 and Figure 4. Added section numbers to Section 5: Circuit description on page 11, Section 5.1 and Section 5.2. Removed "and uC" from first sentence in Section 5: Pigure 9 to Figure 8. Added numbers to Section 7: Slow decay mode on page 18, Section 7.1 and Section 7.2). Renumbered Figure 13 to Figure 17. Added section numbers to Section 8: Application information on page 22, Section 8.1 and Section 8.2. Renumbered Table 8, added header to Table 8, added header to Table 8. Renumbered Figure 18 to Figure 29. Updated section 19: Package information on page 28 (added main title and ECOPACK text. Added titles from Table 9: PowerSO36 package mechanical data to Table 10: SO24 package mechanical data and from Figure 30: PowerSO36 package outline to Figure 31: SO24 package outline, reversed order of named tables and figures. Removed 3D figures 50 package, replaced 0.200 by 0.020 inch of max. B value in Table 10). Added cross-references throughout document. Added section 10: Revision history and Table 11. Minor modifications throughout document.
03-Oct-2018	3	Removed PowerDIP24 package from the whole document. Removed "T _j " from <i>Table 2 on page 4</i> . Minor modifications throughout document.

Table 11. Docume	nt revision history
------------------	---------------------



IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved

DocID7513 Rev 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics: L6207D L6207PD L6207D013TR L6207PD013TR