

EMI Suppression Beads (2643001301)



Part Number: 2643001301

43 SHIELD BEAD

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 1= Not Burnished 2 = Burnished
- The last digit of the Parylene coated part is a “4,” which is available upon request. The minimum coating thickness beads is 0.005 mm (0.0002”).

Fair- Rite offers a broad selection of ferrite EMI suppression beads with guaranteed minimum impedance specifications.

Our “Shield Bead Kit” (part number 0199000019) contains a selection of these beads.

For any EMI suppression bead requirement not listed here, feel free to contact our customer service for availability and pricing.

[Catalog Drawing](#)

[3D Model](#)

The C dimension, the bead length, can be modified to suit specific applications.

Weight: 0.18 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	3.55	±0.15	0.14	—
B	1.65	+0.25	0.07	—
C	5.95	±0.25	0.234	—




Chart Legend

+ Test frequency

• The column "H (Oe)" gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of “H” times the actual NI (ampere- turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note □How to choose Ferrite Components for EMI Suppression□.


Typical Impedance (Ω)	
10 MHz	22
25 MHz ⁺	33
100 MHz ⁺	48
250 MHz	53
Electrical Properties	
H(Oe)	1.6

Suppression beads are controlled for impedances only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is listed on our catalog drawing.

[Catalog Drawing](#)

Single turn impedance tests for 73 and 43 material beads are performed on the E4990A Impedance Analyzer. The 61 material beads are tested on the E4991A / HP4291B Impedance Analyzer. Beads are tested with the shortest practical wire length.

2643001301



Impedance, reactance, and resistance vs. frequency.