

KERN NIB 600K-2



Compact, robust drive-through scale - particularly mobile thanks to its carrying handle, rollers and lightweight construction



Service

Adjustment at the location of installation: 961-250

DAkkS Certificate: 963-130

Category

Brand: KERN

Category: Balances

Product Group: Drive-through scale

Packaging & shipping

Delivery: 48 h

Dimensions packaging (WxDxH): 1135 x 1050 x 200 mm

Gross weight: 62 kg

Net weight: 40 kg

Shipping method: Freight forwarder

Construction

Cable length of display device: 3 m

Casing material: Steel lacquered

Dimensions of display device (WxDxH): 200 x 130 x 60 mm

Dimensions of weighing plate (WxDxH): 1000 x 1000 x 40 mm

Level indicator: yes

Material weighing plate: Steel lacquered

Overall dimensions mounted (WxDxH): 1066 x 1000 x 80 mm

Revolving screw feet: yes

Wall mount: yes

Weighing surface (WxD): 800 x 800 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options: External calibration

Linearity: 100 g

Readability [d]: 200 g

Recommended adjusting weight: 300 kg (M1)

Repeatability: 100 g

Resolution: 3000

Warm up time: 10 min

Weighing capacity [Max]: 600 kg

Weighing system: Strain gauge

Weighing units: g lb oz kg

Display

Display digit height (large): 2,500 cm

Display digit height (small): 2,500 cm

Functions

BMI function: yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: -10 °C

Minimum humidity: 5 %

Power supply

Battery: 4x1.5 V AA

Input voltage: 100 V - 240V AC 50/60Hz
0.3A

Mains adapter: Mains adapter external

Mains adapter/adaptor included: EURO UK AUS US

Operating time: 40 h