

Terminals

Part Number: 9537470000

WDU 6 SL/EN

Terminal WDU w. ten. clamp and spring



Representative Photo

Selected Features

Installation advice	TS 35 + TS 32
Type of connection	Screw connection
Insulation material	Wemid
Rated voltage	500 V
Rated current	41 A
Rated cross-section	6 mm ²
Version	Feed-through terminal
Colour of insulating material	dark beige
Rated impuls voltage	6 kV

Additional Technical Data

EAN	4008190026097
Width	8 mm
Length	57 mm
No. of identical terminals	1
Plug gauge	A4
min. conductor	0.5 mm ²
max. conductor	10.0 mm ²
Height with TS	54.2 mm
Degree of soiling	3
Type of Cross-connection 1	WQV
No. of identical Cross-connection 1	1
Stripping length	16 mm
Blade size / AF size	5.5 x 0.8 mm
Solid, min.	0.5 mm ²
Solid, max.	6 mm ²
Stranded, min.	1.5 mm ²
	6 mm ²

Flexible, min.	0.5 mm ²
Flexible, max.	6 mm ²

Top of Page

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from: