

306A - Click wrenches with removable ratchet




Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Factory accuracy: $\pm 2\%$ except: - R.306-25D - K306-600D - K306-1000D ($\pm 4\%$). - R.304DA ($\pm 6\%$).
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories: - End fitting: 9 x 12 or 14 x 18 mm. - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in a plastic box with ratchet and hinged handle (except Ref R.306A25 - R.301A - K.306A600 - K.306A1000).

	Length L [mm]	Attachement [""]	Capacity [Nm]	Graduation [Nm]	Handle type [""]	Weight [Kg]	Ratchet [""]	Contents []
J.306A100	437.0	9 x 12	20 - 100	1.0	S.305P	1.0	J.372	Tray: PL.352A
J.306A50	357.0	9 x 12	10 - 50	1.0	S.305P	0.93	J.372	Roll: N.38A-9E
K.306A600	990.0	14 x 18	120 - 600	2.0		5.2	K.382	
R.301A	185.0	9 x 12	1 - 5	0.05		0.29	R.372	Box
R.306A25	271.0	9 x 12	5 - 25	0.1		0.45	R.372	Box
S.306A100	437.0	9 x 12	20 - 100	1.0	S.305P	1.0	S.372	
S.306A200	515.0	14 x 18	40 - 200	1.0	S.305P	1.3	S.382	
S.306A350	725.0	14 x 18	70 - 350	2.0	S.305P	1.8	S.382	