



- VDD_OpAmp → 9 B OpAmp
- VXX → 3.3 B DSP
- VDD_GEN2 → 3.3 B/5 B reпертоп 12.288 MHz
- VDD_GEN1 → 3.3 B/5 B репертоп 11.2896 MHz