# Autotransformer AIM 5,0/2,5



## Standards

Autotransformer to: VDE 0570 Part 2-13, DIN EN 61558-2-13, EN 61558-2-13, IEC 61558-2-13

þ

#### Advantages

Low weight and small size (compared to isolating transformers)

Integrated short circuit and overload protection

Very high efficiency

Very good moisture protection and low noise thanks to XtraDenseFill resin encapsulation (AIM 1.8/8 - AIM 5.0/2.5)

Screw terminals under cover with strain relief

# Applications

Autotransformer for adjustment of the voltage on the input and output sides with no requirement for electrical isolation.

## Approvals

BLOCKO-



# Autotransformer AIM 5,0/2,5

	Туре	AIM 5,0/2,5		Туре	AIM 5,0/2,5
Electrical data 7	Input		30	Terminal and mounting	
	Rated input Voltage	115 Vac/220 Vac 230 Vac/240 Vac	1	Terminals	Screw-type terminal
	Rated frequency	50 - 60 Hz		Fixing method	Fixing holes in the terminal connection
	Output		lta	-	compartment
	Rated output voltage	115 Vac/220 Vac 230 Vac/240 Vac	Mechanical data	Measures and weights	
	Rated output current	2.50 (PRI 115 / SEC 220, 230, 240); 5.00 (PRI 115 / SEC 115); 5.00 (PRI 220, 230, 240 / SEC 115, 220, 230, 240)		Weight	5.00 kg
	No-load loss (typ.)	11.80 W			
	Environment			4.3	
	Ambient temperature max.	40 °C			
	Safety and protection				
	Туре	Resin encapsulated transformer			
	Class of Insulation System	A			
	Protection index	IP 20			
	Safety class	May be used in protection category I and II. When protection category I devices are equipped the protective conductor in the output must be connected with the lead-in protective conductor.			
	Short circuit strength	non-inherently short-circuit proof			
	Order numbers				
	Order Number	AIM 5,0/2,5			

