

COAXIAL ADAPTER, BNC, 75 Ohm, jack / jack (female / female)

31_BNC-75-0-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body		SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	75 Ω
Interface frequency	1 GHz

Mechanical data	
Weight	0.0121 kg
Mating cycles	500

COAXIAL ADAPTER, BNC, 75 Ohm, jack / jack (female / female)

31_BNC-75-0-1/133_N

Environmental data	
Operation temperature	-65 °C ... 165°C

Ordering Information Table		
Item number	Item description	Packaging type
22541003	31_BNC-75-0-1/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2418 / Date of publication: 26.11.2023 / uncontrolled copy