




Features

- 100% avalanche tested
- Avalanche ruggedness
- Very low intrinsic capacitances
- High speed switching
- Very low on-resistance



Applications

- Welder
- UPS
- PV Inverter
- Switching applications



Electrical ratings

Absolute maximum ratings			
Parameter	Symbol	Value	Unit
Drain-source voltage ($V_{GS} = 0$)	V_{DS}	1200	V
Gate- source voltage	V_{GS}	± 30	
Drain current (continuous) at $T_C = 25\text{ }^\circ\text{C}$	I_D	8	A
Drain current (continuous) at $T_C = 100\text{ }^\circ\text{C}$		5.5	
Drain current (pulsed)	I_{DM}	22	
Total dissipation at $T_C = 25\text{ }^\circ\text{C}$ (TO-247)	P_{TOT}	260	W
Derating factor		2.56	W/ $^\circ\text{C}$
Operating junction temperature	T_J	-55 to 175	$^\circ\text{C}$
Storage temperature	T_{stg}		

Thermal data				
Parameter	Symbol	Value		Unit
		TO-247	TO-220	
Thermal resistance junction-case max	$R_{thj-case}$	0.39	0.5	W/ $^\circ\text{C}$
Thermal resistance junction-ambient max	$R_{thj-amb}$	50	62.5	
Maximum lead temperature for soldering purpose	T_J	300		

Avalanche characteristics			
Parameter	Symbol	Max value	Unit
Avalanche current, repetitive or not-repetitive (pulse width limited by T_J max)	I_{AR}	8	A
Single pulse avalanche energy (starting $T_J = 25\text{ °C}$, $I_D = I_{AR}$, $V_{DD} = 50\text{ V}$)	E_{AS}	760	mJ

Electrical Characteristics ($T_{vj} = 25\text{ °C}$ unless otherwise specified)

On /off states						
Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Drain-source breakdown voltage	$V_{(BR)DSS}$	$I_D = 1\text{ mA}$, $V_{GS} = 0$	1200	-	-	V
Zero gate voltage drain current ($V_{GS} = 0$)	I_{DSS}	$V_{DS} = \text{Max rating}$ $V_{DS} = \text{Max rating}$, $T_C = 125\text{ °C}$	-	-	66	μA
Gate-body leakage current ($V_{DS} = 0$)	I_{GSS}	$V_{GS} = \pm 30\text{ V}$	-	-	± 100	nA
Gate threshold voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 250\text{ }\mu\text{A}$	3	4	5	V
Static drain-source on resistance	$R_{DS(on)}$	$V_{GS} = 10\text{V}$, $I_D = 4\text{A}$	-	2.3	3.5	Ω

Dynamic						
Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Forward transconductance	g_{fs}	$V_{DS} = 15\text{ V}$, $I_D = 4$	-	7.5	-	S
Input capacitance	C_{iss}	$V_{DS} = 25\text{V}$, $f = 1\text{MHz}$, $V_{GS} = 0$	-	3310	-	pF
Output capacitance	C_{oss}		-	294	-	
Reverse transfer capacitance	C_{rss}		-	22.4	-	
Equivalent Output capacitance	$C_{oss\text{ eq.}}$	$V_{GS} = 0$, $V_{DS} = 0$ to 1200V	-	118	-	
Gate input resistance	R_g	$f = 1\text{MHz}$ Gate DC Bias = 0 Test signal level = 20mV open drain	-	2.2	-	Ω
Total gate charge	Q_g	$V_{DD} = 1200\text{V}$, $I_D = 8\text{A}$ $V_{GS} = 10\text{V}$	-	89.3	-	nC
Gate-source charge	Q_{gs}		-	15.8	-	
Gate-drain charge	Q_{gd}		-	50.3	-	

Switching times						
Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 750 \text{ V}$, $I_D = 4 \text{ A}$, $R_G = 4.7 \Omega$, $V_{GS} = 10 \text{ V}$	-	41	-	ns
Rise time	t_r		-	14.7	-	
Turn-off-delay time	$t_{d(off)}$		-	86	-	
Fall time	t_f		-	31	-	


Source drain diode						
Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Source-drain current	I_{SD}		-	8	-	A
Source-drain current (pulsed)	I_{SDM}		-	22	-	
Forward on voltage	V_{SD}	$I_{SD} = 6 \text{ A}$, $V_{GS} = 0$	-	-	1.2	V
Reverse recovery time	t_{rr}	$I_{SD} = 6 \text{ A}$, $di/dt = 100 \text{ A}/\mu\text{s}$ $V_{DD} = 60 \text{ V}$	-	980	-	nS
Reverse recovery charge	Q_{rr}		-	9.5	-	μC
Reverse recovery current	I_{RRM}		-	19.3	-	A
Reverse recovery time	t_{rr}	$I_{SD} = 6 \text{ A}$, $di/dt = 100 \text{ A}/\mu\text{s}$ $V_{DD} = 60 \text{ V}$, $T_J = 150^\circ\text{C}$	-	884	-	nS
Reverse recovery charge	Q_{rr}		-	8.2	-	μC
Reverse recovery current	I_{RRM}		-	18.6	-	A

Order information


MS8N120FC	TO-247		
MS8N120FT	TO-220		

Electrical characteristics


1. Output Characteristics @ 25°C




2. Extended Output Characteristics @ 25°C




3. Output Characteristics @ 125°C




4. $R_{DS(on)}$ Normalized to I_D Value vs. Junction Temperature




5. $R_{DS(on)}$ Normalized to I_D Value vs. I_D




6. Drain Current vs. Case Temperature




7. Input Admittance




8. Transconductance




9. Source Current vs. Source-To-Drain




10. Gate Charge





11. Capacitance



12. Maximum Transient Thermal Resistance



Package outline dimension



Unit: mm

