




## **Datasheet**

# 3.15A Radial Non-Resettable Wire Ended Fuse, 250V

**RS Stock number 767-5153** 



### **Specifications:**

### **Operating Temperature**

-55°C to +125°C

### Vibration

MIL-STD-202G, Method 201(10-55 Hz x 3axis/no load)

#### Salt Spray

MIL-STD-202G, Method 101, Test Condition B (48Hrs)

#### Insulation Resistance

MIL-STD-202G, Method 302, Test Condition A (After Opening) 10,000 ohms minimum

#### Resistance to Solder Heat

MIL-STD-202G, Method 210, Test Condition B (10sec,at 260°C)

#### Thermal Shock:

MIL-STD-202G, Method 107, Test Condition B (-65°C to +125°C)

#### Material

Base and Cap: Black thermoplastic, UL 94-√0 Round Pins: Copper, Tin-plated

#### Material

Encapsulated, Epoxy-Coated Body; Solder Coated

Copper Wire Leads.


Lead Wire: Diameter 0.64mm


Wire Length: 22mm


RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



# Drawing (mm):







## **Electrical Characteristic:**

Rated	1.5ln 2.1ln		2.75ln		4 In		10 In	
Current	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
40mA~5A	60	2	400	10	150	3	20	150
	min	min	ms	sec	ms	sec	ms	ms
6.3 A~10A	60	2	400	10	150	3	15	150
	min	min	ms	sec	ms	sec	ms	ms