

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 16\_MMBX-50-1-1/111\_N



### Description

Right angle cable plug for flexible cable

Interface standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 12.4 GHz

#### Mechanical Data

Centre contact soldered  
Outer contact crimped  
Weight 0.0012 kg

#### Environmental Data

Operating Temperature -55 °C to 155 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Brass
Insulator	PFA / PTFE
Crimp ferrule	Copper

##### Surface Plating

Gold Plating (Nickel underplated)
SUCOPRO Plating
SUCOPRO Plating
Gold Plating (without Nickel underplating)

#### Related Documents

Outline drawing	DOU-00005795
Catalogue drawing	DOU-00005797
Assembly instruction	DOC-0000178673

#### Ordering Information

Single package 16\_MMBX-50-1-1/111\_NE

#### Additional Information

Suitable cables ENVIROFLEX\_178, RG\_178\_B/U, RG\_196\_A/U

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**