CHIP COIL (CHIP INDUCTORS) LQP03TN C CHIP C CHIP COIL (CHIP INDUCTORS) LQP03TN C CHIP C CHI

1.Scope

This reference specification applies to LQP03TN_02 series, Chip coil (Chip Inductors).

2.Part Numbering

(ex)	LQ	P	03	T	N	0N6	В	0	2	D
	Product ID	Structur	e Dimensio	n Applications	Category	Inductance	Tolerance	Features	Electrode	Packaging
			$(L \times W)$	and						D:Taping
				Characteristics	3					*B:Bulk
	*Bulk pac	king als	o availabl	e. (A product	is put in th	ne plastic ba	g under the	e taping co	nditions.)	

3.Rating

•Operating Temperature Range. -55°C to +125°C

(Ambient temperature: Rated current can be handled in this temperature range.)

• Storage Temperature Range. -55°C to +125°C

Customer			uctance	Q	DC Resistance	Self Resonant Frequency		Rated Current (mA)
Part Number	Part Number	(nH) Tolerance (r		(min)	(Ω max)	(MHz) Min. *Typ.		
	LQP03TN0N6B02D						199.	
	LQP03TN0N6C02D	0.6			0.07			850
	LQP03TN0N7B02D					20000		
	LQP03TN0N7C02D	0.7						
	LQP03TN0N8B02D				0.08			800
	LQP03TN0N8C02D	0.8				40000		
	LQP03TN0N9B02D					18000		
	LQP03TN0N9C02D	0.9					00000	
	LQP03TN1N0B02D						20000	
	LQP03TN1N0C02D	1.0						
	LQP03TN1N1B02D		1		0.10			750
	LQP03TN1N1C02D	1.1				47000		
	LQP03TN1N2B02D					17000		
	LQP03TN1N2C02D	1.2				-		
	LQP03TN1N3B02D							
	LQP03TN1N3C02D	1.3						
	LQP03TN1N4B02D					40000	40000	
	LQP03TN1N4C02D	1.4				16000	19600	
	LQP03TN1N5B02D		B:±0.1nH				47000	
	LQP03TN1N5C02D	1.5	C:±0.2nH	14			17900	
	LQP03TN1N6B02D					20	20000]
	LQP03TN1N6C02D	1.6				15000	20000	
	LQP03TN1N7B02D				0.15	15000	10100	
	LQP03TN1N7C02D	1.7					19100	<u> </u>
	LQP03TN1N8B02D					1770	17700	600
	LQP03TN1N8C02D	1.8					17700	
	LQP03TN1N9B02D						45400	
	LQP03TN1N9C02D	1.9				12500	15100	
	LQP03TN2N0B02D					12500	14800	
	LQP03TN2N0C02D	2.0					14600	
	LQP03TN2N1B02D						13900	
	LQP03TN2N1C02D	2.1				11000	12900	
	LQP03TN2N2B02D					11000	13400	
	LQP03TN2N2C02D	2.2]				13400	
	LQP03TN2N3B02D						12900	<u> </u>
	LQP03TN2N3C02D	2.3	J			10000	12300	
	LQP03TN2N4B02D				0.20		12200	500
	LQP03TN2N4C02D	2.4					12200	

MURATA MFG.CO., LTD

Spec No.JELF243C-0015T-01

Reference Only

P.2/12

Customer	t Number Part Number (nH) Tolerance (r		uctance	Q	DC Resistance	Self Resonant Frequency		Rated Current
Fait Number			(min)	(Ω max)	(MHz) Min. *Typ.		(mA)	
	LQP03TN2N5B02D			-		IVIIA.	*Тур.	
	LQP03TN2N5C02D	2.5					12200	
	LQP03TN2N6B02D					40000	40000	
	LQP03TN2N6C02D	2.6				10000	13300	
	LQP03TN2N7B02D				0.20		13000	
	LQP03TN2N7C02D	2.7	-		0.20		13000	500
	LQP03TN2N8B02D						11800	
	LQP03TN2N8C02D	2.8	-					
	LQP03TN2N9B02D	2.9				9500	12400	
	LQP03TN2N9C02D	2.9	-					
	LQP03TN3N0B02D LQP03TN3N0C02D	3.0					11900	
	LQP03TN3N0C02D	0.0			·			
	LQP03TN3N1C02D	3.1					11300	
	LQP03TN3N2B02D		1			0000	40000	
	LQP03TN3N2C02D	3.2				8000	10600	
	LQP03TN3N3B02D		1		0.25		10900	450
	LQP03TN3N3C02D	3.3	B:±0.1nH				10900	
	LQP03TN3N4B02D		C:±0.2nH				9400	
	LQP03TN3N4C02D	3.4				7000	5400	
	LQP03TN3N5B02D	25				1000	9600	
	LQP03TN3N5C02D	3.5	-					
	LQP03TN3N6B02D	3.6					9500	
	LQP03TN3N6C02D LQP03TN3N7B02D	0.0	-					
	LQP03TN3N7C02D	3.7				6000	8200	400
	LQP03TN3N8B02D	•••	-		0.30			
	LQP03TN3N8C02D	3.8		14			8100	
	LQP03TN3N9B02D					5700	7000	
	LQP03TN3N9C02D	3.9				5700	7900	
	LQP03TN4N0B02D						8600	
	LQP03TN4N0C02D	4.0	-				8000	
	LQP03TN4N1B02D						8400	
	LQP03TN4N1C02D	4.1	-			5300		
	LQP03TN4N2B02D	4.2					8600	
	LQP03TN4N2C02D	4.2						
	LQP03TN4N3H02D LQP03TN4N3J02D	4.3			0.40		9800	350
	LQP03TN4N3J02D LQP03TN4N7H02D		-		0.10			
	LQP03TN4N7J02D	4.7				4400	8800	
	LQP03TN5N1H02D		1			4000		
	LQP03TN5N1J02D	5.1				4200	8600	
	LQP03TN5N6H02D		1				8000	1
	LQP03TN5N6J02D	5.6				4000	0000	
	LQP03TN6N2H02D		H:±3%			-000	7900	
	LQP03TN6N2J02D	6.2	J:±5%					
	LQP03TN6N8H02D	6.8			0.60	3900	8000	300
	LQP03TN6N8J02D	0.0	-		0.00			300
	LQP03TN7N5H02D LQP03TN7N5J02D	7.5				3700	6700	
	LQP03TN7N5J02D LQP03TN8N2H02D		-					
	LQP03TN8N2J02D	8.2				3600	6600	
	LQP03TN9N1H02D		1		0.70	0.000		250
	LQP03TN9N1J02D	9.1				3300	5900	

Spec No.JELF243C-0015T-01

Reference Only

P.3/12

Customer Part Number	MURATA Part Number	(nH) Tolerance		Q (min)	DC Resistance (Ω max)	Self Resonant Frequency (MHz)		Rated Current (mA)
		(nH)	Iolerance			Min.	*Typ.	
	LQP03TN10NH02D	10			0.70	3200	5800	
	LQP03TN10NJ02D			14				_
	LQP03TN11NH02D	11			0.90		5400	
	LQP03TN11NJ02D				0.80	2900		_
	LQP03TN12NH02D	12			0.70			250
	LQP03TN12NJ02D				0.70		4300	250
	LQP03TN13NH02D	13			0.90			
	LQP03TN13NJ02D				0.80	2600		_
	LQP03TN15NH02D	15			0.70		3800	
	LQP03TN15NJ02D				0.70			
	LQP03TN16NH02D	16			0.05		3700	
	LQP03TN16NJ02D				0.95			200
	LQP03TN18NH02D	18		10	0.90		3400	200
	LQP03TN18NJ02D			12	0.80	2200		
	LQP03TN20NH02D	20			2.22		3600	150
	LQP03TN20NJ02D	_0			2.30			
	LQP03TN22NH02D	22			1.00		3300	
	LQP03TN22NJ02D				1.90			
	LQP03TN24NH02D	24					3200	
	LQP03TN24NJ02D				0.00	2000	0200	140
	LQP03TN27NH02D	27			2.30	2000	2900	
	LQP03TN27NJ02D	21					2000	
	LQP03TN30NH02D	30					2700	
	LQP03TN30NJ02D	00			0.05	1700	2100	4
	LQP03TN33NH02D	33			2.95	1100	2600	
	LQP03TN33NJ02D	00	H:±3%				2000	- 120
	LQP03TN36NH02D	36	11.1070			1500	2400	
	LQP03TN36NJ02D	00	J:±5%				2100	
	LQP03TN39NH02D	39			3.00		- 2200	
	LQP03TN39NJ02D	00		~				
	LQP03TN43NH02D	43		9		1300		
	LQP03TN43NJ02D	10						
	LQP03TN47NH02D	47						
	LQP03TN47NJ02D							
	LQP03TN51NH02D	51					2000	
	LQP03TN51NJ02D				2.02	1200	_000	
	LQP03TN56NH02D	56			3.90			
	LQP03TN56NJ02D							400
	LQP03TN62NH02D	62					1800	100
	LQP03TN62NJ02D		4		0	1100		4
	LQP03TN68NH02D	68			8		1500	
	LQP03TN68NJ02D							-
	LQP03TN75NJ02D	75						
	LQP03TN75NH02D		4			1000	1400	
	LQP03TN82NH02D	82						
	LQP03TN82NJ02D		4	0	10			
	LQP03TN91NH02D	91		8	10			
	LQP03TN91NJ02D	- •	4			900	1300	
	LQP03TNR10H02D	100						
	LQP03TNR10J02D							
								80
	LQP03TNR11H02D	110						00
		110			12	800	1100	00

P.4/12

Customer Part Number	MURATA Part Number	Inductance		Q	DC Resistance	Self Resonant Frequency		Rated Current
Fait Nulliber	Fait Nulliber	(nH)		(min)	(Ω max)	(MI	,	(mA)
		()	Tolerance			Min.	*Тур.	
	LQP03TNR13H02D	130					960	
	LQP03TNR13J02D	150				650	300	
	LQP03TNR15H02D	450			9	050	000	80
	LQP03TNR15J02D	150					880	
	LQP03TNR16H02D				0.40			
	LQP03TNR16J02D	160				600	840	
	LQP03TNR18H02D	8H02D 400		11	600	700	70	
	LQP03TNR18J02D	180	H:±3%				790	
	LQP03TNR20H02D	200	J:±5%	5			750	60
	LQP03TNR20J02D	200				500	750	
	LQP03TNR22H02D	000			13	500	740	
	LQP03TNR22J02D	220					710	
	LQP03TNR24H02D	240					620	
	LQP03TNR24J02D	240	40			450	630	
	LQP03TNR27H02D	070	1		15	450	E 9 0	
	LQP03TNR27J02D	270					580	


* Typical value is actual performance.

4. Testing Conditions

Spec No.JELF243C-0015T-01

《Unless otherwise specified》 Temperature : Ordinary Temperature / 15°C to 35°C Humidity : Ordinary Humidity / 25%(RH) to 85 %(RH) 《In case of doubt》


Temperature: 20°C ± 2°CHumidity: 60%(RH) to 70 %(RH)Atmospheric Pressure : 86kPa to 106 kPa



5. Appearance and Dimensions

6. Marking

Polarity Marking :white



Polarity Marking

7.Electrical Performance

No.	Item	Specification	Test Method
7.1	Inductance	Inductance shall meet item 3.	Measuring Equipment: KEYSIGHT E4991A or equivalent Measuring Frequency: (0.6nH~30nH) 500MHz (33nH~120nH) 300MHz (130nH~270nH) 100MHz Measuring Condition: Test signal level / about 0dBm Electrical length / 10mm Weight / about 1N to 5N Measuring Fixture: KEYSIGHT 16197A Position coil under test as shown in below and contact coil with each terminal by adding weight. Coloring side should be a topside, and should be in the direction of
7.2	Q	Q shall meet item 3.	the fixture for position of chip coil.
7.3	DC Resistance	DC Resistance shall meet item 3.	Measuring Equipment:Digital multi meter
7.4	Self Resonant Frequency(S.R.F)	S.R.F shall meet item 3.	Measuring Equipment: KEYSIGHT N5230A or equivalent
7.5	Rated Current	Self temperature rise shall be limited to 25°C max.	The rated current is applied.




8.Mechanical Performance

No.	Item	Specification	Test Method
8.1	Shear Test	Chip coil shall not be damaged after tested as test method.	Substrate:Glass-epoxy substrate
			Force:2N
			Hold Duration:5 s±1 s
			Applied Direction: Parallel to PCB.
			F
			Substrate/'
8.2	Bending Test	Chip coil shall not be damaged	Substrate:Glass-epoxy substrate
		after tested as test method.	(100mm × 40mm × 0.8mm)
			Speed of Applying Force:1mm /s
			Deflection:1mm
			Hold Duration:30 s Pressure jig
			R340 JF
			45 45 5 5 45
			k → → Product (in mm)
8.3	Vibration	Appearance:No damage	Substrate:Glass-epoxy substrate
		Inductance Change: within ±10%	Oscillation Frequency: 10Hz to 2000Hz to 10Hz for 20 min
			Total amplitude 1.5 mm or Acceleration
			amplitude 196 m/s^2 whichever is smaller.
			Testing Time:
			A period of 2h in each of
			3 mutually perpendicular directions.
8.4	Solderability	The electrode shall be at least 90%	Flux: Ethanol solution of rosin 25(wt)%
		covered with new solder coating.	(Immersed for 5s to 10s)
			Solder:Sn-3.0Ag-0.5Cu
			Pre-Heating:150°C±10°C / 60s to 90s
			Solder Temperature:240°C±5°C
8.5	Popietones to	Appeoropee:No demage	Immersion Time:3s±1s
0.D	Resistance to Soldering Heat	Appearance:No damage Inductance Change: within ±10%	Flux: Ethanol solution of rosin 25(wt)% (Immersed for 5s to 10s)
		moduciance Change. within ±10%	Solder:Sn-3.0Ag-0.5Cu
			Pre-Heating:150°C±10°C / 60s to 90s
			Solder Temperature:260°C±5°C
			Immersion Time:5s±1s
			Then measured after exposure in the room
			condition for 24h±2h.

No.	Item	Specification	Test Method
9.1	Heat Resistance	Appearance:No damage	Substrate:Glass-epoxy substrate
		Inductance Change: within ±10%	Temperature:125°C
			Time:1000h (+48h,-0h)
			Then measured after exposure in the
			room condition for 24h±2h.
9.2	Cold Resistance		Substrate:Glass-epoxy substrate
			Temperature:-55°C
			Time:1000 h (+48h,-0h)
			Then measured after exposure in the
			room condition for 24h±2h.
9.3	Humidity		Substrate:Glass-epoxy substrate
			Temperature:40°C±2°C
			Humidity:90%(RH) to 95%(RH)
			Time:1000 h(+48h,-0h)
			Then measured after exposure in the
			room condition for 24h±2h.
9.4	Temperature		Substrate:Glass-epoxy substrate
	Cycle		1 cycle:
			1 step: -55°C / 30min±3 min
			2 step:Ordinary temp. / 10~15 min
			3 step: 125°C / 30min±3 min
			4 step: Ordinary temp. / 10~15 min
			Total of 10 cycles
			Then measured after exposure in the
			room condition for 24h±2h.

10.Specification of Packaging

10.1 Appearance and Dimensions of paper tape (8mm-wide)



68N~R12; 0.65±0.03

10.2 Specification of Taping

- (1) Packing quantity (standard quantity)
 - 15,000 pcs. / reel
- (2) Packing Method

Products shall be packed in the cavity of the base tape and sealed by cover tape.

(3) Sprocket hole

The sprocket holes are to the right as the tape is pulled toward the user.

(4) Spliced point

Base tape and Cover tape has no spliced point.

(5) Missing components number


Missing components number within 0.1 % of the number per reel or 1 pc., whichever is greater, and are not continuous. The Specified quantity per reel is kept.

P.8/12

10.3 Pull Strength


Cover tape 5N min

10.4 Peeling off force of cover tape



10.5 Dimensions of Leader-tape, Trailer and Reel

There shall be leader-tape (top tape and empty tape) and trailer-tape (empty tape) as follows.



10.6 Marking for reel

Customer part number, MURATA part number, Inspection number(*1), RoHS Marking (*2), Quantity etc ···

*1) <expression insp<="" of="" th=""><th>pection No.></th><th></th><th>0000</th><th>XXX</th></expression>	pection No.>		0000	XXX
(1) Factory Code		(1)	(2)	(3)
(2) Date	First digit : Year / Last di			
	Second digit : Month / Jan. to Third, Fourth digit : Day	Sep. \rightarrow	1 to 9,	Oct. to Dec. \rightarrow O,N,D
(3) Serial No.	rinia, roarar aigit . Day			
*2) <expression of="" p="" rol<=""></expression>	HS Marking>	ROHS	– <u>Y</u> (∆	<u>.</u>)


*2) < Expression of RoHS Marking>

(1) RoHS regulation conformity parts. (2) MURATA classification number

10.7 Marking for Outside package (corrugated paper box)

Customer name, Purchasing order number, Customer part number, MURATA part number, RoHS Marking (*2) ,Quantity, etc ···

10.8 Specification of Outer Case



* Above Outer Case size is typical. It depends on a quantity of an order.

(1) (2)

(2)

Reference Only

11. 🕂 Caution

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
 - Aerospace equipment
- (3) Undersea equipment
- Power plant control equipment
- (5) Medical equipment
- (6) Transportation equipment (vehicles, trains, ships, etc.)
- Traffic signal equipment Disaster prevention / crime prevention equipment (8)

- (9) Data-processing equipment (10) Applications of similar complexity and /or reliability requirements to the applications listed in the above


12. Notice

Products can only be soldered with reflow.

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

12.1 Land pattern designing



12.2 Flux, Solder


Use rosin-based flux.

Don't use highly acidic flux with halide content exceeding 0.2(wt)% (chlorine conversion value). Don't use water-soluble flux.

- Use Sn-3.0Ag-0.5Cu solder.
- Standard thickness of solder paste : $100 \,\mu$ m~ $150 \,\mu$ m.

12.3 Reflow soldering conditions

- · Pre-heating should be in such a way that the temperature difference between solder and product surface is limited to 150°C max. Cooling into solvent after soldering also should be in such a way that the temperature difference is limited to 100°C max. Insufficient pre-heating may cause cracks on the product, resulting in the deterioration of products quality.
- Standard soldering profile and the limit soldering profile is as follows. The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.
- Reflow soldering profile



MURATA MFG.CO., LTD

12.4 Reworking with soldering iron


The following conditions must be strictly followed when using a soldering iron.

Pre-heating	150°C,1 min
Tip temperature	350°C max.
Soldering iron output	80W max.
Tip diameter	ϕ 3mm max.
Soldering time	3(+1,-0)s
Time	2 times

Note : Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the products due to the thermal shock.

12.5 Solder Volume

· Solder shall be used not to be exceeded the upper limits as shown below.



Accordingly increasing the solder volume, the mechanical stress to Chip is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.

12.6 Attention regarding P.C.B. bending

The following shall be considered when designing and laying out P.C.B.'s.


(1) P.C.B. shall be designed so that products are not subject to the mechanical stress due to warping the board.

[Products direction]



Products shall be located in the sideways direction (Length:a<b) to the mechanical stress.

(2) Products location on P.C.B. separation



Products (A,B,C,D) shall be located carefully so that products are not subject to the mechanical stress due to warping the board. Because they may be subjected the mechanical stress in order of $A>C>B \cong D$.

12.7 Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1) Cleaning temperature shall be limited to 60°C max.(40°C max for IPA)
- (2) Ultrasonic cleaning shall comply with the following conditions with avoiding the resonance phenomenon at the mounted products and P.C.B.
 - Power : 20 W / I max. Frequency : 28kHz to 40kHz Time : 5 min max.
- (3) Cleaner
 - 1. Alcohol type cleaner Isopropyl alcohol (IPA)
 - 2. Aqueous agent PINE ALPHA ST-100S
- (4) There shall be no residual flux and residual cleaner after cleaning. In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.
- (5) Other cleaning Please contact us.

P.11/12

12.8 Resin coating

When products are coated with resin, please contact us in advance.

12.9 Handling of a substrate

(1)There is a possibility of chip cracking caused by PCBexpansion/contraction with heat, because stress on a chip is different depending on PCB material and structure.

When the thermal expansion coefficient greatly differs between the board used for mounting and the chip, it will cause cracking of the chip due to the thermal expansion and contraction.

The chip is assumed to be mounted on the PCB of glass-epoxy material, and we don't test with other

PCB material which has different thermal expansion coefficient from Glass-epoxy.

When other PCB materials are considered, please be sure to evaluate by yourself.

(2)After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.


Excessive mechanical stress may cause cracking in the product.

In case of the mounting on flexible PCB, there is a possibility of chip cracking caused by mechanical stress even from small bending or twisting.

When the flexible PCB is considered, please be sure to evaluate by yourself.

Bending

Twisting



12.10 Storage and Handing Requirements

(1) Storage period

Use the products within 12 months after delivered. Solderability should be checked if this period is exceeded.

- (2) Storage conditions
 - Products should be stored in the warehouse on the following conditions.
 - Temperature : $-10^{\circ}C \sim 40^{\circ}C$

Humidity : 15% to 85% relative humidity No rapid change on temperature and humidity.

- Products should not be stored on bulk packaging condition to prevent the chipping of the core and the breaking of winding wire caused by the collision between the products.
- Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.

• Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.


(3) Handling Condition

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

13. <u>/ Note</u>

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2)You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice.
- Please approve our product specifications or transact the approval sheet for product specifications before ordering.

P.12/12



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

LQP15MN10NG00D LQP15MN10NG02D LQP15MN12NG00D LQP15MN12NG02D LQP15MN15NG00D
LQP15MN15NG02D LQP15MN18NG00D LQP15MN18NG02D LQP15MN1N0B00D LQP15MN1N0B02D
LQP15MN1N0W02D LQP15MN1N1B00D LQP15MN1N1B02D LQP15MN1N1W02D LQP15MN1N2B00D
LQP15MN1N2B02D LQP15MN1N2W02D LQP15MN1N3B00D LQP15MN1N3B02D LQP15MN1N3W02D
LQP15MN1N4W02D LQP15MN1N5B00D LQP15MN1N5B02D LQP15MN1N5W02D LQP15MN1N6B00D
LQP15MN1N6B02D LQP15MN1N6W02D LQP15MN1N7W02D LQP15MN1N8B00D LQP15MN1N8B02D
LQP15MN1N8W02D LQP15MN1N9W02D LQP15MN22NG00D LQP15MN22NG02D LQP15MN27NG00D
LQP15MN27NG02D LQP15MN2N0B00D LQP15MN2N0B02D LQP15MN2N0W02D LQP15MN2N1W02D
LQP15MN2N2B00D LQP15MN2N2B02D LQP15MN2N2C00D LQP15MN2N2W02D LQP15MN2N3W02D
LQP15MN2N4B00D LQP15MN2N4B02D LQP15MN2N4W02D LQP15MN2N5W02D LQP15MN2N6W02D
LQP15MN2N7B00D LQP15MN2N7B02D LQP15MN2N7C00D LQP15MN2N7W02D LQP15MN2N8W02D
LQP15MN2N9W02D LQP15MN33NG00D LQP15MN33NG02D LQP15MN3N0B00D LQP15MN3N0B02D
LQP15MN3N0W02D LQP15MN3N1W02D LQP15MN3N2W02D LQP15MN3N3B00D LQP15MN3N3B02D
LQP15MN3N3C00D LQP15MN3N3W02D LQP15MN3N4W02D LQP15MN3N5W02D LQP15MN3N6B00D
LQP15MN3N6B02D LQP15MN3N6W02D LQP15MN3N7W02D LQP15MN3N8W02D LQP15MN3N9B00D
LQP15MN3N9B02D LQP15MN3N9W02D LQP15MN4N3B00D LQP15MN4N3B02D LQP15MN4N7B00D
LQP15MN4N7B02D LQP15MN4N7C00D LQP15MN5N1B00D LQP15MN5N1B02D LQP15MN5N6B00D
LQP15MN5N6B02D LQP15MN5N6C00D LQP15MN6N2B00D LQP15MN6N2B02D LQP15MN6N8B00D
LQP15MN6N8B02D LQP15MN6N8C00D LQP15MN7N5B00D LQP15MN7N5B02D LQP15MN8N2B00D
LQP15MN8N2B02D LQP15MN9N1B00D LQP15MN9N1B02D LQP15TN10NH02D LQP15TN12NH02D