


G3VM-35□G□/351VY/401G□/401VY

MOS FET Relays SOP 4-pin, General-purpose Type

General-purpose MOS FET Relays in SOP 4-pin packages for a wide range of applications

- Contact form: 1a (SPST-NO) or 1b (SPST-NC)
- Load voltage: 350 V or 400 V



Note: The actual product is marked differently from the image shown here.

RoHS Compliant

Application Examples



- Semiconductor test equipment
- Test & Measurement equipment
- Communication equipment
- Various battery-driven devices
- Security equipment
- Industrial equipment
- Power circuit
- Amusement equipment

Package

(Unit : mm, Average)

SOP 4-pin

Special SOP 4-pin



Note: The actual product is marked differently from the image shown here.

Model Number Legend

G3VM-□□□□□
1 2 3 4 5

- 1. Load Voltage**
35 : 350 V
40 : 400 V
- 2. Contact form**
1 : 1a (SPST-NO)
3 : 1b (SPST-NC)

- 4. Additional functions**
None: Dielectric strength between I/O 1500 V
Y : Dielectric strength between I/O 3750 V

- 3. Package**
G : SOP 4-pin
V : Special SOP 4-pin

- 5. Other informations**
When specifications overlap, serial code is added in the recorded order.

Ordering Information

Package	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Stick packaging		Tape packaging	
					Model	Minimum package quantity	Model	Minimum package quantity
SOP4	1a (SPST-NO)	Surface-mounting Terminals	350 V	100 mA	G3VM-351G1	100 pcs.	G3VM-351G1(TR)	2,500 pcs.
				110 mA	G3VM-351G		G3VM-351G(TR)	
Special SOP 4-PIN	1b (SPST-NC)		350 V		125 pcs.	G3VM-351VY	125 pcs.	G3VM-351VY(TR05)
				3,000 pcs.	G3VM-351VY	3,000 pcs.	G3VM-351VY(TR)	
SOP4	1a (SPST-NO)	Surface-mounting Terminals	400 V	120 mA	G3VM-353G	100 pcs.	G3VM-353G(TR)	2,500 pcs.
				100 mA	G3VM-401G1		G3VM-401G1(TR)	
Special SOP 4-PIN	1a (SPST-NO)		400 V	120 mA	G3VM-401G	125 pcs.	G3VM-401G(TR)	500 pcs.
				110mA	G3VM-401VY		125 pcs.	

* The AC peak and DC value are given for the load voltage and continuous load current.

Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR)", "(TR05)" to the end of the model number.

SOP

G3VM-35□G□/351VY/401G□/401VY

Absolute Maximum Ratings (Ta = 25°C)


Item		Symbol	G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	Measurement conditions	
Input	LED forward current	IF	50		30	50	30	50	30	mA		
	LED forward current reduction rate	ΔIF/°C	-0.5		-0.3	-0.5	-0.3	-0.5	-0.3	mA/°C	Ta ≥ 25°C	
	LED reverse voltage	VR	5		6	5		6		V		
	Connection temperature	TJ	125									°C
Output	Load voltage (AC peak/DC)	V _{OFF}	350			400					V	
	Continuous load current (AC peak/DC)	Io	100	110	120	100	120	110		mA		
	ON current reduction rate	ΔIo/°C	-1.0	-1.1	-1.2	-1.0	-1.2	-1.1		mA/°C	Ta ≥ 25°C	
	Pulse ON current	Iop	300	330	360	300	360	330		mA	t=100 ms, Duty=1/10	
	Connection temperature	TJ	125									°C
	Dielectric strength between I/O *	Vi-o	1500			3750	1500			3750	Vrms	AC for 1 min
Ambient operating temperature	Ta	-40 to +85		-40 to +110	-40 to +85			-40 to +110		°C	With no icing or condensation	
Ambient storage temperature	Tstg	-55 to +125									°C	
Soldering temperature	-	260									°C	10 s

* The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

Item		Symbol	G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	Measurement conditions		
Input	LED forward voltage	Minimum	1.0		1.1	1.0	1.1	1.0	1.1	V	IF=10 mA		
		Typical	1.15		1.27	1.15	1.27	1.15	1.27				
		Maximum	1.3		1.4	1.3	1.4	1.3	1.4				
	Reverse current	IR	Maximum 10									μA	VR=5 V
	Capacitance between terminals	CT	Typical 30									pF	V=0, f=1 MHz
	Trigger LED forward current	IFT (IFC) *2	Typical	0.4	1	0.8	1	-	1	0.8	mA	G3VM-351G1/351G/401G1: Io=100 mA G3VM-351VY/401VY: Io=110 mA G3VM-353G: IOFF=10 μA G3VM-401G: Io=120 mA	
			Maximum	1	3			0.2	3				
Release LED forward current	IFC (IFT) *2	Minimum	0.1			-		0.1		mA	G3VM-351G1/351VY/351G/401G1/401G/401VY: IOFF=100 μA G3VM-353G: Io=120 mA		
		Typical	-	0.4	-	0.001	-	0.5					
Output	Maximum resistance with output ON	Typical	35 (25)		35 (22)	15	18	17	40 (30)	Ω	G3VM-351G1: IF=2 mA, Io=100 mA Values in parentheses are for t < 1 s. G3VM-351G: IF=5 mA, Io=110 mA Values in parentheses are for t < 1 s. G3VM-351VY/401VY: IF=5 mA, Io=110 mA Values in parentheses are for t < 1 s. G3VM-353G: Io=120 mA G3VM-401G1: IF=0.5 mA, Io=100 mA, t < 1 s G3VM-401G: IF=5 mA, Io=120 mA		
		Maximum	50 (35)		25	35		65 (45)					
	Current leakage when the relay is open	I _{LEAK}	Typical	1	-	1	-	1	-	1		nA	
			Maximum	1,000									
Capacitance between terminals	C _{OFF}	Typical	35	30	30	65	70	30	pF	G3VM-351G1/351VY/351G/401G1/401G/401VY: V=0, f=1 MHz G3VM-353G: V=0, f=1 MHz, IF=5 mA			
Capacitance between I/O terminals	Cl-o	Typical	0.8									pF	f=1 MHz, Vs=0 V
Insulation resistance between I/O terminals	Ri-o	Minimum	1000									MΩ	Vi-o=500 VDC, RoH≤60%
		Typical	10 ⁸										
Turn-ON time	ton	Typical	1	0.3	0.5	-	2	0.3	0.5	ms	G3VM-351G1: IF=2 mA, RL=200 Ω, VDD=20 V G3VM-401G1: IF=0.5 mA, RL=200 Ω, VDD=20 V Others: IF=5 mA, RL=200 Ω, VDD=20 V *1		
		Maximum	5	1			10	1					
Turn-OFF time	toff	Typical	1	0.1		-	1	0.1					
		Maximum	3	1	0.5	3	5	1	0.5				

*1. Turn-ON and Turn-OFF Times



*2. These values are for Relays with NC contacts

SOP

G3VM-35□G□/351VY/401G□/401VY

Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.

Item	Symbol		G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	
Load voltage (AC peak/DC)	V _{DD}	Maximum	280				320				V
Operating LED forward current	I _F	Minimum	-	5			-	5			mA
		Typical	2	7.5		-	0.5	7.5			
		Maximum	25								
Continuous load current (AC peak/DC)	I _O	Maximum	80	100	110	120	80	120	110		
Ambient operating temperature	T _a	Minimum	-20								°C
		Maximum	65		100	65			100		

Spacing and Insulation


Item	G3VM-35□G□/401G□	G3VM-351VY/401VY	Unit
	Minimum		
Creepage distances	4.0	5.0	mm
Clearance distances	4.0	5.0	
Internal isolation thickness	0.1	0.2	

SOP


G3VM-35□G□/351VY/401G□/401VY

Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage




G3VM-351VY/401G/401G1/401VY




On-state resistance vs. Ambient temperature




G3VM-351VY/401G/401G1/401VY




Trigger LED forward current vs. Ambient temperature



Turn ON, Turn OFF time vs. LED forward current




G3VM-351VY/401G/401G1/401VY




SOP
G3VM-35□G□/351VY/401G□/401VY

Engineering Data


● **Turn ON, Turn OFF time vs. Ambient temperature**
G3VM-351G/351G1/353G




G3VM-351VY/401G/401G1/401VY




● **Current leakage vs. Ambient temperature**
G3VM-351G/351G1/353G/351VY/401G/401G1



G3VM-401VY



● **Current leakage vs. Load voltage**



SOP


G3VM-35□G□/351VY/401G□/401VY

■ Appearance / Terminal Arrangement / Internal Connections


● Appearance

SOP (Small Outline Package)

SOP 4-pin



Special SOP 4-pin (G3VM-351VY/401VY)




- Note 1:** The actual product is marked differently from the image shown here.
- Note 2:** "G3VM" does not appear in the model number on the Relay.
- Note 3:** The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.


● Terminal Arrangement/Internal Connections (Top View)

G3VM-351G1/G/VY

G3VM-401G1/G/VY




G3VM-353G



■ Dimensions (Unit: mm)


SOP (Small Outline Package)

SOP 4-pin




Surface-mounting Terminals

Weight: 0.1 g




Actual Mounting Pad Dimensions

(Recommended Value, Top View)




Note: The actual product is marked differently from the image shown here.

Special SOP 4-pin * (G3VM-351VY/401VY)




Surface-mounting Terminals

Weight: 0.1 g



Actual Mounting Pad Dimensions

(Recommended Value, Top View)



* The external dimensions are different from those of the standard SOP 4-pin, but the mounting pad dimensions are the same.

Note: The actual product is marked differently from the image shown here.

■ Approved Standards

UL recognized 

Model	Approved Standards	Contact form	File No.
G3VM-351G1 G3VM-351G G3VM-401G G3VM-351VY G3VM-401VY	UL (recognized)	1a (SPST-NO)	E80555
G3VM-353G		1b (SPST-NC)	

Models Certified by BSI for EN/IEC Standards

Model	Approved Standards	Contact form	File No.
G3VM-401G	EN62368-1 (BSI certified)	1a (SPST-NO)	VC669262

SOP

G3VM-35□G□/351VY/401G□/401VY

■Safety Precautions

- Refer to the *Common Precautions for All MOS FET Relays* for precautions that apply to all MOS FET Relays.

SOP

G3VM-35□G□/351VY/401G□/401VY

Please check each region's Terms & Conditions by region website.

OMRON Corporation**Electronic and Mechanical Components Company****Regional Contact****Americas**<https://www.components.omron.com/>**Asia-Pacific**<https://ecb.omron.com.sg/>**Korea**<https://www.omron-ecb.co.kr/>**Europe**<http://components.omron.eu/>**China**<https://www.ecb.omron.com.cn/>**Japan**<https://www.omron.co.jp/ecb/>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

[G3VM-401VY\(TR05\)](#) [G3VM-401VY](#)