




# 2 x 5mm Rectangular *micro*LED® Optopipe™ Optical Light Pipe, 2 Array

# Dialight

## 515-1051



## MicroLED SMT LEDs for use with 515-1051

PART NO.	PAGE #
<b>Recommended</b>	
597-3xx1-2xx	1-21
597-77x1-2xx	1-23 & 1-24
<b>Alternatives</b>	
597-3xx1-5xx	1-30
597-77x1-5xx	1-31

2

LED alternatives may not produce optimum light output  
Solder Pad/Holes layout shown is for single color LEDs listed under "Recommended" category  
Contact factory for other layouts

### Features

- Compatible with Dialight's 515-1054
- High transmissivity polycarbonate material
- UL94V-0 compliance
- ESD protection (circuit isolation from front panel)
- Wide viewing angle
- Arrays reduce insertion costs
- Secures to PCB by press-fit

### LED Data

For absolute maximum ratings and other electrical and optical data on the recommended LEDs, refer to LED data sheets.

### Operating/Storage Temperature

-30°C to +100°C

### Dialight Optopipe Light Pipe Description

This Optopipe™ functions as a through-the-case indicator with the appearance of dual 2 x 5mm rectangular LEDs. It is held to the PCB by 2 press-fit pins. It can utilize either a single or multi-color SMT LED, and can be used to form longer arrays with the 515-1054 light pipe. The light pipe material is water clear transmissive polycarbonate rated UL94-V0, and has a 35% oxygen index.

Dialight can provide custom Optopipe™ solutions for your applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

515-1051F