


**Search**

Home > Products > Fuses > Axial Radial Thru Hole Fuses > TR5 Fuses > 370 > 37001000410

Print

## 37001000410 - 370 Series



Series: 370

[Fuse 370 Datasheet](#)

The 370 Series are TR5®, sub-miniature, fast-acting type, 250V rated fuses, designed in accordance to IEC 60127- 3.

**Features:**

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free

Questions? [Contact Littelfuse Support](#)

**Check Stock**

**Order Samples**

**NEW!**  
Product Selection Guide eCatalog  
[Read Now](#)

**Electronics**  
News and Information  
**SIGN UP NOW**

Feedback

**Electrical Characteristics** | **Technical Resources** | **Environmental Info**

Property (Mouseover for details)	Value
Ampere Rating (A)	0.1
Nominal Melting I <sup>2</sup> T (A <sup>2</sup> sec)	0.0038
Interrupting Rating	35A@250VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	130
Nominal Voltage Drop (mV)	600
Nominal Cold Resistance (Ohms)	4.61
Opening	Fast-Acting (F)
Package Size	TR5 (8.5x8mm)
VAC (V)	250

**Connect with Littelfuse**

Sign up to receive special offers and news

For more details about how we use your information, check our [Privacy Statement](#).



Mobile Site

**About Littelfuse**

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

**Explore Littelfuse**

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

**Technical Resources**

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents