

## 1.SCOPE


HAODA's SAW filter series have broad line up products meeting all broadcast standard including NTSC,PAL and SECAM systems. These filters are composed of two interdigital transducers on a single-crystal. piezoelectrical chip. they are used in electronic equipments such as TV and so on.

## 2.Construction

### 2.1 Dimension and materials


Manufacturer's name : HAODA ELECTRONICS Co. LTD(CHINA)

Type : IF38B4M




0: year(0,1,2,3,4,5,6,7,8,9)

B:product in this quarter(A:1~3,B:4~6,C:7~9,D:10~12)



Components	Materials
1.Outer casing	PPS
2.Substrate	Lithium niobate
3.Base	Epoxy resin
4.Absorber	Epoxy resin
5.Lead	Cu alloy+Au plate
6.Bonding wire	AlSi alloy
7.Electrode	Al

OR



### 3.Characteristics

#### Standard atmospheric conditions

Unless otherwise specified , the standard rang of atmospheric conditions for making measurements and tests is as follows;

- Ambient temperature : 15 to 35
- Relative humidity : 25% to 85%
- Air pressure : 86kPa to 106kPa

#### Operating temperature rang

Operating temperature rang is the rang of ambient temperatures in which the filter can be

operated continuously. -10 ~ +60

#### Storage temperature rang

Storage temperature rang is the rang of ambient temperatures at which the filter can be stored

without damage.

Conditions are as specified elsewhere in these specifications. -40 ~ +70

Reference temperature +25

#### 3.1 Maximum Rating

DC voltage	VDC	12	V	Between any terminals
AC voltage	Vpp	10	V	Between any terminals

**3.2 Electrical Characteristics**Source impedance  $Z_s=50$ Load impedance  $Z_L=50$  $T_A=25$ 

Items	Freq	Min	typ	max	
Insertion attenuation Reference level	36.00MHz	-	22.0	-	dB
Relative attenuation	38.00MHz	3.6	5.1	6.6	dB
	33.57MHz		0.0	1.0	dB
	32.50MHz	14.5	16.5	18.5	dB
	31.50MHz	14.5	16.5	-	dB
	30.00MHz	40.0	52.0		dB
	39.50MHz	39.0	50.0		dB
Sidelobe	25.00~30.00MHz	34.0	41.0		dB
	39.50~45.00MHz	31.0	38.0		dB
Temperature coefficient		-72			Ppm/k

**3.3 Environmental Performance Characteristics**

Item Test condition	Allowable change of absolute Level at center frequency(dB)
High temperature test 70 1000H	< 1.0
Low temperature test -40 1000H	< 1.0
Humidity test 40 90-95% 1000H	< 1.0
Thermal shock -20 ==25 ==80 20 cycle 30M 10M 30M	< 1.0
Solder temperature test Sold temp.260 for 10 sec.	< 1.0
Soldering Immerse the pins melt solder at 260 +5/-0 for 5 sec.	More then 95% of total area of the pins should be covered with solder


**3.4 Mechanical Test**

Item Test condition	Allowable change of absolute Level at center frequency(dB)
Vibration test 600-3300rpm amplitude 1.5mm 3 directions 2 H each	<1.0
Drop test On maple plate from 1 m high 3 times	<1.0
Lead pull test	<1.0

SHOULDER ELECTRONICS LIMITED

Pull with 1 kg force for 30 seconds	
Lead bend test 90° bending with 500g weigh 2 times	<1.0

**3.5 Voltage Discharge Test**

Item Test condition	Allowable change of absolute Level at center frequency(dB)
Surge test Between any two electrode 	<1.0