

## DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, deep drawn, high profile, unperforated, 1.5 mm thick, material: aluminum, height 15 mm, width 35 mm, length 2000 mm


The illustration shows version NS 35/15-AL without holes with captive slide nut GLM 4

### Why buy this product

- The slide nuts even enable components without an additional snap-on foot to be mounted
- The NS 35/15 AL DIN rail is designed to accommodate GLM ... slide nuts



### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 017477
Weight per Piece (excluding packing)	680.0 g
Custom tariff number	76042990
Country of origin	Germany

### Technical data

#### Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm

#### General

Material	Aluminum
Coating	uncoated
Color	silver
Test standard	Similar to EN 60715: 2001
Nominal current $I_N$	8400 A

# DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756

## Technical data

### Standards and Regulations

Test standard	Similar to EN 60715: 2001
Connection in acc. with standard	IEC / EN

## Classifications

### eCl@ss

eCl@ss 4.0	23150301
eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27141143
eCl@ss 7.0	27141143
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

## Drawings

Dimensional drawing

