



Number	Description
1	Fuse element
2	Ceramic body
3	Transparent cover

Fusing time ISO 8820-6 [s]		
Load [%]	Minimum [s]	Maximum [s]
100 %	360,000	-
135 %	5	1,800
150 %	1	600
200 %	0.2	60
350 %	0.03	1
600 %	0.01	0.2

Note: mounting torque in test fixture  
12 Nm ± 1

Rating [ A ]	Volt [ V ]	iMaXX Reference
30	58	CF030
50	58	CF050
75	58	CF075
100	58	CF100
125	58	CF125
150	58	CF150
175	58	CF175
200	58	CF200
250	58	CF250
300	58	CF300

Note: Amperage rating and production date (WWYY) stamped on metal part

Revisions			Date	Appr.	
	Date	Type	Drawn	06/12	GRH
a	10/14	Added CF030	Checked	03/16	BE
b	06/15	Added trace code info	Standards		
c	03/16	Corrected ISO fusing time	Approved	03/16	AdH
			Scale	not to scale	Title
			Projection	Tolerance ± 0.2 mm unless otherwise noted	Drawing type
					Drawing number
					Sheet
					Layers / Sheet

