

## FEATURES

- Conforms to the latest requirements of British and European standards.
- Cable gland design provides external clamping
- Lockable protection window on all variants to enhance safety
- Screw terminals accept conductors up to 2.5mm<sup>2</sup> for 16A, 6mm<sup>2</sup> for 32A, 16mm<sup>2</sup> for 63A and 50mm<sup>2</sup> for 125A types
- IP67 and IP66 rated
- Red, blue and yellow colours offered in this range of power connectors
- Voltage ratings of 110V, 230V and 415V offered in this range
- Halogen free

## RS PRO IP66, IP67 Red Cable Mount 3P+N+E Industrial Power Socket, Rated At 63.0A, 415.0 V

RS Stock No.: 724-9164



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From the trusted brand RS PRO, comes a range of high-quality cable mounted free socket power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

## General Specifications

<b>Pole Format</b>	3P+N+E
<b>Hour Position</b>	6h
<b>Gender</b>	Female
<b>Body Orientation</b>	Straight
<b>Material</b>	Engineering Plastic
<b>Colour</b>	Red
<b>Applications</b>	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

## Electrical Specifications

<b>Current Rating</b>	63A
<b>Voltage Rating</b>	415V
<b>Working Frequency</b>	50Hz, 60Hz
<b>Plug/Socket</b>	Socket
<b>Termination Method</b>	Screw
<b>Cable CSA</b>	16mm <sup>2</sup>

## Operation Environment Specifications

Maximum Operating Temperature	40°C
Minimum Operating Temperature	-25°C

## Mechanical Specifications

Mounting Type	Cable Mount
---------------	-------------

## Protection Category

IP Rating	IP66, IP67
-----------	------------

## Approvals

Compliance/Certifications	EN 60309-1, EN 60309-2
---------------------------	------------------------



