







ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			VEE	18-08-10	JAG	30-08-10	XXX	01-09-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



Electrical Characteristics:
 Rated current: UL/VEDE to 250 VAC-10 Amp
 DPST Power Switch: UL/CSA to 250 VAC-10 Amp
 Voltage Selector Card: VDE to 250 VAC-10 Amp
 100-120VAC or 200-240 VAC Input Voltage
 UL/CSA/VEDE to 250-10 Amp

Double 5 X 20 Fuseholder
 Solder Tab Terminals
 Flammability Class UL94V-0
 Plastic Case
 Screw Mount Type

Part Number Table

Description	Part Number
Panel Mount Fuseholder	2171

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

DRAWING TITLE:

Panel Mount Fuseholder

DRAWN BY:	DATE:
VEE	18-08-10
CHECKED BY:	DATE:
JAG	30-08-10
APPROVED BY:	DATE:
XXX	01-09-10

SIZE	DWG. NO.	ELECTRONIC FILE
A	XXX	92N5195
SCALE:	NTS	U.O.M.: Millimeters
SHEET:	1	OF 1

REV

92N5195

A