


S75CS010 Datasheet

Technical Specifications



S75CS010

Conical Sharp 1.00mm (0.04")

Tip Style: Conical Sharp


Tip Width: 1.00mm (0.04")

Tip Length: 15.40mm (0.61")

| | |
|--|--|
| 75 Type Cartridge ¹ : | 350°C - 398°C |
| RoHS Compliant ² / Lead Free: | YES |
| Equivalent to: | SSC-701A |
| For Use With: | TMT-2000PS, SP200, MFR-PS1100, MFR-PS2200 (SSC Tips) |

Material Composition

Patented Color Band



All components are RoHS compliant and Lead-Free.

¹ Thermaltronics tip cartridges will typically idle within a temperature range of +/-1.1°C. However, there is variation in idle temperature across tip geometries within an individual temperature series. Thermaltronics offers a wide variety of tip geometries from 0.25mm fine point tip to 5mm chisel. The length and geometry of a tip will have an influence on the tip idle temperature. To accurately measure idle temperature it will depend greatly on the measurement method, technique and equipment used. Two different methods or the use of alternative equipment will produce different test results.

² Please refer to <http://www.rohs.gov.uk> for details on RoHS Compliance.