




DIMENSIONS




PCB LAYOUT



GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000A

TERMINATION



ORDERING INFORMATION

SERIES	8609	3	4	8	7	3	13	7	4	5	ELF
ROWS FITTED WITH CONTACTS											
ROW a	-	-	-	-	-	-	-	-	-	-	16
ROW b	a	b	c	-	-	-	-	-	-	-	48
ROW c	a	b	c	-	-	-	-	-	-	-	32
NO. OF CONTACTS											
TYPE OF INSULATOR											
3 ROW MALE INSULATOR											7
METHOD OF MOUNTING											
STANDARD MOUNTING - STYLE C/2											3
TERMINATION											
ANGLED SPILL											13
OPTIONS											
NO. OPTION											7
WITH HARPOONS											H
PERFORMANCE CLASS											
DIN 41612 CLASS 3											4
DIN 41612 CLASS 2											5
DIN 41612 CLASS 1											6
AS PER MIL C 55302 / JSS 50808											8
PITCH PER ROW											
2.54 mm											5
LEAD FREE VERSION											ELF

mat'l. code	SEE DWG C-8609-0000A	surface	ISO 1302	tolerance	ISO 406 ISO 1101	projection	product family	8609
itr	ecn no dr	date	tolerances unless otherwise specified	angles	linear	mm	title	DIN STANDARD HEADER DIN 41612 STYLE C/2
H	ELX-I-40953	MJA	2021-05-19	0.X ±0.1	0.XX ±0.1	0.XXX ±0.1	dwg no	sheet 1 of 1 size
C	I05-0089	MINI	2005-05-19	0*±2*	2004-09-17	2004-09-17	C-8609-2003	A3
D	I06-0061	MINI	2006-05-31	dr	MINI K V	2004-09-17	Amphenol FCI	Customer Drawing
E	I08-0146	KR	2008-10-21	engr	RAKHEE G	2004-09-17		
F	I09-0217	KR	2009-10-13	chr	M JACOB	2021-05-19		
G	I10-0020	KR	2010-01-13	appd	SANOJ	2021-05-19		
sheet index	revision	H						
1	1							