

Honeywell Sensing and Control



Search



narrow your search

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9676)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9237)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

Need Help?

Click here to contact us

V7-1C17D8-022 Premium V-Basic Switches

(Home : Products)



Actual product appearance may vary.

V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 15 A at 277 Vac, Straight Lever Actuator, 0,80 N [2.9 oz] Maximum Operating Force, Silver Contacts, Quick Connect Termination

Sales & Service

Distributor Inventory

Overview Specs Documentation Application Notes

Product Specifications

Switch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Straight Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 82 °C [-40 °F to 180 °F]
Voltage	277 Vac
Actuator Length	35,6 mm [1.41 in]
Contact Type	Silver
Operating Force (OF)	0,80 N [2.82 oz] max.
Release Force	0,08 N [0.28 oz] min.
Pretravel (PT)	2,79 mm [0.110 in] max.
Overtravel (OT)	2,29 mm [0.090 in] min.
Differential Travel (DT)	0,75 mm [0.030 in] max.
Operating Position (OP)	15,2 mm ±1,524 mm [0.600 ±0.060 in]
Housing Material	PCT Polyester Thermoplastic
High Temperature	85 °C [185 °F]
Agency Approvals and Standards	UL, CSA
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	V7