

Specification Sheet

Part Number: 596-00857

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure

Aggressive adhesive ensures strong bond, even on powder coated surfaces

Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability

Optional Paint Shields provide additional protection for pre-printed and variable data placards



Article Number	596-00857
Type	ACDISCTM5ENG
Color	Black (BK)
Quantity Per	pack

Product Description

Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, HellermannTyton offers two styles of variable placards: hand-writable and engravable. Both hand-writable placards feature a silver variable data area that can be marked using an industrial paint pen. Engravable placards have a black area that can be engraved using standard engraving equipment.

Short Description	Metal Solar Placard, Engravable, PHOTOVOLTAIC AC DISCONNECT, 3.75"x1.0", AA, Black, 5/pkg
Global Part Name	ACDISCTM5ENG-AA-BK
Technical Description	3.75" X 1" Black text on aluminum background that reads as: "PHOTOVOLTAIC AC DISCONNECT." - 10 per pack. Nameplate can be used with standard engraving equipment to add variable data.
Local Order Number 2	Cross Reference = Paint Shield: 596-00796
Length L (Imperial)	3.75
Length L (Metric)	95.25
Width W (Imperial)	3.75
Width W (Metric)	92.25
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive

Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014 NEC2017
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	7616995195
Labels per Column	1
Labels per Row	1