

Specification Sheet

Part Number: 596-00842

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.

Aggressive adhesive ensures strong bond, even on powder coated surfaces.

Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.

PHOTOVOLTAIC

DC DISCONNECT

Optional Paint Shields provide additional protection for pre-printed and variable data placards.

Metal Solar Placard, Hand Writable, PV DC DISCONNECT, 3.75" x 1.0", AA, Black, 5/pkg

Article Number	596-00842
Type	DCDISCTM5
Color	Black (BK)
Quantity Per	pack

Product Description

Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, hand-writable placards are designed to meet industry codes. Hand-writable placards feature a silver variable data area that can be marked using an industrial paint pen.

Short Description	Metal Solar Placard, Hand Writable, PV DC DISCONNECT, 3.75" x 1.0", AA, Black, 5/pkg
Global Part Name	DCDISCTM5-AA-BK
Technical Description	3.75" X 1" Silver aluminum text on black background that reads as: "PHOTOVOLTAIC DC DISCONNECT." - 10 per pack. Nameplate is also printable using a paint pen to add variable voltage information on demand.
Local Order Number 2	Cross Reference = Paint Shield: 596-00796
Length L (Imperial)	3.75
Length L (Metric)	95.25
Width W (Imperial)	3.75
Width W (Metric)	95.25
Height H (Imperial)	1.00
Height H (Metric)	25.40
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive

Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 NEC2014
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	7616995195
Labels per Column	1
Labels per Row	1