



**Table of Contents**

**Z-PACK HS3 Connector** . . . . . 95-136

  Product Line Overview . . . . . 96-98

  Part Number Selection Chart . . . . . 99, 100

  6 Row Connectors . . . . . 101-112

  10 Row Connectors . . . . . 113-126

  Coding Keys (10 Row Only) . . . . . 127


  Power and Guide Hardware . . . . . 127-133

  Mating Sequence Chart . . . . . 134

  Application Tooling and Equipment . . . . . 135

**4**

Z-PACK HS3 Connector



## Z-PACK HS3 Connector (Continued)

### Product Line Overview

#### Product Facts


- High speed, high density two piece board-to-board backplane connector
- Dual beam provides redundant contact for improved reliability
- For data rates of 6.2+ Gb/s
- 10 row, 100 high speed lines per 25.00 [.984]
- 6 row, 60 high speed lines per 25.00 [.984]
- Controlled impedance: 50 ohm Single Ended 100 ohm Differential
- Feedthrough versions for midplane applications
- 250 mating cycles
- End stackable on 2.50 [.098] centerline, signal pin to signal pin
- Advanced ESD/Power (10 Amps) using optional guide pins and power contacts

#### Applications

- High Speed Telecommunications Equipment
- Mid-range and high-end services
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476



IGES is a trademark of IAMBA Networks, Inc.  
PRO/E is a trademark of Parametric Technology Corp.



The emergence of high speed serial backplanes has forced interconnections to be able to transfer data at gigabit speeds.

The Z-PACK HS3 connector system has been specifically designed to support this generation of high speed serial data transfer. Tyco Electronics has incorporated a controlled impedance microstrip path through the connector to minimize signal degradation and

crosstalk. Compliant pins are used on both daughter-card and backplane.

This connector family is press fit and is compatible with other Z-PACK HM family connectors on the same board edge. Z-PACK HS3 connectors support data rates of 6.2+ Gb/s per differential pair. The 6 row version is optimized for 20.32mm or 0.8 inch card centerline applications, while the 10 row version is

optimized for high density for 25.4mm or 1.0 inch card centerline applications.

The Tyco Electronics Universal Power Module (UPM) is designed to be compatible with the Z-PACK HS3 connector.

Static Discharge Guide/ Power Pins, Guide Pin/ Power Receptacles, Universal Guide Pin and Receptacles, and Coding Keys (10 row only) are also available.

#### Availability

Fully validated SPICE models: E-mail requests to [modeling@tycoelectronics.com](mailto:modeling@tycoelectronics.com)

Samples: go to <http://tycoelectronics.custhelp.com>

Pro/E models and IGES models: E-mail requests to [Tycocad@tycoelectronics.com](mailto:Tycocad@tycoelectronics.com)

White Papers: available on product website at <http://hs3.tycoelectronics.com>

Electrical Performance Report: <http://hs3.tycoelectronics.com>

6 row EPR #138505; 10 row EPR #138506

Routing Guide: <http://hs3.tycoelectronics.com>

Routing Guide #20GC017

<http://hs3.tycoelectronics.com>

#### Technical Documents

##### Product Specification

108-1957

##### Application Specification

114-13020

##### Qualification Test Report

501-501

#### Material and Finish

**Contact Area Finish** — 0.80µm Au min. over 1.3µm Ni min.

**Compliant Pin Finish** — 0.8µm SnPb min. over 1.3µm Ni min.

**Contact** — Copper Alloy

**Housing** — Glass filled polyester, 94V-0 rated

#### Ratings

**Current** — 1.15A per fully energized

**Operating Voltage** — 250 VAC max.

**Temperature** — -65°C to 105°C

**Mating Force** — 0.75N max. per contact (signal = 1 contact, ground = 1 contact)

**Durability** — 250 cycles

\* Reference Product Spec. 108-1957 for complete list of performance data.



**Z-PACK HS3 Connector (Continued)**

**Performance Specifications**

**Electrical Characteristics**

**Characteristic Impedance** —

100 ± 10% Ohms

**Nominal Resistance** — 21 mOhm

**Crosstalk** — See table at right

**Insertion Loss** — See chart below

**Asynchronous Diff. NEXT (%)**

Edge rate 20-80%	HS3 10-Row Measured Noise Totals			
	50 ps	100 ps	150 ps	250 ps
BC Pair Total NEXT	2.3%	1.9%	1.7%	1.3%
DE Pair Total NEXT	4.0%	3.3%	3.0%	2.4%
FG Pair Total NEXT	4.0%	3.4%	3.1%	2.7%
HJ Pair Total NEXT	2.3%	1.9%	1.7%	1.5%



**Synchronous Diff. NEXT (%)**

Edge rate 20-80%	HS3 10-Row Measured Noise Totals			
	50 ps	100 ps	150 ps	250 ps
BC Pair Total FEXT	0.5%	0.3%	0.3%	0.2%
DE Pair Total FEXT	1.5%	0.8%	0.5%	0.5%
FG Pair Total FEXT	1.4%	0.8%	0.7%	0.5%
HJ Pair Total FEXT	1.0%	0.6%	0.4%	0.3%

Edge rates specified are at the connector.

Noise includes 1.60 [.063] footprints on both sides of the connector.


Totals include contributions from 8 adjacent aggressor pairs.



**PRBS 2<sup>7</sup>-1 data pattern**  
**10 Gb/s data rate**  
**BC Pair**  
**64% Eye Opening**  
**12.6ps Jitter**

**4**

Z-PACK HS3 Connector



Calibrated to include only the connector and the 1.60 [.063] footprints on both sides of the connector.

**Note:** All part numbers are RoHS compliant.

Catalog 1773095  
 Revised 12-08


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
 Canada: 1-905-470-4425  
 Mexico: 01-800-733-8926  
 C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
 Hong Kong: 852-2735-1628  
 Japan: 81-44-844-8013  
 UK: 44-8706-080-208





**Z-PACK HS3 Connector (Continued)**

**Z-PACK HS3 Connector: Printed Circuit Design Rules for Backplane Routing**

**Using Standard Commercial Design Rules**

This table lists routing specifications which meet design rules practiced by most printed circuit board vendors. This table should be used to route the Z-PACK HS3 connector for most applications and especially under one or more of these considerations:

1. Edge rates require the widest conductors possible.
2. Backplanes having layer counts above 16.
3. Backplanes which exceed 508mm (20") in length or width.
4. Cost is a major factor.

Finished Hole Dia.	Drilled Hole Dia.	Pad Dia.	Annular Ring	Pad-Pad Spacing 63 mils (1.58mm) C/C	Conductor Routing Options	
					5 mil spacing	6 mil spacing
24 mils 0.6mm	28 mils 0.7mm	44 mils 1.1mm	2 mils 0.05mm	19 mils 0.475mm	9 mils 0.225mm	7 mils 0.175mm
24 mils 0.6mm	28 mils 0.7mm	42 mils 1.05mm	1 mil 0.025mm	21 mils 0.525mm	11 mils 0.275mm	9 mils 0.225mm
24 mils 0.6mm	28 mils 0.7mm	40 mils 1.0mm	tangency tangency	23 mils 0.575mm	13 mils 0.325mm	11 mils 0.275mm

**Commercial Design Rules:**

Minimum pad diameter for tangency: Drill Diameter (D)+12 mils (0.3mm)  
 Hole location tolerance: +/- 3 mils (0.075mm)  
 Pad/Pad artwork tolerance: +/- 2 mils (0.05mm)  
 Feature tolerance (1 oz foil): +/- 0.075 mils (0.0175mm)

**Using Advanced Design Rules**

This table lists routing specifications which can be built by a limited number of leading edge printed circuit vendors using advanced design rules. This table can be used as a reference for Z-PACK HS3 connector in backplane applications where very high density is a major factor. The PCB vendor should be consulted regarding applicability of these rules to a specific design. Consideration should be given to the following:

1. Signal layer count reduction is possible with these design rules.
2. Backplanes which exceed 508mm (20") in length or width generally cannot be built with these rules.
3. Cost factors can potentially be higher.


Finished Hole Dia.	Drilled Hole Dia.	Pad Dia.	Annular Ring	Pad-Pad Spacing 63 mil (1.58mm) C/C	Conductor Routing Options	
					5 mil spacing	6 mil spacing
24 mils 0.6mm	28 mils 0.7mm	38 mils 0.95mm	tangency tangency	25 mils 0.625mm	15 mils 0.35mm	13 mils 0.3mm
<b>Two Conductor Routing</b>						
24 mils 0.6mm	28 mils 0.7mm	42 mils 1.05mm	2 mils 0.05mm	21 mils 0.525mm	4.5 mil lines/4 mil spacing 0.11mm lines/0.09mm spacing	
24 mils 0.6mm	28 mils 0.7mm	40 mils 1.0mm	1 mil 0.025mm	23 mils 0.575mm	5.5 mil lines/4 mil spacing 0.125mm lines/0.1mm spacing	

**Advanced Design Rules:**

Minimum pad diameter for tangency: Drill Diameter (D)+10 mils (0.25mm)  
 Hole location tolerance: +/- 2 mils (0.05mm)  
 Pad/Pad artwork tolerance: +/- 2 mils (0.05mm)  
 Feature tolerance (1 oz foil): +/- 0.075 mils (0.0175mm)

**Z-PACK HS3 Connector Routing Pattern**


For more details request Report #20GC004-1 or visit [http://www.tycoelectronics.com/products/simulation/files/papers/20GC004\\_1.pdf](http://www.tycoelectronics.com/products/simulation/files/papers/20GC004_1.pdf)





**Z-PACK HS3 Connector (Continued)**


**Part Number Selection Chart  
10 Row Z-PACK HS3 Connector**



**Part Number 5120874**  
50 Position  
Right Receptacle  
Univ Pwr Guide Pin




**Part Number 5120670**  
50 Position  
Right Header  
Univ Pwr Guide Pin




**Part Number 5120665**  
50 Position  
Right Header  
ESD/HDI Guide Pin




**Part Number 5120667**  
50 Position  
Right Feed-Through  
ESD/HDI Guide Pin




**Part Number 5120792**  
50 Position  
Right Receptacle  
ESD/HDI Guide Pin




**Part Number 5120661**  
50 Position  
Right Header  
ESD/HDI Guide Pin




**Part Number 5120662**  
50 Position  
Left Receptacle  
ESD/HDI Guide Pin




**Part Number 5120666**  
50 Position  
Left Header  
ESD/HDI Guide Pin




**Part Number 5120790**  
100 Position  
Center Receptacle




**Part Number 5120658**  
100 Position  
Center Header



**Part Number 5120664**  
100 Position  
Center Feed-Through



**Part Number 5120663**  
100 Position  
Center Shroud



**Part Number 5120791**  
50 Position  
Center Receptacle




**Part Number 5120747**  
50 Position  
Center Header




**Part Number 5120748**  
50 Position  
Center Feed-Through




**Part Number 5120750**  
50 Position  
Center Shroud



**Part Number 5120793**  
50 Position  
Left Receptacle  
ESD/HDI Guide Pin




**Part Number 5120662**  
50 Position  
Left Header  
ESD/HDI Guide Pin




**Part Number 5120666**  
50 Position  
Left Feed-Through  
ESD/HDI Guide Pin



**Part Number 5120668**  
50 Position  
Left Shroud  
ESD/HDI Guide Pin




**Part Number 5120875**  
50 Position  
Left Receptacle  
Univ Pwr Guide Pin



**Part Number 5120672**  
50 Position  
Left Header  
Univ Pwr Guide Pin

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.









**4**  
Z-PACK HS3 Connector





**Z-PACK HS3 Connector** (Continued)

**Part Number Selection Chart**  
**6 Row Z-PACK HS3 Connector**








**Part Number 5120788**  
30 Position  
Right Receptacle

**Part Number 5120677**  
30 Position  
Right Header

**Part Number 5120680**  
30 Position  
Right Header  
Feed-Through

**Part Number 5120683**  
30 Position  
Right Shroud

**Part Number 120949-1**  
60 Position  
Receptacle  
with Guide Module






**Part Number 5120786**  
60 Position  
Center Receptacle

**Part Number 5120674**  
60 Position  
Center Header

**Part Number 5120679**  
60 Position  
Center Header  
Feed-Through

**Part Number 5120682**  
60 Position  
Center Shroud

**Part Number 120948-1**  
90 Position  
Receptacle




**Part Number 5120787**  
30 Position  
Center Receptacle

**Part Number 5120732**  
30 Position  
Center Header

**Part Number 5120742**  
30 Position  
Center Header  
Feed-Through

**Part Number 5120743**  
30 Position  
Center Shroud



**Part Number 5120789**  
30 Position  
Left Receptacle

**Part Number 5120678**  
30 Position  
Left Header

**Part Number 5120681**  
30 Position  
Left Header  
Feed-Through


**Part Number 5120684**  
30 Position  
Left Shroud

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle  
6 Row, Left Module (ac-  
cepts ESD Guide Pin)**



**4**  
Z-PACK HS3 Connector

**Pin Header Assemblies**


Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
30	5120789-1	1338742-1	408-8394	1338744-1	408-8393	1338745-1	408-8410

**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.




**Recommended PC Board Layout  
(Component Side Shown)**



**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**  
(Continued)  
**6 Row, Center Module**



**Pin Header Assemblies**


Number of Positions	Dimensions			Part Number	Application Tooling					
	A	B	C		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
60	24.88 .980	22.50 .886	25.40 1.00	5120786-1	1338742-2	408-8394	1338744-1	408-8393	1338745-1	408-8410
30	12.38 .487	10.00 .394	12.90 .508	5120787-1	1338742-1	408-8394	1338744-1	408-8393	1338745-1	408-8410

**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Recommended PC Board Layout (Component Side Shown)**





K

**Tyco Electronics** High Speed Backplane Connectors

**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**  
(Continued)  
**6 Row, Right Module**  
(accepts ESD Guide Pin)

Technical drawings of the Z-PACK HS3 Connector showing side and front views with dimensions in millimeters and inches. Dimensions include: 13.18 ± 0.20 / [.518 ± .000], 21.67 / [.853], 1.00 Typ. / [.039], 12.00 / [.472], 14.10 / [.555], 1.50 Typ. / [.059], 1.00 Typ. / [.039], 2.00 Typ. / [.078], 10.80 Typ. / [.425], 4.05 Typ. / [.159], 21.57 / [.849], 10.00 / [.393], 5.75 / [.226], 2.50 Typ. / [.098], 2.00 Typ. / [.078], 1.50 Typ. / [.059], 4.58 / [.180], 2.00 / [.078], 1.81 / [.072], 9.81 / [.386], 1.50 Typ. / [.059], 4.58 / [.180], 2.00 / [.078]. Distance From Row "a" to Board Surface. Location Ref. 1, 2, 3, 4, 5, a, b, c, d, e.

**4**  
Z-PACK HS3 Connector

**Pin Header Assemblies**

Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
30	5120788-1	1338742-1	408-8394	1338744-1	408-8393	1338745-1	408-8410

**P.C.B. Hole Dimensions**

**Drilled Hole** — 0.7±0.025mm

**Fin. Hole** — 0.55 to 0.65mm

**Cu-thickness** — 0.025 to 0.050mm

**SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

Recommended PC Board Layout (Component Side Shown) diagram with dimensions: 15.75 / [.620], 10.00 Typ. / [.394], 2.50 Typ. / [.098], 1.25 Typ. / [.049], Ø 2.50 [.098] Finished Size Optional Power Contact P/N 535875-x, 5.50 / [.217], 1.00 Typ. / [.039], 3.50 Typ. / [.138], 7.00 Typ. / [.276], 2.00 Ref. / [.079]. Location Ref. 1, 5, f, e, d, c, b, a.

**Recommended PC Board Layout (Component Side Shown)**

Catalog 1773095  
Revised 12-08

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208


103

Black ID: GARRYV

Downloaded from [Arrow.com](http://Arrow.com)

**Z-PACK HS3 Connector (Continued)**

**Vertical Receptacle  
6 Row, 90 Position**



Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
90	120948-1	1725624-1	408-8870	—	—	—	—

**P.C.B. Hole Dimensions**

**Drilled Hole** — 0.7±0.025mm


**Fin. Hole** — 0.55 to 0.65mm

**Cu-thickness** — 0.025 to 0.050mm

**SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.




**Recommended PC Board Layout  
(Component Side Shown)**



**Z-PACK HS3 Connector (Continued)**

**Vertical Receptacle**  
(Continued)  
**6 Row, 60 Position, with Guide Module**



**4**  
Z-PACK HS3 Connector


Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
60	120949-1	1725623-1	408-8870	—	—	—	—

**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Recommended PC Board Layout (Component Side Shown)**

K

**Tyco Electronics** High Speed Backplane Connectors

**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Assemblies**  
**6 Row, Left Module (accepts ESD Guide Pin)**

**P.C.B. Hole Dimensions**

**Drilled Hole** — 0.7±0.025mm  
**Fin. Hole** — 0.55 to 0.65mm  
**Cu-thickness** — 0.025 to 0.050mm  
**SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Pin Header Assemblies**

Number of Positions	Dimensions					Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D	E			Seating	IS Sheet	Signal Pin		Ground Blade	
										Repair Kit	IS Sheet	Repair Kit	IS Sheet
30	13.70 .539	10.00 .393	14.80 .583	8.20 .322	3.70 .145	<b>A</b>	5120678-1	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	13.70 .539	10.00 .393	14.80 .583	9.70 .381	3.70 .145	<b>B</b>	5120678-2	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	13.70 .539	10.00 .393	14.80 .583	8.20 .322	13.00 .511	<b>K</b>	5120681-1	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	13.70 .539	10.00 .393	14.80 .583	9.70 .381	14.50 .570	<b>P</b>	5120681-2	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573

**5120678-1 Shown**

Dimensions: 7.00 Typ. [0.276], 3.50 Typ. [0.138], 1.00 Typ. [0.039], 2.50 Typ. [0.098], 10.00 Typ. [0.394], 5.75 [0.226], 1.25 Typ. [0.049], 2.00 Ref. [0.079], 6.42 [0.253].

Pin locations: a, b, c, d, e.

Optional Power Contact P/N 535875-x

**K Pin**  
**P Pin**  
**A Pin**  
**B Pin**

Action Pin Area, Contact Area, Ref. Line, Seating Plane Connector.

**Recommended PC Board Layout (Component Side Shown)**  
**For Non-Midplane Applications**  
**For Midplane Applications Reference Page 112**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

106

Catalog 1773095  
 Revised 12-08  
 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
 Canada: 1-905-470-4425  
 Mexico: 01-800-733-8926  
 C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
 Hong Kong: 852-2735-1628  
 Japan: 81-44-844-8013  
 UK: 44-8706-080-208

Black ID: GARRY7

Downloaded from Arrow.com

**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Assemblies (Continued)**  
**6 Row, Center Module**

**P.C.B. Hole Dimensions**


**Drilled Hole** — 0.7±0.025mm

**Fin. Hole** — 0.55 to 0.65mm

**Cu-thickness** — 0.025 to 0.050mm

**SnPb-thickness** — 0.004 to 0.010mm


**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**Pin Header Assemblies**

Number of Positions	Dimensions					Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D	E			Seating	IS Sheet	Signal Pin		Ground Blade	
										Repair Kit	IS Sheet	Repair Kit	IS Sheet
60	24.90 .980	22.50 .885	24.90 .980	8.20 .322	3.70 .145	<b>A</b>	5120674-1	91313-2	408-4546	354687-2	408-9979	1320534-1	408-4573
	24.90 .980	22.50 .885	24.90 .980	9.70 .381	3.70 .145	<b>B</b>	5120674-2	91313-2	408-4546	354687-2	408-9979	1320534-1	408-4573
	24.90 .980	22.50 .885	24.90 .980	8.20 .322	13.00 .511	<b>K</b>	5120679-1	91313-2	408-4546	354687-2	408-9979	1320534-1	408-4573
	24.90 .980	22.50 .885	24.90 .980	9.70 .381	14.50 .570	<b>P</b>	5120679-2	91313-2	408-4546	354687-2	408-9979	1320534-1	408-4573
30	12.41 .488	10.00 .393	12.40 .488	8.20 .322	3.70 .145	<b>A</b>	5120732-1	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	12.41 .488	10.00 .393	12.40 .488	9.70 .381	3.70 .145	<b>B</b>	5120732-2	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	12.41 .488	10.00 .393	12.40 .488	8.20 .322	13.00 .511	<b>K</b>	5120742-1	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	12.41 .488	10.00 .393	12.40 .488	9.70 .381	14.50 .570	<b>P</b>	5120742-2	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573

**4**  
Z-PACK HS3 Connector




**Recommended PC Board Layout (Component Side Shown)**  
**For Non-Midplane Applications**  
**For Midplane Applications Reference Page 112**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Z-PACK HS3 Connector (Continued)**


**Vertical Pin Header Assemblies (Continued)**  
**6 Row, Right Module (accepts ESD Guide Pin)**



**P.C.B. Hole Dimensions**


- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.





**Pin Header Assemblies**

Number of Positions	Dimensions				Pin Ref.	Part Numbers	Application Tooling					
	A	B	D	E			Seating	IS Sheet	Signal Pin		Ground Blade	
									Repair Kit	IS Sheet	Repair Kit	IS Sheet
30	14.45 .568	10.00 .393	8.20 .322	3.70 .145	<b>A</b>	5120677-1	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	14.45 .568	10.00 .393	9.70 .381	3.70 .145	<b>B</b>	5120677-2	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	14.45 .568	10.00 .393	8.20 .322	13.00 .511	<b>K</b>	5120680-1	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573
	14.45 .568	10.00 .393	9.70 .381	14.50 .570	<b>P</b>	5120680-2	91313-1	408-4546	354687-2	408-9979	1320534-1	408-4573



**Recommended PC Board Layout (Component Side Shown) For Non-Midplane Applications**  
 For Midplane Applications Reference Page 112





**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.





**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Shrouds  
6 Row, Left Module**




**P.C.B. Hole Dimensions**

**Drilled Hole** — 0.7±0.025mm

**Fin. Hole** — 0.55 to 0.65mm

**Cu-thickness** — 0.025 to 0.050mm

**SnPb-thickness** — 0.004 to 0.010mm




**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**4**


Z-PACK HS3 Connector

**Pin Header Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling			
	A	B	C		Insertion	IS Sheet	Ground Blade	
							Repair Kit	IS Sheet
30	13.70 .537	10.00 .393	14.80 .582	5120684-1	91313-1	408-4546	1320534-1	408-4573



**Non-Coplanar Daughtercards**  
(Pin 1a Header = Pin 1f Shroud Side)  
Recommended PC Board Layout — Reference Page 112  
(Shroud Side Shown)



**Coplanar Daughtercards**  
(Pin 1a Header = Pin 5a Shroud Side)  
Recommended PC Board Layout — Reference Page 112  
(Shroud Side Shown)

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

Catalog 1773095  
Revised 12-08

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803


South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208





**Z-PACK HS3 Connector (Continued)**


**Vertical Pin Header Shrouds (Continued)  
6 Row, Center Module**



**P.C.B. Hole Dimensions**


- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.




**Pin Header Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling			
	A	B	C		Insertion	IS Sheet	Ground Blade	
							Repair Kit	IS Sheet
60	24.90 .980	22.50 .885	24.90 .980	5120682-1	91313-2	408-4546	1320534-1	408-4573
30	12.57 .494	10.00 .393	12.40 .488	5120743-1	91313-1	408-4546	1320534-1	408-4573



**Non-Coplanar Daughtercards**  
(Pin 1a Header = Pin 1f Shroud Side)  
Recommended PC Board Layout — Reference Page 112  
(Shroud Side Shown)



**Coplanar Daughtercards**  
(Pin 1a Header = Pin 5a Shroud Side)  
Recommended PC Board Layout — Reference Page 112  
(Shroud Side Shown)


**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.





**Z-PACK HS3 Connector (Continued)**


**Vertical Pin Header Shrouds (Continued)**  
**6 Row, Right Module**



**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.




**4**


Z-PACK HS3 Connector

**Pin Header Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling			
	A	B	C		Insertion	IS Sheet	Ground Blade	
							Repair Kit	IS Sheet
30	—	10.00 .393	14.20 .559	5120683-1	91313-1	408-4546	1320534-1	408-4573



**Non-Coplanar Daughtercards**  
(Pin 1a Header = Pin 1f Shroud Side)  
Recommended PC Board Layout — Reference Page 112  
(Shroud Side Shown)




**Coplanar Daughtercards**  
(Pin 1a Header = Pin 5a Shroud Side)  
Recommended PC Board Layout — Reference Page 112  
(Shroud Side Shown)

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.


**Z-PACK HS3 Connector (Continued)**

**Layout Guide for Midplane Applications  
6 Row Connectors**



**Non-Coplanar Applications**



**Coplanar Applications**





**Right Module**





Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120680	5120683-1

**Right Module**





Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120680	5120684-1

**Center Module**





Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120679	5120682-1

**Center Module**





Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120679	5120682-1

**Left Module**



Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120681	5120684-1

**Left Module**



Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120681	5120683-1


**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**

**10 Row, Left Module  
(accepts Universal Guide Pin)**



4

Z-PACK HS3 Connector


**Receptacle Assemblies**

Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
50	5120875-1	1338743-1	408-8394	1338744-1	408-8393	1338746-1	408-8410

**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.




**Recommended PC Board Layout  
(Component Side Shown)**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**  
(Continued)

**10 Row, Left Module**  
(accepts ESD Guide Pin)




**Receptacle Assemblies**

Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
50	5120793-1	1338743-1	408-8394	1338744-1	408-8393	1338746-1	408-8410

**P.C.B. Hole Dimensions**


- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**Recommended PC Board Layout**  
(Component Side Shown)

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.






**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**  
(Continued)

**10 Row, Center Module**



**4**  
Z-PACK HS3 Connector

**Receptacle Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling					
	A	B	C		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
100	24.94 .982	22.50 .886	25.48 1.03	5120790-1	1338743-2	408-8394	1338744-1	408-8393	1338746-1	408-8410
50	12.44 .490	10.00 .394	12.90 .508	5120791-1	1338743-1	408-8394	1338744-1	408-8393	1338746-1	408-8410

**P.C.B. Hole Dimensions**


**Drilled Hole** — 0.7±0.025mm

**Fin. Hole** — 0.55 to 0.65mm

**Cu-thickness** — 0.025 to 0.050mm

**SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**Recommended PC Board Layout (Component Side Shown)**


**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**  
(Continued)

**10 Row, Right Module**  
(accepts Universal Guide Pin)




**Receptacle Assemblies**

Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
50	5120874-1	1338743-1	408-8394	1338744-1	408-8393	1338746-1	408-8410

**P.C.B. Hole Dimensions**


- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**Recommended PC Board Layout**  
(Component Side Shown)


**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



**Z-PACK HS3 Connector (Continued)**

**Right Angle Receptacle**  
(Continued)

**10 Row, Right Module**  
(accepts ESD Guide Pin)



**4**  
Z-PACK HS3 Connector


**Receptacle Assemblies**

Number of Positions	Part Number	Application Tooling					
		Insertion	IS Sheet	Hsg Removal	IS Sheet	Chiclet Removal	IS Sheet
50	5120792-1	1338743-1	408-8394	1338744-1	408-8393	1338746-1	408-8410

**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**Recommended PC Board Layout**  
(Component Side Shown)

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

**Z-PACK HS3 Connector (Continued)**


**Vertical Pin Header Assemblies**

**10 Row, Left Module (accepts Universal Guide Pin)**


**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.




Number of Positions	Dimensions				Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D			Seating	IS Sheet	Signal Pin		Ground Blade	
									Repair Kit	IS Sheet	Repair Kit	IS Sheet
50	13.70 .539	10.00 .394	21.61 .851	8.20 .323	<b>A</b>	5120672-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	13.70 .539	10.00 .394	21.61 .851	9.70 .383	<b>B</b>	5120672-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573



**Recommended PC Board Layout (Component Side Shown) For Non-Midplane Applications For Midplane Applications Reference Page 126**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.







**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Assemblies (Continued)**

**10 Row, Left Module (accepts ESD Guide Pin)**

**P.C.B. Hole Dimensions**


Drilled Hole — 0.7±0.025mm

Fin. Hole — 0.55 to 0.65mm

Cu-thickness — 0.025 to 0.050mm

SnPb-thickness — 0.004 to 0.010mm


**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**4**

Z-PACK HS3 Connector

Number of Positions	Dimensions					Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D	E			Seating	IS Sheet	Signal Pin		Ground Blade	
										Repair Kit	IS Sheet	Repair Kit	IS Sheet
50	14.80 .583	10.00 .394	22.71 .894	8.20 .323	3.70 .146	<b>A</b>	5120662-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.80 .583	10.00 .394	22.71 .894	9.70 .382	3.70 .146	<b>B</b>	5120662-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.80 .583	10.00 .394	22.71 .894	8.20 .323	13.00 .512	<b>K</b>	5120666-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.80 .583	10.00 .394	22.71 .894	9.70 .382	14.50 .571	<b>P</b>	5120666-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573



**Recommended PC Board Layout (Component Side Shown) For Non-Midplane Applications For Midplane Applications Reference Page 126**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

Catalog 1773095  
Revised 12-08


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208



K

**Tyco Electronics**  
High Speed Backplane Connectors

**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Assemblies (Continued)**

**10 Row, Center Module**

**P.C.B. Hole Dimensions**

Drilled Hole — 0.7±0.025mm  
Fin. Hole — 0.55 to 0.65mm  
Cu-thickness — 0.025 to 0.050mm  
SnPb-thickness — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

Number of Positions	Dimensions					Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D	E			Seating	IS Sheet	Signal Pin		Ground Blade	
										Repair Kit	IS Sheet	Repair Kit	IS Sheet
100	24.90 .980	22.50 .885	24.90 .980	8.20 .322	3.70 .145	<b>A</b>	5120658-1	91312-2	408-4546	354687-2	408-9979	1320534-2	408-4573
	24.90 .980	22.50 .885	24.90 .980	9.70 .381	3.70 .145	<b>B</b>	5120658-2	91312-2	408-4546	354687-2	408-9979	1320534-2	408-4573
	24.90 .980	22.50 .885	24.90 .980	8.20 .322	13.00 .511	<b>K</b>	5120664-1	91312-2	408-4546	354687-2	408-9979	1320534-2	408-4573
	24.90 .980	22.50 .885	24.90 .980	9.70 .381	14.50 .570	<b>P</b>	5120664-2	91312-2	408-4546	354687-2	408-9979	1320534-2	408-4573
50	12.41 .488	10.00 .393	12.40 .488	8.20 .322	3.70 .145	<b>A</b>	5120747-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	12.41 .488	10.00 .393	12.40 .488	9.70 .381	3.70 .145	<b>B</b>	5120747-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	12.41 .488	10.00 .393	12.40 .488	8.20 .322	13.00 .511	<b>K</b>	5120748-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	12.41 .488	10.00 .393	12.40 .488	9.70 .381	14.50 .570	<b>P</b>	5120748-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573

**Recommended PC Board Layout (Component Side Shown)**  
For Non-Midplane Applications  
For Midplane Applications Reference Page 126

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

120

Catalog 1773095  
Revised 12-08  
www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208

Black ID: Garryv

Downloaded from Arrow.com

**Z-PACK HS3 Connector (Continued)**


**Vertical Pin Header Assemblies (Continued)**

**10 Row, Right Module (accepts Universal Guide Pin)**

**P.C.B. Hole Dimensions**

- Drilled Hole — 0.7±0.025mm
- Fin. Hole — 0.55 to 0.65mm
- Cu-thickness — 0.025 to 0.050mm
- SnPb-thickness — 0.004 to 0.010mm


**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.



**4**

Z-PACK HS3 Connector

Number of Positions	Dimensions				Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D			Signal Pin		Ground Blade			
	Seating	IS Sheet	Repair Kit	IS Sheet			Repair Kit	IS Sheet				
50	14.45 .568	10.00 .393	22.28 .877	8.20 .322	<b>A</b>	5120670-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.45 .568	10.00 .393	22.28 .877	9.70 .381	<b>B</b>	5120670-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573



**Recommended PC Board Layout (Component Side Shown) For Non-Midplane Applications For Midplane Applications Reference Page 126**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

Catalog 1773095  
Revised 12-08  
www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208

K

**Tyco Electronics**  
High Speed Backplane Connectors

**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Assemblies (Continued)**

**10 Row, Right Module (accepts ESD Guide Pin)**

Part Number  
5120661-1

Part Number  
5120665-1

**P.C.B. Hole Dimensions**

Drilled Hole — 0.7±0.025mm

Fin. Hole — 0.55 to 0.65mm

Cu-thickness — 0.025 to 0.050mm

SnPb-thickness — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

Number of Positions	Dimensions					Pin Ref.	Part Numbers	Application Tooling					
	A	B	C	D	E			Seating	IS Sheet	Signal Pin		Ground Blade	
	Repair Kit	IS Sheet	Repair Kit	IS Sheet									
50	14.46 .569	10.00 .393	22.28 .877	8.20 .322	3.70 .145	<b>A</b>	5120661-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.46 .569	10.00 .393	22.28 .877	9.70 .381	3.70 .145	<b>B</b>	5120661-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.46 .569	10.00 .393	22.28 .877	8.20 .322	13.00 .511	<b>K</b>	5120665-1	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573
	14.46 .569	10.00 .393	22.28 .877	9.70 .381	14.50 .570	<b>P</b>	5120665-2	91312-1	408-4546	354687-2	408-9979	1320534-2	408-4573

**Recommended PC Board Layout (Component Side Shown)**  
For Non-Midplane Applications  
For Midplane Applications Reference Page 126

5120661-1 Shown

Ref. Line Seating Plane Connector

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

122

Catalog 1773095  
Revised 12-08

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208

Black ID: GARRYV


Downloaded from Arrow.com



**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Shrouds**

**10 Row, Left Module**



**P.C.B. Hole Dimensions**

- Drilled Hole** — 0.7±0.025mm
- Fin. Hole** — 0.55 to 0.65mm
- Cu-thickness** — 0.025 to 0.050mm
- SnPb-thickness** — 0.004 to 0.010mm


**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**4**


Z-PACK HS3 Connector

**Receptacle Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling			
	A	B	C		Seating	IS Sheet	Ground Blade	
							Repair Kit	IS Sheet
50	13.70 [.539]	10.00 [.877]	22.80 [.322]	5120668-1	91312-1	408-4546	1320534-2	408-4573



**Non-Coplanar Daughtercards**  
(Pin 1a Header = Pin 1k Shroud Side)  
Recommended PC Board Layout — Reference Page 126  
(Shroud Side Shown)



**Coplanar Daughtercards**  
(Pin 1a Header = Pin 5a Shroud Side)  
Recommended PC Board Layout — Reference Page 126  
(Shroud Side Shown)

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



K

**Tyco Electronics**  
High Speed Backplane Connectors

**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Shrouds (Continued)**

**10 Row, Center Module**

**P.C.B. Hole Dimensions**  
**Drilled Hole** — 0.7±0.025mm  
**Fin. Hole** — 0.55 to 0.65mm  
**Cu-thickness** — 0.025 to 0.050mm  
**SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.

**Receptacle Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling			
	A	B	C		Seating	IS Sheet	Ground Blade	
							Repair Kit	IS Sheet
100	24.90 .980	22.50 .886	24.90 .980	5120663-1	91312-2	408-4546	1320534-2	408-4573
50	12.41 .488	10.00 .394	12.40 .488	5120750-1	91312-1	408-4546	1320534-2	408-4573

**Non-Coplanar Daughtercards**  
 (Pin 1a Header = Pin 1k Shroud Side)  
 Recommended PC Board Layout — Reference Page 126  
 (Shroud Side Shown)

**Coplanar Daughtercards**  
 (Pin 1a Header = Pin 10a Shroud Side)  
 Recommended PC Board Layout — Reference Page 126  
 (Shroud Side Shown)

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

124

Catalog 1773095  
 Revised 12-08  
 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
 Canada: 1-905-470-4425  
 Mexico: 01-800-733-8926  
 C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
 Hong Kong: 852-2735-1628  
 Japan: 81-44-844-8013  
 UK: 44-8706-080-208

Black ID: GARRYV


Downloaded from Arrow.com



**Z-PACK HS3 Connector (Continued)**

**Vertical Pin Header Shrouds (Continued)**

**10 Row, Right Module**



**P.C.B. Hole Dimensions**

**Drilled Hole** — 0.7±0.025mm

**Fin. Hole** — 0.55 to 0.65mm

**Cu-thickness** — 0.025 to 0.050mm


**SnPb-thickness** — 0.004 to 0.010mm

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-13020.


**4**  
Z-PACK HS3 Connector

**Receptacle Assemblies**

Number of Positions	Dimensions			Part Number	Application Tooling			
	A	B	C		Seating	IS Sheet	Ground Blade	
							Repair Kit	IS Sheet
50	14.46 .569	10.00 .394	22.28 .877	5120667-1	91312-1	408-4546	1320534-2	408-4573



**Non-Coplanar Daughtercards**  
(Pin 1a Header = Pin 1k Shroud Side)  
Recommended PC Board Layout — Reference Page 126  
(Shroud Side Shown)



**Coplanar Daughtercards**  
(Pin 1a Header = Pin 5a Shroud Side)  
Recommended PC Board Layout — Reference Page 126  
(Shroud Side Shown)


**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.




**Z-PACK HS3 Connector (Continued)**

**Layout Guide for Midplane Applications  
10 Row Connectors**


**Non-Coplanar Applications**



**Coplanar Applications**




**Right Module**




Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120665	5120667-1

**Right Module**




Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120665	5120668-1


**Center Module**




No. of Pos.	Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
100	5120664	5120663-1
50	—	5120750-1




**Center Module**




No. of Pos.	Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
100	5120664	5120663-1
50	—	5120750-1




**Left Module**




Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120666	5120667-1



**Left Module**



Vertical Pin Header, Feed-Through Part No.	Shroud Part No.
5120666	5120668-1



**Note:** All part numbers are RoHS compliant.



**Z-PACK HS3 Connector (Continued)**

**Coding Keys (10 Row Only)**

**Compatibility** — Z-PACK HS3, Z-PACK 12 row connectors  
Part Number 120639-3 (white)  
Part Number 120639-6 (red)

**Material & Finish** — Valox

**Power and Guide Hardware  
Universal Power Module  
Vertical Receptacle (3 Pos.)**



The Tyco Electronics Universal Power Module is a multi-position, modular, hard metric board-to-board power connector designed to be compatible with Z-PACK 2mm HM connectors. The design is in an “inverse-sex” orientation and the vertical receptacle module meets the IEC 950 safety requirements for finger probe protection.

Both the headers and receptacle utilize Tyco Electronics ACTION PIN press-fit leads for ease of assembly onto printed circuit boards. Additionally, the vertical receptacle leads are polarized to allow only one orientation onto the printed circuit board, eliminating the possibility of reverse placement.


The Universal Power Module is compatible with a wide variety of other Tyco Electronics board-to-board connectors including Z-PACK HS3, Z-PACK HM-Zd and Z-PACK TinMan connectors.

The right angle header contacts are available with sequenced lengths for “make-first/break-last” applications.





Generous alignment features designed into the housings and optional guide pins and receptacles make the Tyco Electronics Universal Power Module ideal for “blind mating” applications.



**Part Number 120639-6**



**Part Number 120639-3**



**Recommended PC Board Hole Layout**

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

	Position Loaded	Part Numbers
Vertical Receptacle	ABC	5223955-2
	AC	5223984-1
High Current	ABC	5-5223955-2

**PCB Hole Dim.**  
Drilled Hole =  $0.7000 \pm 0.025$  [0.2756 ± .0010]  
Finished Hole =  $0.60 \pm 0.05$  [0.24 ± .002]  
Cu Thickness =  $0.375 \pm 0.0125$  [0.148 ± .00049]  
SnPb Thickness =  $0.007 \pm 0.003$  [0.0003 ± .0001]

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-1103.

**4**

Z-PACK HS3 Connector

**Z-PACK HS3 Connector (Continued)**

**Power and Guide Hardware**  
(Continued)

**Expanded Universal Power Module Vertical Receptacles**

**Material and Finish**

**Housing** — Polyester, gray

**Contact** — Copper alloy, plated 0.00127 [.000050] min. gold in mating area, 0.00050 [.000020] min. Tin-Lead on ACTION PIN product area, with entire contact underplated 0.00127 [.000050] min. nickel

**Related Product Data**

**Guiding Hardware** (Optional) — pages 132 and 133

**Application Tooling**

**Header**

Seating Tool, 224441-1  
Board Support Fixture, 224442-1

**Receptacle**

Seating Tool, 224421-1  
Board Support Fixture, 217602-1

**Technical Documents**

**Product Specification**




108-1651

**Application Specification**

114-1103

**Tyco Electronics Instruction Sheet**

408-4169 (Receptacle Seating Tool 224421-1)



**PCB Hole Dim.**  
Drilled Hole =  $0.7000 \pm 0.025$  [.02756 ± .0010]  
Finished Hole =  $0.60 \pm 0.05$  [.024 ± .002]  
Cu Thickness =  $0.375 \pm 0.0125$  [.0148 ± .00049]  
SnPb Thickness =  $0.007 \pm 0.003$  [.0003 ± .0001]

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-1103.

**Recommended PCB Hole Layout**

Position	A	B Ref.	Standard *10A Part Number	High Current *15A Part Number
4	3	12.50 .492	5223995-1	120953-1
5	4	15.50 .610	5223995-2	120953-2
6	5	18.50 .728	5223995-3	120953-3
7	6	21.50 .846	5223995-4	120953-4
8	7	24.50 .965	5223995-5	120953-5

\*Reference Product Specification 108-1651.

**Note:** For additional Power Module options reference Catalog 1773096, "Power Connectors and Interconnection Systems," or contact your Tyco Electronics Sales Representative.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.



## Z-PACK HS3 Connector (Continued)





### Power and Guide Hardware (Continued)

#### Universal Power Module Right Angle Headers (3 Pos.)

#### Material and Finish

**Housing** — polyester, natural color

**Contacts** — Copper alloy, plated 0.00127 [.000050] min. gold in mating area, 0.00050 [.000020] min. Tin-Lead on ACTION PIN post area, with entire contact underplated 0.00127 [.000050] min. nickel



PCB Hole Dim.  
 Drilled Hole =  $0.7000 \pm 0.025$  [.02756 ± .0010]  
 Finished Hole =  $0.60 \pm 0.05$  [.024 ± .002]  
 Cu Thickness =  $0.375 \pm 0.0125$  [.0148 ± .00049]  
 SnPb Thickness =  $0.007 \pm 0.003$  [.0003 ± .0001]

**Note:** For finishes other than Tin-Lead, reference Application Specification 114-1103.

Recommended PC Board Hole Layout

Blade Length Dimensions			Standard *10A Right Angle Header Part Numbers	High Current *15A Right Angle Header Part Numbers
Position A	Position B	Position C		
10.90 [.429]	10.90 [.429]	10.90 [.429]	5223961-1	5-5223961-1
10.90 [.429]	9.30 [.366]	10.90 [.429]	5223962-1	—
10.90 [.429]	9.30 [.366]	9.30 [.366]	5223968-1	—
10.90 [.429]	7.68 [.302]	10.90 [.429]	5223972-1	—
10.90 [.429]	7.68 [.302]	9.30 [.366]	5223971-1	—
10.90 [.429]	7.68 [.302]	7.68 [.302]	5223970-1	—
9.30 [.429]	10.90 [.429]	9.30 [.366]	5223963-1	—
9.30 [.366]	10.90 [.429]	7.68 [.302]	5223964-1	—
9.30 [.366]	9.30 [.366]	9.30 [.366]	5223967-1	—
9.30 [.366]	—	9.30 [.366]	5223975-1	—
9.30 [.366]	9.30 [.366]	7.68 [.302]	5223981-1	—
9.30 [.366]	7.68 [.302]	9.30 [.366]	5223965-1	—
7.68 [.302]	9.30 [.366]	7.68 [.302]	5223983-1	—
7.68 [.302]	7.68 [.302]	9.30 [.366]	5223980-1	—
7.68 [.302]	7.68 [.302]	7.68 [.302]	5223974-1	5-5223974-1

**Note:** For additional Power Module options reference Catalog 1773096, "Power Connectors and Interconnection Systems," or contact your Tyco Electronics Sales Representative.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

\*Reference Product Specification 108-1651.

**4**  
Z-PACK HS3 Connector



**Z-PACK HS3 Connector (Continued)**

**Power and Guide Hardware**  
(Continued)

**Expanded Universal Power Module Right Angle Headers**

**Material and Finish**

**Housing** — Polyester, gray

**Contacts** — Phosphor bronze, plated 0.00127 [.000050] min. gold in mating area, 0.00054 [.000021] min. Tin-Lead on ACTION PIN product area, with entire contact underplated 0.00127 [.000050] min. nickel

**Related Product Data**

**Guiding Hardware** (Optional) — pages 132 and 133

**Application Tooling**

**Header**

Seating Tool, 224441-1  
Board Support Fixture, 224442-1

**Receptacle**

Seating Tool, 224421-1  
Board Support Fixture, 217602-1

**Technical Documents**

**Product Specification**


108-1651

**Application Specification**

114-1103

**Tyco Electronics Instruction Sheet**

408-4169 (Receptacle Seating Tool 224421-1)



Positions	Dimensions		Standard *10A Base Part Number <sup>1</sup>	High Current *15A Base Part Number <sup>1</sup>
	A	B		
4	15.00 .591	12.75 .502	5646954	120954
5	18.00 .709	15.75 .620	5646955	120955
6	21.00 .827	18.75 .738	5646956	120956
7	24.00 .945	21.75 .856	5646957	120957
8	27.00 1.063	24.75 .974	5646958	120958

<sup>1</sup> Dash number indicates sequence pattern. See customer drawing for specific dash numbers.

\*Reference Product Specification 108-1651.

**Note:** All part numbers are RoHS compliant. Tin-Lead parts are RoHS compliant through exemption for lead in press-fit connectors.

**Note:** For additional Power Module options reference Catalog 1773096, "Power Connectors and Interconnection Systems," or contact your Tyco Electronics Sales Representative.




**Z-PACK HS3 Connector (Continued)**
**Power and Guide Hardware**

(Continued)


**AMP-HDI Static Discharge  
Guide/Power Pins**
**Compatibility** — Z-PACK HS3,  
Z-PACK 2mm HM connectors

**Part Number** — 532828-5\*

**Nut** — 21124-4

**Washer** — 986794-1

**Max. Current Rating** — 10 Amperes

 \*Additional sequence lengths are  
available, contact Tyco Electronics

**Material and Finish**

 Brass, plated 0.00076 [0.00030] gold  
over 0.00127-0.00254 [0.00050-  
.000100] nickel


4

Z-PACK HS3 Connector

**AMP-HDI Guide Pin/Power  
Receptacles**
**Compatibility** — Z-PACK HS3  
connector

**Part Number** — 535875-1\*


**Max. Current Rating** — 10 Amperes

 \*Additional lengths are available, see  
customer drawing.

**Material and Finish**
**Contact Finish** — 0.00076 [0.00030]  
gold in contact area, over 0.00127  
[0.00050] min. nickel underplate. Gold  
flash on remainder of the contact.

**ESD-Guide Pin/Feed-through**
**Compatibility** — Z-PACK HS3  
connector

**Part Number** — 120759-2\*

**Max. Current Rating** — 10 Amperes

 \*Additional sequence lengths are  
available, contact Tyco Electronics

**Note:** All part numbers are RoHS compliant.

 Catalog 1773095  
Revised 12-08

[www.tycoelectronics.com](http://www.tycoelectronics.com)

 Dimensions are in millimeters  
and inches unless otherwise  
specified. Values in brackets  
are U.S. equivalents.

 Dimensions are shown for  
reference purposes only.  
Specifications subject  
to change.

 USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

 South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208


K

**Tyco Electronics** High Speed Backplane Connectors

**Z-PACK HS3 Connector (Continued)**

**Power and Guide Hardware**  
(Continued)

**Guide Pin (Unkeyed)**

**Material and Finish**  
**Guide Pin** — Passivated stainless steel  
**Part Number 223956-1**

Technical drawing of a Guide Pin (Unkeyed). The side view shows a pin with a 4.85 Dia. [191] section, a length dimension B, and a section A. The end view shows a 7.80 Dia. [307] hexagonal base. A note indicates 'LOCTITE sealant applied in this area.' and 'See Chart'.

Dimension		Thread	Part Numbers
A	B		
7.50 [295]	24.73 [974]	M4 x 7-6g	223982-1*
9.20 [362]	25.16 [991]	M4 x 7-6g	223969-7
12.70 [500]	25.16 [991]	8-32 UNC-2A	223969-4
12.70 [500]	25.16 [991]	M4 x 7-6g	223969-1
6.20 [244]	25.16 [991]	M4 x 7-6g	223956-1
12.70 [500]	31.25 [1.230]	8-32 UNC-2A	1-223969-0
3.80** [150]	27.16 [1.069]	M4 x 7-6h	120646-1
2.00** [079]	27.16 [1.069]	M3 x 0.5	223988-1

\*6.35 Hex Base  
\*\*Internal Thread

**Female Guide Module (Unkeyed)**

**Material and Finish**  
**Guide Module** — Zinc alloy, chromate conversion coated

**Related Product Data**  
**Application Tooling** —  
Seating Tool, 224440-1  
Board Support Fixture, 217603-1

**Technical Documents**  
**Product Specification**  
108-1651  
**Application Specification**  
114-1103  
**Part Number 223957-1**  
(as shown)  
**Part Number 223979-1**  
(dual alignment posts)

Technical drawing of a Female Guide Module (Unkeyed). The side view shows a module with a 7.90 [311] length, a 5.40 Dia. [213] section, and a 4.00 [157] section. The end view shows a 9.70 [382] length and a 5.50 [217] section. A detail view shows a 3.175 ± 0.08 [125 ± .003] Dia. Drilled Hole 2 Plcs. and a 34.20 [1.346] length. A 4-40 UNC-2B thread is also indicated. Other dimensions include 3.95 [156] Ref., 15.00 [591], 5.75 [226], and 11.00 [443].

**Recommended PC Board Hole Layout**

LOCTITE is a trademark of Henkel Corp.

**Note:** All part numbers are RoHS compliant.

132

Catalog 1773095  
Revised 12-08  
www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are U.S. equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752  
Canada: 1-905-470-4425  
Mexico: 01-800-733-8926  
C. America: 52-55-1106-0803

South America: 55-11-2103-6000  
Hong Kong: 852-2735-1628  
Japan: 81-44-844-8013  
UK: 44-8706-080-208

Black ID: GARRYV

Downloaded from Arrow.com

**Z-PACK HS3 Connector (Continued)**

**Power and Guide Hardware**  
(Continued)


**Guide Pin (Keyed)**

**Material and Finish**

**Guide Pin** — Zinc alloy, chromate conversion coated

**Part Number 223985**

Dimension		Part Number
A	B	
25.16 .991	20.39 .803	223985-1
29.00 1.142	24.23 .954	223985-3



**Recommended PC Board Layout  
(Position Shown Used with  
Part Number 5223986-1)**


**Female Guide Module (Keyed)**

**Material and Finish**

**Guide Module** — Zinc alloy, chromate conversion coated

**Part Number 5223986**

Dim. A	Thread	Part Number
0°	4-40	5223986-1
45°	4-40	5223986-2
90°	4-40	5223986-3
135°	4-40	5223986-4
180°	4-40	5223986-5
225°	4-40	5223986-6
270°	4-40	5223986-7
315°	4-40	5223986-8
0°	M2.6	5120913-1
45°	M2.6	5120913-2
90°	M2.6	5120913-3
135°	M2.6	5120913-4
180°	M2.6	5120913-5
225°	M2.6	5120913-6
270°	M2.6	5120913-7
315°	M2.6	5120913-8




**Note:** All part numbers are RoHS compliant.

**4**


Z-PACK HS3 Connector

### Z-PACK HS3 Connector (Continued)

#### Z-PACK HS-3 Connector Mating Sequence Chart



Fully Mated



Reliable Mate


Product Family	Dim. C	Dim. A Fully Mated	Contact	Dim. B.		Fully Mated Wipe Length
				Reliable Mate	First Mate Last Break	
Z-PACK HM-Zd Product	1.50 .059	12.50 .492	Ground Shield	16.78 [.661]	17.55 [.691]	4.28 [.169]
			Signal Level 2	15.41 [.607]	15.85 [.624]	2.91 [.115]
			Signal Level 1	13.91 [.548]	14.35 [.565]	1.41 [.056]
Z-PACK HM-Zd Guide Hardware	3.00 .118	12.50 .492	24.0 mm Pin	27.50 [1.083]	33.40 [1.315]	N/A
			22.2 mm Pin	25.70 [1.012]	31.60 [1.244]	N/A
			Key Blocking Point	N/A	22.03 [.867]	N/A
Z-PACK TinMan Product	1.50 .059	12.50 .492	Ground Pins	16.44 [.647]	17.13 [.674]	3.94 [.155]
			Signal Level 2	14.94 [.588]	15.63 [.615]	2.44 [.096]
			Signal Level 1	N/A	N/A	N/A
Z-PACK 2mm HM Product	1.50 .059	12.50 .492	Signal Level 3	18.27 [.719]	18.84 [.742]	5.77 [.227]
			Signal Level 2	16.77 [.660]	17.34 [.683]	4.27 [.168]
			Signal Level 1	15.27 [.601]	15.84 [.624]	2.77 [.109]
MULTIGIG RT T1 Product	2.50 .098	12.50 .492	Ground	18.00 [.709]	—	5.50 [.217]
			Signal Level 3	18.00 [.709]	—	5.50 [.217]
			Signal Level 2	16.50 [.650]	—	4.00 [.157]
			Signal Level 1	15.00 [.591]	—	2.50 [.098]
MULTIGIG RT T2 Product	2.25 .089	12.50 .492	Ground	18.00 [.709]	—	5.50 [.217]
			Signal Level 3	18.00 [.709]	—	5.50 [.217]
			Signal Level 2	16.50 [.650]	—	4.00 [.157]
MULTIGIG RT Power Module	5.50 .217	12.50 .492	Signal Level 1	15.00 [.591]	—	2.50 [.098]
			Power Level 3	23.75 [.935]	—	11.25 [.443]
			Power Level 2	22.25 [.876]	—	9.75 [.384]
MULTIGIG RT Guide Hardware	N/A	12.50 .492	Power Level 1	20.75 [.817]	—	8.25 [.325]
			Guide Pin Key	33.25 [1.309]	N/A	20.75 [.817]
			Guide ESD Contact	30.75 [1.211]	—	18.25 [.719]
Z-PACK HS3 Product	1.50 .059	12.50 .492	Ground	17.08 [.672]	17.60 [.693]	4.78 [.188]
			Signal Level 2	16.05 [.632]	16.47 [.648]	3.75 [.148]
			Signal Level 1	14.55 [.573]	14.97 [.589]	2.25 [.089]
UPM	3.50 .138	12.50 .492	Power Level 3	20.25 [.797]	20.95 [.825]	8.10 [.319]
			Power Level 2	18.65 [.734]	19.35 [.762]	6.50 [.256]
			Power Level 1	17.03 [.670]	17.73 [.698]	4.88 [.192]
UPM Guide Hardware	5.75 .226	12.50 .492	Guide Pin Key	31.39 [1.236]	36.16 [1.424]	N/A
			Keyed Guide Pin	31.39 [1.236]	36.16 [1.424]	N/A
			Keyed Guide Pin	35.23 [1.387]	40.00 [1.575]	N/A
MULTI-BEAM XL Right Angle Header to Vertical Receptacle	5.08 .200	14.73 .580	PreMate Power — Level 1	—	16.84 [.663]	5.61 [.221] Min.
			PostMate Power — Level 2	—	17.81 [.701]	4.34 [.171] Min.
			PreMate Signal — Level 2	—	18.26 [.719]	3.81 [.150] Min.
			PostMate Signal — Level 3	—	19.53 [.769]	2.54 [.100] Min.
MULTI-BEAM XL Right Angle Receptacle to Vertical Header	3.81 .150	13.21 .520	PreMate Power — Level 1	—	15.32 [.603]	5.61 [.221] Min.
			PostMate Power — Level 2	—	16.28 [.641]	4.34 [.171] Min.
			PreMate Signal — Level 2	—	16.74 [.659]	3.81 [.150] Min.
			PostMate Signal — Level 3	—	18.01 [.709]	2.54 [.100] Min.





**Z-PACK HS3 Connector (Continued)**

**Application Tooling and Equipment**



1585280-1 Model AP3

1585696-1 Model BMEP 5T

1585699-1 Model MEP 6T

Typical Manual Arbor Frame Assembly (Commercially Available)

Insertion Tool Assembly IS 408-9979

Contact Replacement Tool IS 408-2636-1

Replacement Pin Assembly IS 408-9979

Setscrew IS 408-9979

Extraction Tool Assembly IS 408-9979

Pusher IS 408-9979

Spacer

Pin Support Tube IS 408-9979

Tool Tip IS 408-9979

Pin Repair Kit IS 408-9979


Chiclet Removal Tool IS 408-8410

Ground Blade Repair Kit IS 408-4573


Housing Removal Tool Kit IS 408-8393

Ground Blade Extraction Tool IS 408-4573


Ground Blade Insertion Tool IS 408-4573



Typical PC Board Support (Customer Supplied)



Typical Receptacle Seating Tool IS 408-8500



Typical Pin Header Seating Tool IS 408-8501

Note: All part numbers are RoHS compliant.





**Engineering Notes**

