

WSLP

RoHS

COMPLIANT

HALOGEN


FREE

<u>GREEN</u>

(5-2008)

Vishay Dale

Power Metal Strip[®] Resistors, Very High Power (to 3 W), Low Value (Down to 0.0005 Ω), Surface-Mount



LINKS TO ADDITIONAL RESOURCES

FEATURES

- Very high power to foot print size ratio (3 W in 2512, 2 W in 2010, 1 W in 1206, 0.5 W in 0805, and 0.4 W in 0603 package)
- All welded construction of the Power Metal Strip[®] resistors are ideal for all types of current sensing, voltage division and pulse applications
- Proprietary processing technique produces extremely low resistance values (down to 0.0005 Ω)
- Sulfur resistance by construction that is unaffected by high sulfur environments
- Very low inductance 0.5 nH to 5 nH
- Low thermal EMF (< 3 µV/°C)
- AEC-Q200 qualified (1)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

Notes

30


3D Models

- This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts
 with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details
- Follow link to Overview of Automotive Grade Products for more details: <u>www.vishay.com/doc?49924</u>
- "SMD Current Sense: AEC-Q200 vs. Vishay Qualification" technical note: <u>www.vishay.com/doc?30416</u>
- ⁽¹⁾ Flame retardance test may not be applicable to some resistor technologies

| STANDARD ELECTRICAL SPECIFICATIONS | | | | | | | |
|------------------------------------|------|---|---------------|---------------------|---------------|--|--|
| GLOBAL MODEL | SIZE | POWER RATING P _{70 °C} W | RESISTANCE V | WEIGHT (typical) | | | |
| | | | TOL. ± 0.5 % | TOL. ± 1.0 % | g/1000 pieces | | |
| WSLP0603 | 0603 | 0.4 | 0.015 to 0.1 | 0.01 to 0.1 | 1.9 | | |
| WSLP0805 | 0805 | 0.5 | 0.005 to 0.1 | 0.005 to 0.1 | 4.8 | | |
| WSLP1206 | 1206 | 1.0 | 0.005 to 0.05 | 0.0005 to 0.05 | 16.2 | | |
| WSLP2010 | 2010 | 2.0 | 0.004 to 0.03 | 0.001 to 0.03 | 38.9 | | |
| WSLP2512 | 2512 | 3.0 | 0.003 to 0.01 | 0.0005 to 0.01 | 63.6 | | |

Notes

- · Part marking: value; tolerance: due to resistor size limitations some resistors will be marked with only the resistance value
- "Thermal Management for Surface-Mount Devices" white paper: <u>www.vishay.com/doc?30380</u>
- ⁽¹⁾ WSLP1206 0.0005 Ω to 0.00099 Ω is only available with 2 % tolerance (G tolerance code)



Notes

- Per PCN-DR-00009-2022-REV-0, WSL marking will be removed effective March 1st, 2023
- ⁽¹⁾ WSL marking (<u>www.vishay.com/doc?30327</u>); WSL decade values (<u>www.vishay.com/doc?30117</u>)
- (2) Packaging code: EB (lead (Pb)-free) and TB (tin / lead) are non-standard packaging codes that designate 1000 piece reel quantities. These non-standard packaging codes are identical to our standard EA (lead (Pb)-free) and TA (tin / lead), except that they have a package quantity of 1000 pieces
- ⁽³⁾ Follow link for customization capabilities: <u>www.vishay.com/doc?48163</u>

Revision: 10-Jan-2023

1

Document Number: 30122

For technical questions, contact: ww2bresistors@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



www.vishay.com

WSLP


Vishay Dale


| TECHNICAL SPECIFICATIONS | | | | | | | |
|-------------------------------------|--------|--|---|----------|----------|----------|--|
| PARAMETER | UNIT | RESISTOR CHARACTERISTICS | | | | | |
| FARAMETER | UNIT | WSLP0603 (1) | WSLP0805 | WSLP1206 | WSLP2010 | WSLP2512 | |
| | ppm/°C | \pm 75 for 50 m Ω to 100 m Ω | \pm 75 for 7 m Ω to 500 m Ω | | | | |
| Component temperature coefficient | | \pm 110 for 10 m Ω to 49 m Ω | \pm 110 for 5 m Ω to 6.9 m Ω | | | | |
| (including terminal) ⁽²⁾ | | - | \pm 150 for 3 m Ω to 4.9 m Ω | | | | |
| TCR measured from -55 °C to +155 °C | | - | \pm 275 for 1 m Ω to 2.9 m Ω | | | | |
| | | - | \pm 400 for 0.5 m Ω to 0.99 m Ω | | | 2 | |
| Element TCR ⁽³⁾ | ppm/°C | < 20 | | | | | |
| Operating temperature range | °C | -65 to +170 | | | | | |
| Maximum working voltage (4) | V | $(P \times R)^{1/2}$ | | | | | |

Notes

- "Temperature Coefficient of Resistance for Current Sensing" white paper: <u>www.vishay.com/doc?30405</u>
- ⁽¹⁾ Consult factory for detailed TCR performance across temperature range associated with PCN-DR-00003-2020 for WSLP0603. TCR performance is improved for +25 °C to +155 °C
 ⁽²⁾ Consult factory for +25 °C to +155 °C
- ⁽²⁾ Component TCR total TCR that includes the TCR effects of the resistor element and the copper terminal
- (3) Element TCR only applies to the alloy used for the resistor element; refer to item 1 in the construction illustration on the following page
- ⁽⁴⁾ Maximum working voltage the WSL is not voltage sensitive, but is limited by power / energy dissipation and is also not ESD sensitive

DIMENSIONS





Notes

- 3D models available. WSLP models: <u>www.vishay.com/doc?30313</u>
- Surface-mount solder profile recommendations: <u>www.vishay.com/doc?31052</u>

| MODEL | RESISTANCE RANGE | DIMENSIONS in inches (millimeters) | | | | SOLDER PAD DIMENSIONS in inches (millimeters) | | |
|--------------|---------------------|--|---------------------------------|---|---|--|-----------------|-----------------|
| | (Ω) | L | w | н | т | а | b | I |
| WSLP0603 (1) | 0.01 to 0.1 | 0.060 ± 0.010 (1.52 ± 0.254) | 0.030 ± 0.010 (0.76 ± 0.254) | $\begin{array}{c} 0.016 \pm 0.005 \\ (0.406 \pm 0.127) \end{array}$ | $\begin{array}{c} 0.015 \pm 0.010 \\ (0.381 \pm 0.254) \end{array}$ | 0.040 (1.02) | 0.040 (1.02) | 0.020 (0.50) |
| WSLP0805 (2) | 0.005 to 0.1 | $\begin{array}{c} 0.080 \pm 0.010 \\ (2.03 \pm 0.254) \end{array}$ | 0.050 ± 0.010 (1.27 ± 0.254) | 0.016 ± 0.005 (0.406 ± 0.127) | $\begin{array}{c} 0.015 \pm 0.010 \\ (0.381 \pm 0.254) \end{array}$ | 0.040 (1.02) | 0.050 (1.27) | 0.020 (0.50) |
| WSLP1206 | 0.0005 to 0.00099 | 0.126 ± 0.010 (3.20 ± 0.254) | 0.063 ± 0.010 (1.60 ± 0.254) | 0.025 ± 0.010 (0.635 ± 0.254) | 0.041 ± 0.010 (1.04 ± 0.254) | 0.089 (2.26) | 0.076 (1.93) | 0.023 (0.58) |
| | 0.001 to 0.0019 | | | | | 0.086 (2.18) | 0.076 (1.93) | 0.029 (0.74) |
| | 0.002 to 0.0059 | | | | 0.025 ± 0.010 (0.635 ± 0.254) | 0.070 (1.78) | 0.076 (1.93) | 0.061 (1.55) |
| | 0.006 to 0.050 | | | | $\begin{array}{c} 0.020 \pm 0.010 \\ (0.508 \pm 0.254) \end{array}$ | 0.065 (1.65) | 0.076 (1.93) | 0.071 (1.80) |
| WSLP2010 | 0.001 to 0.0069 | 0.200 ± 0.010 (5.08 ± 0.254) | 0.100 ± 0.010 (2.54 ± 0.254) | 0.025 ± 0.010 (0.635 ± 0.254) | 0.058 ± 0.010 (1.47 ± 0.254) | 0.093 (2.36) | 0.120 (3.05) | 0.055 (1.40) |
| | 0.007 to 0.03 | | | | $\begin{array}{c} 0.020 \pm 0.010 \\ (0.508 \pm 0.254) \end{array}$ | 0.055 (1.40) | | 0.130 (3.30) |
| WSLP2512 | 0.0005 to 0.00099 | 0.250 ± 0.010 (6.35 ± 0.254) | 0.125 ± 0.010 (3.18 ± 0.254) | 0.025 ± 0.010 (0.635 ± 0.254) | 0.107 ± 0.010 (2.72 ± 0.254) | 0.120 (3.05) | 0.145 (3.68) | 0.050 |
| | 0.001 to 0.0049 | | | | 0.087 ± 0.010 (2.21 ± 0.254) | | | (1.27) |
| | 0.005 to 0.0069 | | | | 0.047 ± 0.010 (1.19 ± 0.254) | 0.083 (2.11) | | 0.125 (3.18) |
| | 0.007 to 0.01 | | | | 0.030 ± 0.010 (0.762 ± 0.254) | 0.065 (1.65) | | 0.160 (4.06) |

Notes

(1) PCN-DR-00003-2020 changed terminal height for WSLP0603 from 0.013" ± 0.005" for clad construction to 0.016" ± 0.005" for welded construction

 $^{(2)}$ PCN-DR-000023-2021-REV-1 changed terminal height for WSLP0805 from 0.013" \pm 0.005" for clad construction to 0.016" \pm 0.005" for welded construction

| Revision: 10-Jan-2023 | 2 | Doc |
|-----------------------|--|-----|
| | For technical questions, contact: ww2bresistors@vishay.com | |

Document Number: 30122

esistors@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000


Upgrade for Wider Resistance Range to WFM




WSLP

Vishay Dale

DERATING




PULSE CAPABILITY



www.vishay.com/resistors/power-metal-strip-calculator

WELDED CONSTRUCTION



- (1) Resistive element: solid metal nickel-chrome or manganese-copper alloy resistive element with low TCR (< 20 ppm/°C)
- Terminal: solid copper, 100 % Sn (200 µ" min.) (2) with 100 % Ni (40 μ^{*} min.) under layer finish
- (3) Terminal / element weld
- (4) Silicone coating with ink print

| PERFORMANCE | | | | | |
|---------------------------|---|----------------------|--|--|--|
| TEST | CONDITIONS OF TEST | TEST LIMITS | | | |
| Thermal shock | -55 °C to +150 °C, 1000 cycles, 15 min at each extreme | ± (0.5 % + 0.0005 Ω) | | | |
| Short time overload | Refer to link for short time overload performance and pulse capability; www.vishay.com/resistors/power-metal-strip-calculator/ | ± (0.5 % + 0.0005 Ω) | | | |
| Low temperature operation | -65 °C for 24 h | ± (0.5 % + 0.0005 Ω) | | | |
| High temperature exposure | 1000 h at +170 °C | ± (1.0 % + 0.0005 Ω) | | | |
| Bias humidity | +85 °C, 85 % RH, 10 % bias, 1000 h | ± (0.5 % + 0.0005 Ω) | | | |
| Mechanical shock | 100 g's for 6 ms, 5 pulses | ± (0.5 % + 0.0005 Ω) | | | |
| Vibration | Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h | ± (0.5 % + 0.0005 Ω) | | | |
| Load life | 1000 h at 70 °C, 1.5 h "ON", 0.5 h "OFF" | ± (1.0 % + 0.0005 Ω) | | | |
| Resistance to solder heat | +260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence | ± (0.5 % + 0.0005 Ω) | | | |
| Moisture resistance | MIL-STD-202, method 106, 0 % power, 7b not required | ± (0.5 % + 0.0005 Ω) | | | |

| PACKAGING ⁽¹⁾ | | | | | | | |
|--------------------------|--------------------------|-------------|---------------|------|--|--|--|
| MODEL | REEL | | | | | | |
| MODEL | TAPE WIDTH | DIAMETER | PIECES / REEL | CODE | | | |
| WSLP0603 | 8 mm / punched paper | 178 mm / 7" | 5000 | EA | | | |
| WSLP0805 | 8 mm / punched paper | 178 mm / 7" | 5000 | EA | | | |
| WSLP1206 | 8 mm / embossed plastic | 178 mm / 7" | 4000 | EA | | | |
| WSLP2010 | 12 mm / embossed plastic | 178 mm / 7" | 4000 | EA | | | |
| WSLP2512 | 12 mm / embossed plastic | 178 mm / 7" | 2000 | EA | | | |

Notes

Embossed carrier tape per EIA-481

(1) Additional packaging details at www.vishay.com/doc?20051

Revision: 10-Jan-2023

3

Document Number: 30122

For technical questions, contact: ww2bresistors@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.