

## 25A, 50V - 1000V Standard Bridge Rectifier

#### **FEATURES**

- AEC-Q101 qualified available
- Glass passivated chip junction
- Ideal for printed circuit board
- Typical IR less than 0.1μA
- High surge current capability
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

#### **APPLICATIONS**

- Switching mode power supply (SMPS)
- Adapters
- Lighting application


#### **MECHANICAL DATA**

- Case: TS-6P
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Mounting torque: 0.92 N⋅m maximum
- Polarity: As marked
- Weight: 7.15g (approximately)

KEY PARAMETERS					
PARAMETER	VALUE	UNIT			
I <sub>F</sub>	25	Α			
$V_{RRM}$	50 - 1000	V			
I <sub>FSM</sub>	350	Α			
$T_{JMAX}$	150	°C			
Package	TS-6P				
Configuration	Quad				







ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25°C unless otherwise noted)									
PARAMETER	SYMBOL	TS25P 01G	TS25P 02G	TS25P 03G	TS25P 04G	TS25P 05G	TS25P 06G	TS25P 07G	UNIT
Marking code on the device		TS25P 01G	TS25P 02G	TS25P 03G	TS25P 04G	TS25P 05G	TS25P 06G	TS25P 07G	
Repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	1000	V
Reverse voltage, total rms value	$V_{R(RMS)}$	35	70	140	280	420	560	700	V
Forward current	l <sub>F</sub>	25					Α		
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	350					А		
Rating of fusing (t<8.3ms)	l <sup>2</sup> t 508.37					A <sup>2</sup> s			
Junction temperature	T <sub>J</sub>	- 55 to +150				°C			
Storage temperature	T <sub>STG</sub>	- 55 to +150					°C		

Taiwan Semiconductor

THERMAL PERFORMANCE						
PARAMETER	SYMBOL	TYP	UNIT			
Junction-to-case thermal resistance	R <sub>eJC</sub>	0.6	°C/W			

ELECTRICAL SPECIFICATIONS (T <sub>A</sub> = 25°C unless otherwise noted)						
PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT	
Forward voltage per diode <sup>(1)</sup>	I <sub>F</sub> = 12.5A, T <sub>J</sub> = 25°C	V <sub>F</sub>	-	1.0	V	
	I <sub>F</sub> = 25.0A, T <sub>J</sub> = 25°C		-	1.1	V	
Reverse current @ rated V <sub>R</sub> per diode <sup>(2)</sup>	T <sub>J</sub> = 25°C		-	10	μΑ	
	T <sub>J</sub> = 125°C	I <sub>R</sub>	-	500	μA	

#### Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION					
ORDERING CODE <sup>(1)(2)</sup>	PACKAGE	PACKING			
TS25PxG	TS-6P	15 / Tube			
TS25PxGH	TS-6P	15 / Tube			

#### Notes:

- 1. "x" defines voltage from 50V(TS25P01G) to 1000V(TS25P07G)
- 2. "H" means AEC-Q101 qualified



#### **CHARACTERISTICS CURVES**

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 

**Fig.1 Forward Current Derating Curve** 




Fig.3 Typical Reverse Characteristics





Fig.2 Typical Junction Capacitance



**Fig.4 Typical Forward Characteristics** 






Fig.5 Maximum Non-Repetitive Forward Surge Current





### **PACKAGE OUTLINE DIMENSIONS**

TS-6P



DIM.	M Unit (mm)		Unit (	(inch)	
DIIVI.	Min.	Max.	Min.	Max.	
Α	4.40	4.80	0.173	0.189	
A1	3.40	3.80	0.134	0.150	
A2	2.50	2.90	0.098	0.114	
b	0.90	1.10	0.035	0.043	
b2	2.00	2.40	0.079	0.094	
С	0.65	0.75	0.026	0.030	
D	19.70	20.30	0.776	0.799	
D2	10.80	11.20	0.425	0.441	
D3	-	4.80	-	0.189	
E	29.70	30.30	1.169	1.193	
E2	2.30	2.70	0.091	0.106	
е	7.30	7.70	0.287	0.303	
e1	9.80	10.20	0.386	0.402	
L	17.00	18.00	0.669	0.709	
L4	3.80	4.20	0.150	0.165	
L5	0.45	0.65	0.018	0.026	
Р	3.10	3.40	0.122	0.134	

## **MARKING DIAGRAM**



P/N = Marking Code

G = Green Compound

YWW = Date Code

F = Factory Code



Taiwan Semiconductor

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Taiwan Semiconductor:

<u>TS25P01G</u> <u>TS25P02G</u> <u>TS25P03G</u> <u>TS25P04G</u> <u>TS25P04G</u> <u>TS25P05G</u> <u>TS25P06G</u> <u>TS25P07G</u> <u>TS25P04GH</u> <u>TS25P05GH</u> TS25P06GH TS25P07GH