





| ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified) |  |                   |             |      |
|---|--|-------------------|-------------|------|
| PARAMETER   | TEST CONDITION   | SYMBOL            | VALUE       | UNIT |
| <b>INPUT</b>  |  |                   |             |      |
| Reverse voltage   |  | V <sub>R</sub>    | 6           | V    |
| Forward current   |  | I <sub>F</sub>    | 60          | mA   |
| Surge current   | t ≤ 10 μs  | I <sub>FSM</sub>  | 2.5         | A    |
| Power dissipation   |  | P <sub>diss</sub> | 100         | mW   |
| <b>OUTPUT</b>   |  |                   |             |      |
| Collector emitter breakdown voltage   |  | V <sub>CEO</sub>  | 70          | V    |
| Emitter base breakdown voltage  |  | V <sub>EBO</sub>  | 7           | V    |
| Collector current   |  | I <sub>C</sub>    | 50          | mA   |
|   | t < 1 ms   | I <sub>C</sub>    | 100         | mA   |
| Power dissipation   |  | P <sub>diss</sub> | 150         | mW   |
| <b>COUPLER</b>  |  |                   |             |      |
| Storage temperature range   |  | T <sub>stg</sub>  | -55 to +150 | °C   |
| Operating temperature range   |  | T <sub>amb</sub>  | -55 to +100 | °C   |
| Junction temperature  |  | T <sub>j</sub>    | 100         | °C   |
| Soldering temperature   | Max. 10 s, dip soldering: distance to seating plane ≥ 1.5 mm | T <sub>slid</sub> | 260         | °C   |

**Note**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability

| ELECTRICAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified) |  |                    |      |      |      |      |
|---|--|--------------------|------|------|------|------|
| PARAMETER   | TEST CONDITION                                   | SYMBOL             | MIN. | TYP. | MAX. | UNIT |
| <b>INPUT</b>  |  |                    |      |      |      |      |
| Forward voltage   | I <sub>F</sub> = 10 mA                           | V <sub>F</sub>     | -    | 1.1  | 1.5  | V    |
| Reverse current   | V <sub>R</sub> = 3 V                             | I <sub>R</sub>     | -    | -    | 10   | μA   |
| Capacitance   | V <sub>R</sub> = 0 V, f = 1 MHz                  | C <sub>O</sub>     | -    | 50   | -    | pF   |
| <b>OUTPUT</b>   |  |                    |      |      |      |      |
| Collector emitter breakdown voltage   | I <sub>C</sub> = 1 mA, I <sub>F</sub> = 0 mA     | BV <sub>CEO</sub>  | 30   | -    | -    | V    |
| Emitter collector breakdown voltage   | I <sub>E</sub> = 100 μA, I <sub>F</sub> = 0 mA   | BV <sub>ECO</sub>  | 7    | -    | -    | V    |
| Collector base breakdown voltage  | I <sub>C</sub> = 10 μA, I <sub>F</sub> = 0 mA    | BV <sub>CBO</sub>  | 70   | -    | -    | V    |
| Collector emitter leakage current   | V <sub>CE</sub> = 10 V, I <sub>F</sub> = 0 mA    | I <sub>CEO</sub>   | -    | 5    | 50   | nA   |
| Emitter collector capacitance   | V <sub>CE</sub> = 0 V                            | C <sub>CE</sub>    | -    | 6    | -    | pF   |
| <b>COUPLER</b>  |  |                    |      |      |      |      |
| Collector emitter, saturation voltage   | I <sub>CE</sub> = 0.5 mA, I <sub>F</sub> = 10 mA | V <sub>CEsat</sub> | -    | -    | 0.4  | V    |
| Capacitance (input-output)  |  | C <sub>IO</sub>    | -    | 0.5  | -    | pF   |

**Note**

- Minimum and maximum values were tested requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

| CURRENT TRANSFER RATIO         |  |                   |      |      |      |      |
|--------------------------------|--|-------------------|------|------|------|------|
| PARAMETER                      | TEST CONDITION                                 | SYMBOL            | MIN. | TYP. | MAX. | UNIT |
| I <sub>C</sub> /I <sub>F</sub> | V <sub>CE</sub> = 10 V, I <sub>F</sub> = 10 mA | CTR <sub>DC</sub> | 50   | -    | -    | %    |

| SWITCHING CHARACTERISTICS |   |                  |      |      |      |      |
|---------------------------|---|------------------|------|------|------|------|
| PARAMETER                 | TEST CONDITION  | SYMBOL           | MIN. | TYP. | MAX. | UNIT |
| Turn-on time              | I <sub>C</sub> = 2 mA, R <sub>L</sub> = 100 Ω, V <sub>CE</sub> = 10 V | t <sub>on</sub>  | -    | 3    | -    | μs   |
| Turn-off time             |   | t <sub>off</sub> | -    | 3    | -    | μs   |



| SAFETY AND INSULATION RATINGS                |  |                   |                    |                   |
|--|--|-------------------|--------------------|-------------------|
| PARAMETER                                    | TEST CONDITION                                     | SYMBOL            | VALUE              | UNIT              |
| Climatic classification                      | According to IEC 68 part 1                         |                   | 55 / 100 / 21      |                   |
| Comparative tracking index                   |  | CTI               | 175                |                   |
| Maximum rated withstanding isolation voltage | t = 1 min  | V <sub>ISO</sub>  | 4420               | V <sub>RMS</sub>  |
| Maximum transient isolation voltage          |  | V <sub>IOTM</sub> | 8000               | V <sub>peak</sub> |
| Maximum repetitive peak isolation voltage    |  | V <sub>IORM</sub> | 890                | V <sub>peak</sub> |
| Isolation resistance                         | V <sub>IO</sub> = 500 V, T <sub>amb</sub> = 25 °C  | R <sub>IO</sub>   | ≥ 10 <sup>12</sup> | Ω                 |
|  | V <sub>IO</sub> = 500 V, T <sub>amb</sub> = 100 °C | R <sub>IO</sub>   | ≥ 10 <sup>11</sup> | Ω                 |
| Output safety power                          |  | P <sub>SO</sub>   | 700                | mW                |
| Input safety current                         |  | I <sub>SI</sub>   | 400                | mA                |
| Safety temperature                           |  | T <sub>S</sub>    | 175                | °C                |
| Creepage distance                            |  |                   | ≥ 7                | mm                |
| Clearance distance                           |  |                   | ≥ 7                | mm                |
| Insulation thickness                         |  | DTI               | ≥ 0.4              | mm                |

**Note**

- As per IEC 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for “safe electrical insulation” only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits

**TYPICAL CHARACTERISTICS** (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 1 - Forward Voltage vs. Forward Current

Fig. 2 - Normalized Non-Saturated and Saturated CTR vs. LED Current





Fig. 3 - Normalized Non-Saturated and Saturated CTR vs. LED Current






Fig. 4 - Normalized Non-Saturated and Saturated CTR vs. LED Current




Fig. 7 - Collector Emitter Leakage Current vs. Temperature




Fig. 5 - Normalized Non-Saturated and Saturated CTR vs. LED Current




Fig. 8 - Normalized CTR<sub>cb</sub> vs. LED Current and Temperature




Fig. 6 - Collector Emitter Current vs. Temperature and LED Current




Fig. 9 - Normalized Photocurrent vs. I<sub>F</sub> and Temperature






Fig. 10 - Normalized Non-Saturated  $h_{FE}$  vs. Base Current and Temperature




i4n25\_13

Fig. 13 - Switching Timing




i4n25\_11

Fig. 11 - Normalized HFE vs. Base Current and Temperature



i4n25\_14

Fig. 14 - Switching Schematic






i4n25\_12

Fig. 12 - Propagation Delay vs. Collector Load Resistor







PACKAGE DIMENSIONS in millimeters

DIP-6



Option 9





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.