

PNP SWITCHING SILICON TRANSISTOR

Qualified per MIL-PRF-19500/396

Devices

2N3762	2N3763	2N3764	2N3765
2N3762L	2N3763L		

Qualified Level

JAN
JANTX
JANTXV

MAXIMUM RATINGS

Ratings	Symbol	2N3762* 2N3764	2N3763* 2N3765	Unit
Collector-Emitter Voltage	V_{CEO}	40	60	Vdc
Collector-Base Voltage	V_{CBO}	40	60	Vdc
Emitter-Base Voltage	V_{EBO}	5.0		Vdc
Collector Current	I_C	1.5		Adc
		2N3762* ¹ 2N3763*	2N3764 ² 2N3765	
Total Power Dissipation @ $T_A = +25^{\circ}C$	P_T	1.0	0.5	W
Operating & Storage Junction Temp. Range	T_{op}, T_{stg}	-55 to +200		$^{\circ}C$


THERMAL CHARACTERISTICS

Characteristics	Symbol	Max.		Unit
		2N3762* 2N3763*	2N3764 2N3765	
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	60	88	$^{\circ}C/W$

*Electrical characteristics for "L" suffix devices are identical to the "non L" corresponding devices

1) Derate linearly at 5.71 mW/ $^{\circ}C$ for $T_A > +25^{\circ}C$

2) Derate linearly at 2.86 mW/ $^{\circ}C$ for $T_A > +25^{\circ}C$



*See appendix A for package outline

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

Characteristics	Symbol	Min.	Max.	Unit
-----------------	--------	------	------	------

OFF CHARACTERISTICS

Collector-Emitter Breakdown Current $I_C = 10$ mAdc	2N3762, 2N3764 2N3763, 2N3765	$V_{(BR)CEO}$	40 60	Vdc
Collector-Base Cutoff Current $V_{CB} = 20$ Vdc $V_{CB} = 30$ Vdc $V_{CB} = 40$ Vdc $V_{CB} = 60$ Vdc	2N3762, 2N3764 2N3763, 2N3765 2N3762, 2N3764 2N3763, 2N3765	I_{CBO}		100 100 10 10 η Adc μ Adc

2N3762, L, 2N3763, L, 2N3764, 2N3765 JAN SERIES

ELECTRICAL CHARACTERISTICS (con't)

Characteristics	Symbol	Min.	Max.	Unit
Collector-Emitter Cutoff Current $V_{EB} = 2.0 \text{ Vdc}, V_{CE} = 20 \text{ Vdc}$ $V_{EB} = 2.0 \text{ Vdc}, V_{CE} = 30 \text{ Vdc}$	I_{CEX}		100	ηAdc
2N3762, 2N3764 2N3763, 2N3765			100	
Emitter-Base Cutoff Current $V_{EB} = 2.0 \text{ Vdc}$ $V_{EB} = 5.0 \text{ Vdc}$	I_{EBO}		200	ηAdc
All Types			10	
2N3762, 2N3764 2N3763, 2N3765			10	

ON CHARACTERISTICS (3)

Forward-Current Transfer Ratio $I_C = 10 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}$ $I_C = 150 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}$ $I_C = 500 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}$ $I_C = 1.0 \text{ Adc}, V_{CE} = 1.5 \text{ Vdc}$	h_{FE}		35	
2N3762, 2N3764			40	140
2N3763, 2N3765			40	120
2N3762, 2N3764			20	80
2N3763, 2N3765			30	20
Collector-Emitter Saturation Voltage $I_C = 10 \text{ mAdc}, I_B = 1.0 \text{ mAdc}$ $I_C = 150 \text{ mAdc}, I_B = 15 \text{ mAdc}$ $I_C = 500 \text{ mAdc}, I_B = 50 \text{ mAdc}$ $I_C = 1.0 \text{ Adc}, I_B = 100 \text{ mAdc}$	$V_{CE(sat)}$		0.1	Vdc
			0.22	
			0.5	
			0.9	
Base-Emitter Saturation Voltage $I_C = 10 \text{ mAdc}, I_B = 1.0 \text{ mAdc}$ $I_C = 150 \text{ mAdc}, I_B = 15 \text{ mAdc}$ $I_C = 500 \text{ mAdc}, I_B = 50 \text{ mAdc}$ $I_C = 1.0 \text{ Adc}, I_B = 100 \text{ mAdc}$	$V_{BE(sat)}$		0.8	Vdc
			1.0	
			1.2	
			1.4	
		0.9		

DYNAMIC CHARACTERISTICS

Forward Current Transfer Ratio, Magnitude $I_C = 50 \text{ mAdc}, V_{CE} = 10 \text{ Vdc}, f = 100 \text{ MHz}$	$ h_{fe} $		1.8	6.0
2N3762, 2N3764 2N3763, 2N3765			1.5	6.0
Output Capacitance $V_{CB} = 10 \text{ Vdc}, I_E = 0, 100 \text{ kHz} \leq f \leq 1.0 \text{ MHz}$	C_{obo}		25	pF
Input Capacitance $V_{EB} = 0.5 \text{ Vdc}, I_C = 0, 100 \text{ kHz} \leq f \leq 1.0 \text{ MHz}$	C_{ibo}		80	pF

SWITCHING CHARACTERISTICS

Delay Time	$V_{CC} = 30 \text{ Vdc}, V_{EB} = 0,$ $I_C = 1.0 \text{ mAdc}, I_{B1} = 100 \text{ mAdc}$	t_d		8.0	ηs
Rise Time		t_r		35	ηs
Storage Time	$V_{CC} = 30 \text{ Vdc}, V_{EB} = 0,$ $I_C = 1.0 \text{ mAdc}, I_{B1} = 100 \text{ mAdc}$	t_s		80	ηs
Fall Time		t_f		35	ηs

(3) Pulse Test: Pulse Width = 300 μs , Duty Cycle \leq 2.0%.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

[2N3763](#) [2N3763L](#) [2N3765](#) [2N3762L](#) [2N3764](#) [2N3762](#) [Jantx2N3762](#) [2N3763U4](#) [Jantxv2N3763](#) [Jantx2N3763](#)
[Jantxv2N3764](#) [Jan2N3762](#) [Jantx2N3764](#) [Jan2N3763](#) [Jantx2N3762L](#) [JANTX2N3762U4](#) [Jantx2N3763L](#)
[JANTX2N3763U4](#) [JANTX2N3764L](#) [JANTX2N3764U4](#) [JANS2N3765L](#) [JANS2N3765U4](#) [JANS2N3765](#)
[JANS2N3762U4](#) [JANS2N3763](#) [JANS2N3763U4](#) [JANS2N3764](#) [JANS2N3764L](#) [JANS2N3764U4](#) [JAN2N3764L](#)
[JAN2N3764U4](#) [Jan2N3765](#) [JAN2N3765L](#) [JAN2N3765U4](#) [JANTXV2N3765U4](#) [Jan2N3762L](#) [JAN2N3762U4](#)
[Jan2N3763L](#) [JAN2N3763U4](#) [Jan2N3764](#) [Jantxv2N3763L](#) [JANTXV2N3763U4](#) [JANTXV2N3764L](#) [JANTXV2N3764U4](#)
[Jantxv2N3765](#) [JANTXV2N3765L](#) [Jantx2N3765](#) [JANTX2N3765L](#) [JANTX2N3765U4](#) [Jantxv2N3762](#) [Jantxv2N3762L](#)
[JANTXV2N3762U4](#) [JANTX2N3763S](#)