

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile panel with 8,9 cm / 3,5"-TFT display (analog resistive (polyester)), 65536 colors, Arm9™, 200 MHz, 1x USB Host 2.0, without, Windows® CE 5.0 and user software: TSvisRT. (bus system: MPI)

Commercial data

Item number	2401380
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR17
Product key	DRCAEB
GTIN	4055626148687
Weight per piece (including packing)	2,500 g
Weight per piece (excluding packing)	2,500 g
Customs tariff number	84713000
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	8,9 cm / 3,5"-TFT
Screen resolution	240 x 320 Pixel(s)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	320 cd/m ² typical (adjustable)
MTBF	30000 h
Color spectrum	65536 colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	80.00 °
Reading angle bottom	60.00 °

Software

User software	TSvisRT
---------------	---------

Interfaces

Interfaces	1x USB Host 2.0
Optional interfaces	none
Network	without
Bus system	MPI

System properties

User software	TSvisRT
---------------	---------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Typical current consumption	0.25 A
-----------------------------	--------

Real-time clock

Realtime clock	Yes
----------------	-----

Supply

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Power supply unit	24 V DC \pm 20 %
-------------------	--------------------

Mounting

Mounting type	none
---------------	------

Material specifications

Material front plate	Plastic
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	145 mm / 265 mm / 67 mm
------------------------	-------------------------

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Classifications

ECLASS

ECLASS-11.0

27330201

UNSPSC

UNSPSC 21.0

43211712

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Environmental product compliance

China RoHS	Environmentally Friendly Use Period = 15; For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"
------------	---

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Accessories

TOUCH PEN - Touch pen

2701379

<https://www.phoenixcontact.com/us/products/2701379>



Touch pen for analog-resistive HMI, silver coated. Delivery includes self-adhesive pen holder.

USB FLASH DRIVE - USB memory stick

2402809

<https://www.phoenixcontact.com/us/products/2402809>



USB memory stick, 8 GB

HT06AT/732050/311/00100 S00001 - Mobile panel



2401380

<https://www.phoenixcontact.com/us/products/2401380>

HMI BATTERY - Battery/accumulator

2701383

<https://www.phoenixcontact.com/us/products/2701383>

Lithium battery



WH HT06AT - Holder

2401468

<https://www.phoenixcontact.com/us/products/2401468>



Mounting material for fastening the handheld panel (HP) to the wall using magnets.

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com