



LETTERING: BLANK

REV	Change record	Change the date
A/0	Initial issue	2022-12-15



NO.	Cable length (L)	Cable Tolerance (T)
1	1500mm	20mm
2	2000mm	20mm
3	3000mm	30mm
4	5000mm	50mm

Test Conditions:

- 100% open & short circuit test;
- Insulation Resistance: 10Mohm (MIN);
- Conduction Resistance: 5ohm (MAX) at 300V DC/0.01S .
- Test requirement: 4K (3840*2160)@60Hz

NO.	The material content	unit	quantity
⑥	PROTECTIVE CASE: PE (polyethylene)	PCS	2
⑤	SHELL:ZINC ALLOY SHELL, SILVER	PCS	2
④	OVER MOLDING:45P PVC(Polyvinyl chloride), BLACK	g	N/A
③	INNER MOLDING:LD PE (polyethylene)	g	N/A
②	CONN:HDMI 19PIN MALE SOLDERING TYPE GOLD PLATED, INSULATION: RED	PCS	2
①	CABLE:HDMI2.0V (1P+DW+AL/MY)*5P+4C+ADB OD:7.3, PVC JACKET, BLACK	mm	L

VCOM INTERNATIONAL LTD.

TITLE	HDMI A/M to A/M, 2.0V	CUSTOMER		UNIT	mm	PAGE: 1 of 1
PART NO.	AC-139	CUSTOMER NO.		SCALE		
PRODUCT NO.	CG579	REV:	A/0	DATE	2022-12-15	
APPROVED BY: XIANG	CHECKED BY:		DRAWN BY: CHEN			