

DC COMPONENTS CO., LTD.

RECTIFIER SPECIALISTS

SMF5.0A THRU SMF200A

TECHNICAL SPECIFICATIONS OF TRANSIENT VOLTAGE SUPPRESSOR VOLTAGE RANGE - 5.0 to 220Volts PEAK PULSE POWER - 200 Watts

FEATURES


- * Glass passivated junction
- * 200 Watts Peak Pulse Power capability on 10/1000 μs waveform
- * Excellent clamping capability
- * Low inductance
- * Fast response time

MECHANICAL DATA

- * Case: Molded plastic
- * Epoxy: UL 94V-0 rate flame retardant
- * Lead: MIL-STD-202E, Method 208 guaranteed
- * Polarity: Color band denotes positive end (cathode) except bidirectional types
- * Mounting position: Any
- * Weight: 0.017 gram

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.



DEVICES FOR BIPOLAR APPLICATIONS

For Bidirectional use C or CA suffix (e.g. SMF5.0C, SMF220CA). Electrical characteristics apply in both directions


	SYMBOL	VALUE	UNITS
Peak Pulse Power Dissipation on 10/1000 μs waveform (Note1,FIG.1)	Реем	200	Watts
Steady State Power Dissipation at TA = 25°C Lead Lengths .375"(9.5mm) (Note 2)	P _{M(AV)}	1.0	Watts
Peak Forward Surge Current, 8.3ms single half sine-wave superimposed on rated load(JEDEC Method) (Note 3)	Ігэм	20	Amps
Operating and Storage Temperature Range	TJ, Tstg	-55 to + 150	°C


NOTES: 1. Non-repetitive current pulse, per Fig. 3 and derated above TA = 25° C per Fig. 2.


- 2. Mounted on Copper Leaf area of 0.2 X 0.2"(5.0 X 5.0mm) per Fig. 5
- 3. 8.3ms single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum.


REV-3,MAR,2017 1 www.dccomponents.com


RATING AND CHARACTERISTIC CURVES (SMF5.0A THRU SMF220CA)











SMF (200W) SERIES TRANSIENT VOLTAGE SUPPRESSORS

	Reverse Breakdown			Maximum		Maximum	Maximum	
	Stand-off			Test	Reve	erse	Clamping	Peak
		Volt	•	Current	Leak	age	Voltage	Pulse
TYPE	Voltage	w w	lτ		@ VRWM		@ IPP	Current
		V	RP.		Is	IR		
	VRWM	Min.	Max.	l I	UNI-	BI-	Vc	IPР
	V	V	V V	mA	μΑ	μΑ	V	А
SMF5.0A	5.0	6.40	7.00	10	400	800	9.2	21.74
SMF6.0A	6.0	6.67	7.37	10	400	800	10.2	19.42
SMF6.5A	6.5	7.22	7.98	10	250	500	11.2	17.86
SMF7.0A	7.0	7.78	8.60	10	100	200	12.0	16.67
SMF7.5A	7.5	8.33	9.21	1	50	100	12.9	15.50
SMF8.0A	8.0	8.89	9.83	1	25	50	13.6	14.71
SMF8.5A	8.5	9.44	10.4	1	10	20	14.4	13.89
SMF9.0A	9.0	10.0	11.1	1	5	10	15.4	12.99
SMF10A	10	11.1	12.3	1	2.		17.0	11.76
SMF11A	11	12.2	13.5	1	2.		18.2	10.99
SMF12A	12	13.3	14.7	1			19.9	10.05
SMF13A	13	14.4	15.9	1			21.5	9.30
SMF14A	14	15.6	17.2	1	1		23.2	8.62
SMF14A SMF15A	15	16.7	18.5	1			23.2	8.20
				1	1			
SMF16A SMF17A	16 17	17.8 18.9	19.7 20.9	1	1		26.0 27.6	7.69 7.25
SMF18A				1	1			
SMF19A	18 19	20.0	22.1	1	1		29.2 30.6	6.85
			23.3		1			6.54
SMF20A	20	22.2	24.5	1	1		32.4	6.17
SMF22A	22	24.4	26.9	1	1		35.5	5.63
SMF24A	24	26.7	29.5	1	1		38.9	5.14
SMF26A	26	28.9	31.9	1	1		42.1	4.75
SMF28A	28	31.1	34.4	1	1		45.4	4.41
SMF30A	30	33.3	36.8	1	1		48.4	4.13
SMF33A	33	36.7	40.6	1	1		53.3	3.75
SMF36A	36	40.0	44.2	1	1		58.1	3.44
SMF40A	40	44.4	49.1	1	1		64.5	3.10
SMF43A	43	47.8	52.8	1	1		69.4	2.88
SMF45A	45	50.0	55.3	1	1		72.7	2.75
SMF48A	48	53.3	58.9	1	1		77.4	2.58
SMF51A	51	56.7	62.7	1	1		82.4	2.43
SMF54A	54	60.0	66.3	1	1		87.1	2.30
SMF58A	58	64.4	71.2	1	1		93.6	2.14
SMF60A	60	66.7	73.7	1	1		96.8	2.07
SMF64A	64	71.1	78.6	1	1		103	1.94
SMF70A	70	77.8	86.0	1	1		113	1.77
SMF75A	75	83.3	92.1	1	1		121	1.65
SMF78A	78	86.7	95.8	1	1		126	1.59
SMF80A	80	88.8	97.6	1	1		129	1.55
SMF85A	85	94.4	104	1	1		137	1.46
SMF90A	90	100	111	1	1		146	1.37
SMF100A	100	111	123	1	1		162	1.23
SMF110A	110	122	135	1	1		177	1.13
SMF120A	120	133	147	1	1		193	1.04
SMF130A	130	144	159	1	1		209	0.96
SMF140A	140	155	171	1	1		224	0.89
SMF150A	150	167	185	1	1		243	0.82
SMF160A	160	178	197	1	1		259	0.77
SMF170A	170	189	209	1	1		275	0.73
SMF180A	180	200	220	1	1		292	0.68
SMF190A	190	211	232	1	1		308	0.65
SMF200A	200	224	247	1	1		324	0.62
SMF220A	220	246	272	1	1		356	0.56

Disclaimer

Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold *DC COMPONENTS* are harmless against all damages.

DC COMPONENTS' disclaims any and all liability arising out of the application or use of any product, including consequential or incidental damages. Statement regarding the suitability of products for certain types of applications are based on DC COMPONENTS's knowledge of typical requirements that are often placed on DC COMPONENTS products in generic applications. Such statements are not binding statements about the suitability of products for aparticular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application.

DC COMPONENTS reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein, and disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product. Parameters provided in datasheets and specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify *DC COMPONENTS*'s terms and conditions of purchase, including but not limited to the warranty expressed therein.

Unless otherwise in writing, *DC COMPONENTS* products are intended for use as general electronic components in standard applications (eg: Consumer electronic, Computer equipment, Office equipment, etc.), and not recommended for use in a high specific application where a failure or malfunction of the device could result in human injury or death (eg: Aerospace equipment, Submarine cables, Combustion equipment, Safety devices, Life support systems, etc.)

Customers using or selling *DC COMPONENTS* products not expressly indicated for use in such applications do so at their own risk. If customer intended to use *DC COMPONENTS* standard quality grade devices for applications not envisioned by *DC COMPONENTS*, please contact our sales representatives in advance.

