Low Power, Standard Frequency Oscillator



Features

- 51 standard frequencies between 3.75 MHz and 77.76 MHz
- 100% pin-to-pin drop-in replacement to quartz-based XO
- Excellent total frequency stability as low as ±20 PPM
- Low power consumption of 3.6 mA typical
- Standby mode for longer battery life
- Fast startup time of 5 ms
- LVCMOS/HCMOS compatible output
- Industry-standard packages: 2.0 x 1.6, 2.5 x 2.0, 3.2 x 2.5, 5.0 x 3.2, 7.0 x 5.0 mm x mm
- Instant samples with Time Machine II and field programmable oscillators
- Pb-free, RoHS and REACH compliant

Applications

- Ideal for DSC, DVC, DVR, IP CAM, Tablets, e-Books, SSD, GPON, EPON, etc
- Ideal for high-speed serial protocols such as: USB, SATA, SAS, Firewire, 100M / 1G / 10G Ethernet, etc.







Electrical Characteristics^[1]

Parameter and Conditions	Symbol	Min.	Тур.	Max.	Unit	Condition
			F	requency R	ange	<u>'</u>
Output Frequency Range	f	(Refer to th	e frequency	list page 10)	MHz	51 standard frequencies between 3.75 MHz and 77.76 MHz
	· L		Freque	ncy Stability	and Aging	9
Frequency Stability	F_stab	-20	-	+20	PPM	Inclusive of Initial tolerance at 25°C, 1st year aging at 25°C, and
		-25	-	+25	PPM	variations over operating temperature, rated power supply voltage and load.
		-50	_	+50	PPM	voltage and load.
	•		Operati	ng Tempera	ture Range	e
Operating Temperature Range	T_use	-20	_	+70	°C	Extended Commercial
		-40	-	+85	°C	Industrial
		S	upply Voltag	ge and Curr	ent Consui	mption
Supply Voltage	Vdd	1.62	1.8	1.98	V	Contact SiTime for 1.5V support
		2.25	2.5	2.75	V	
		2.52	2.8	3.08	V	
		2.7	3.0	3.3	V	
		2.97	3.3	3.63	V	
		2.25	-	3.63	V	
Current Consumption	ldd	-	3.8	4.5	mA	No load condition, f = 20 MHz, Vdd = 2.8V to 3.3V
		-	3.6	4.2	mA	No load condition, f = 20 MHz, Vdd = 2.5V
		-	3.4	3.9	mA	No load condition, f = 20 MHz, Vdd = 1.8V
OE Disable Current	I_OD	-	-	4	mA	Vdd = 2.5V to 3.3V, OE = GND, output is Weakly Pulled Down
		-	-	3.8	mA	Vdd = 1.8 V. OE = GND, output is Weakly Pulled Down
Standby Current	I_std	-	2.6	4.3	μА	ST = GND, Vdd = 2.8V to 3.3V, Output is Weakly Pulled Down
		-	1.4	2.5	μА	ST = GND, Vdd = 2.5V, Output is Weakly Pulled Down
		-	0.6	1.3	μΑ	ST = GND, Vdd = 1.8V, Output is Weakly Pulled Down
			LVCMOS	Output Ch	aracteristic	CS
Duty Cycle	DC	45	-	55	%	All Vdds
Rise/Fall Time	Tr, Tf	-	1	2	ns	Vdd = 2.5V, 2.8V, 3.0V or 3.3V, 20% - 80%
		-	1.3	2.5	ns	Vdd =1.8V, 20% - 80%
		-	-	2	ns	Vdd = 2.25V - 3.63V, 20% - 80%
Output High Voltage	VOH	90%	-	-	Vdd	IOH = -4 mA (Vdd = 3.0V or 3.3V) IOH = -3 mA (Vdd = 2.8V and Vdd = 2.5V) IOH = -2 mA (Vdd = 1.8V)
Output Low Voltage	VOL	-	-	10%	Vdd	IOL = 4 mA (Vdd = 3.0V or 3.3V) IOL = 3 mA (Vdd = 2.8V and Vdd = 2.5V) IOL = 2 mA (Vdd = 1.8V)
	•		Inp	out Characte	eristics	
Input High Voltage	VIH	70%	-	-	Vdd	Pin 1, OE or ST
Input Low Voltage	VIL	-	-	30%	Vdd	Pin 1, OE or ST
Input Pull-up Impedence	Z_in	-	87	100	kΩ	Pin 1, OE logic high or logic low, or ST logic high
		2	_	_	MΩ	Pin 1, ST logic low

Note:

SiTime Corporation 990 Almanor Avenue Sunnyvale, CA 94085 (408) 328-4400 www.sitime.com Rev. 1.2

Downloaded from Arrow.com.

^{1.} All electrical specifications in the above table are specified with 15 pF output load and for all Vdd(s) unless otherwise stated.

Low Power, Standard Frequency Oscillator




Electrical Characteristics^[1] (continued)

Parameter and Conditions	Symbol	Min.	Тур.	Max.	Unit	Condition		
Startup and Resume Timing								
Startup Time	T_start	_	_	5	ms	Measured from the time Vdd reaches its rated minimum value		
Enable/Disable Time	T_oe	_	_	130	ns	f = 110 MHz. For other frequencies, T_oe = 100 ns + 3 * cycles		
Resume Time	T_resume	_	_	5	ms	Measured from the time ST pin crosses 50% threshold		
Startup Time	T_start	_	-	5	ms	Measured from the time Vdd reaches its rated minimum value		
			•	Jitter	•			
RMS Period Jitter	T_jitt	_	1.76	3	ps	f = 75 MHz, Vdd = 2.5V, 2.8V, 3.0V or 3.3V		
		_	1.78	3	ps	f = 75 MHz, Vdd = 1.8V		
RMS Phase Jitter (random)	T_phj	_	0.5	0.9	ps	f = 75 MHz, Integration bandwidth = 900 kHz to 7.5 MHz		
		-	1.3	2	ps	f = 75 MHz, Integration bandwidth = 12 kHz to 20 MHz		

Notes:

Pin Description

Pin	Symbol		Functionality
1	OE/ ST	Output Enable	H or Open ^[2] : specified frequency output L: output is high impedance. Only output driver is disabled.
'		Standby	H or Open ^[2] : specified frequency output L: output is low (weak pull down). Device goes to sleep mode. Supply current reduces to I_std.
2	GND	Power	Electrical ground ^[3]
3	OUT	Output	Oscillator output
4	VDD	Power	Power supply voltage ^[3]



Notes:

2. A pull-up resistor of <10 k Ω between OE/ $\overline{\text{ST}}$ pin and Vdd is recommended in high noise environment. 3. A capacitor value of 0.1 μF between Vdd and GND is required.

Absolute Maximum

Attempted operation outside the absolute maximum ratings of the part may cause permanent damage to the part. Actual performance of the IC is only guaranteed within the operational specifications, not at absolute maximum ratings.

Parameter	Min.	Max.	Unit
Storage Temperature	-65	150	°C
VDD	-0.5	4	V
Electrostatic Discharge	-	2000	V
Soldering Temperature (follow standard Pb free soldering guidelines)	-	260	°C
Junction Temperature	-	150	°C

Thermal Consideration

Package	θJA, 4 Layer Board (°C/W)	θJA, 2 Layer Board (°C/W)	θJC, Bottom (°C/W)
7050	191	263	30
5032	97	199	24
3225	109	212	27
2520	117	222	26
2016	124	227	26

Environmental Compliance

Parameter	Condition/Test Method		
Mechanical Shock	MIL-STD-883F, Method 2002		
Mechanical Vibration	MIL-STD-883F, Method 2007		
Temperature Cycle	JESD22, Method A104		
Solderability	MIL-STD-883F, Method 2003		
Moisture Sensitivity Level	MSL1 @ 260°C		

^{1.} All electrical specifications in the above table are specified with 15 pF output load and for all Vdd(s) unless otherwise stated.



Test Circuit and Waveform^[4]




Figure 1. Test Circuit

Note:

4. Duty Cycle is computed as Duty Cycle = TH/Period.

tr — tf 80% Vdd 50% 20% Vdd High Pulse (TH) Period Period

Figure 2. Waveform

Timing Diagram




Figure 3. Startup Timing (OE/ST Mode)






Figure 4. Standby Resume Timing (ST Mode Only)





T_OE: Time to put the output drive in High Z mode

Figure 5. OE Enable Timing (OE Mode Only)

Figure 5. OE Disable Timing (OE Mode Only)

Notes:

- 5. SiT1602 supports "no runt" pulses and "no glitch" output during startup or resume.
- 6. SiT1602 supports gated output which is accurate within rated frequency stability from the first cycle.



Performance Plots





Figure 7. IDD vs Frequency






Figure 9. RMS Phase Jitter vs Frequency (12 kHz to 20 MHz Integration Bandwidth)




Figure 10. RMS Phase Jitter vs Frequency (900 kHz to 20 MHz Integration Bandwidth)




Figure 11. Duty Cycle vs Frequency




Figure 12. Rise Time vs Temperature, 20 MHz Output

Note:

7. All plots are measured with 15 pF load at room temperature, unless otherwise stated.

Low Power, Standard Frequency Oscillator



Programmable Drive Strength

The SiT1602 includes a programmable drive strength feature to provide a simple, flexible tool to optimize the clock rise/fall time for specific applications. Benefits from the programmable drive strength feature are:

- Improves system radiated electromagnetic interference (EMI) by slowing down the clock rise/fall time
- Improves the downstream clock receiver's (RX) jitter by decreasing (speeding up) the clock rise/fall time.
- Ability to drive large capacitive loads while maintaining full swing with sharp edge rates.

For more detailed information about rise/fall time control and drive strength selection, see the SiTime Applications Note section; http://www.sitime.com/support/application-notes.

EMI Reduction by Slowing Rise/Fall Time

Figure 13 shows the harmonic power reduction as the rise/fall times are increased (slowed down). The rise/fall times are expressed as a ratio of the clock period. For the ratio of 0.05, the signal is very close to a square wave. For the ratio of 0.45, the rise/fall times are very close to near-triangular waveform. These results, for example, show that the 11th clock harmonic can be reduced by 35 dB if the rise/fall edge is increased from 5% of the period to 45% of the period.




Figure 13. Harmonic EMI reduction as a Function of Slower Rise/Fall Time

Jitter Reduction with Faster Rise/Fall Time

Power supply noise can be a source of jitter for the downstream chipset. One way to reduce this jitter is to increase rise/fall time (edge rate) of the input clock. Some chipsets would require faster rise/fall time in order to reduce their sensitivity to this type of jitter. The SiT1602 provides up to 3 additional high drive strength settings for very fast rise/fall time. Refer to the Rise/Fall Time Tables to determine the proper drive strength.

High Output Load Capability

The rise/fall time of the input clock varies as a function of the actual capacitive load the clock drives. At any given drive strength, the rise/fall time becomes slower as the output load increases. As an example, for a 3.3V SiT1602 device with default drive strength setting, the typical rise/fall time is 1ns for 15 pF output load. The typical rise/fall time slows down to 2.6ns when the output load increases to 45 pF. One can

choose to speed up the rise/fall time to 1.68ns by then increasing the drive strength setting on the SiT1602.

The SiT1602 can support up to 60 pF or higher in maximum capacitive loads with up to 3 additional drive strength settings. Refer to the Rise/Tall Time Tables to determine the proper drive strength for the desired combination of output load vs. rise/fall time

SiT1602 Drive Strength Selection

Tables 1 through 5 define the rise/fall time for a given capacitive load and supply voltage.

- 1. Select the table that matches the SiT1602 nominal supply voltage (1.8V, 2.5V, 2.8V, 3.0V, 3.3V).
- Select the capacitive load column that matches the application requirement (5 pF to 60 pF)
- 3. Under the capacitive load column, select the desired rise/fall times.
- 4. The left-most column represents the part number code for the corresponding drive strength.
- Add the drive strength code to the part number for ordering purposes.

Calculating Maximum Frequency

Based on the rise and fall time data given in Tables 1 through 4, the maximum frequency the oscillator can operate with guaranteed full swing of the output voltage over temperature as follows:

Max Frequency =
$$\frac{1}{5 \times \text{Trf}_{20/80}}$$

Where Trf_20/80 is the typical rise/fall time at 20% to 80% Vdd $\,$

Example 1

Calculate f_{MAX} for the following condition:

- Vdd = 1.8V (Table 1)
- Capacitive Load: 30 pF
- Desired Tr/f time = 3 ns (rise/fall time part number code = E)

Part number for the above example:

SiT1602AIE12-18E-66.666660



Drive strength code is inserted here. Default setting is "-"

Low Power, Standard Frequency Oscillator



Rise/Fall Time (20% to 80%) vs C_{LOAD} Tables

	Rise/Fall Time Typ (ns)					
Drive Strength \ C _{LOAD}	5 pF	15 pF	30 pF	45 pF	60 pF	
L	6.16	11.61	22.00	31.27	39.91	
Α	3.19	6.35	11.00	16.01	21.52	
R	2.11	4.31	7.65	10.77	14.47	
В	1.65	3.23	5.79	8.18	11.08	
T	0.93	1.91	3.32	4.66	6.48	
Е	0.78	1.66	2.94	4.09	5.74	
U	0.70	1.48	2.64	3.68	5.09	
F or "-": default	0.65	1.30	2.40	3.35	4.56	

Tahla 1	Vdd = 1	8V Rice	/Fall Tir	nae for	Specific	C

Rise/Fall Time Typ (ns)								
Drive Strength \ C _{LOAD}	Drive Strength \ C _{LOAD} 5 pF 15 pF 30 pF 45 pF 60 pF							
L	4.13	8.25	12.82	21.45	27.79			
Α	2.11	4.27	7.64	11.20	14.49			
R	1.45	2.81	5.16	7.65	9.88			
В	1.09	2.20	3.88	5.86	7.57			
T	0.62	1.28	2.27	3.51	4.45			
E or "-": default	0.54	1.00	2.01	3.10	4.01			
U	0.43	0.96	1.81	2.79	3.65			
F	0.34	0.88	1.64	2.54	3.32			

Table 2. Vdd = 2.5V Rise/Fall Times for Specific C_{LOAD}

Rise/Fall Time Typ (ns)								
Drive Strength \ C _{LOAD}	5 pF	15 pF	30 pF	45 pF	60 pF			
L	3.77	7.54	12.28	19.57	25.27			
Α	1.94	3.90	7.03	10.24	13.34			
R	1.29	2.57	4.72	7.01	9.06			
В	0.97	2.00	3.54	5.43	6.93			
T	0.55	1.12	2.08	3.22	4.08			
E or "-": default	0.44	1.00	1.83	2.82	3.67			
U	0.34	0.88	1.64	2.52	3.30			
F	0.29	0.81	1.48	2.29	2.99			

Table 3. Vdd = 2.8V Rise/Fall Times for Specific C_{LOAD}

	Rise/Fall Time Typ (ns)							
Drive Strength \ C _{LOAD}	5 pF	15 pF	30 pF	45 pF	60 pF			
L	3.60	7.21	11.97	18.74	24.30			
Α	1.84	3.71	6.72	9.86	12.68			
R	1.22	2.46	4.54	6.76	8.62			
В	0.89	1.92	3.39	5.20	6.64			
T or "-": default	0.51	1.00	1.97	3.07	3.90			
E	0.38	0.92	1.72	2.71	3.51			
U	0.30	0.83	1.55	2.40	3.13			
F	0.27	0.76	1.39	2.16	2.85			

Table 4. Vdd = 3.0V Rise/Fall Times for Specific C_{LOAD}

Rise/Fall Time Typ (ns)								
Drive Strength $\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \$	Orive Strength \ C _{LOAD} 5 pF 15 pF 30 pF 45 pF 60 pF							
L	3.39	6.88	11.63	17.56	23.59			
Α	1.74	3.50	6.38	8.98	12.19			
R	1.16	2.33	4.29	6.04	8.34			
В	0.81	1.82	3.22	4.52	6.33			
T or "-": default	0.46	1.00	1.86	2.60	3.84			
E	0.33	0.87	1.64	2.30	3.35			
U	0.28	0.79	1.46	2.05	2.93			
F	0.25	0.72	1.31	1.83	2.61			

Table 5. Vdd = 3.3V Rise/Fall Times for Specific C_{LOAD}

Low Power, Standard Frequency Oscillator



Instant Samples with Time Machine and Field Programmable Oscillators

SiTime supports a field programmable version of the SiT1602 low power oscillator for fast prototyping and real time customization of features. The <u>field programmable devices</u> (FP devices) are available for all five standard SiT1602 package sizes and can be configured to one's exact specification using the <u>Time Machine II</u>, an USB powered MEMS oscillator programmer.

Customizable Features of the SiT1602 FP Devices Include

- 51 standard frequencies between 3.75 MHz and 77.76MHz (Refer to the frequency list page 10)
- Three frequency stability options, ±20 PPM, ±25 PPM, ±50 PPM
- Two operating temperatures, -20 to 70°C or -40 to 85°C
- Five supply voltage options, 1.8V, 2.5V, 2.8V, 3.0V, 3.3V and 2.25 to 3.65V continuous

· Output drive strength


For more information regarding SiTime's field programmable solutions, visit http://www.sitime.com/fp-devices.

SiT1602 is typically factory-programmed per customer ordering codes for volume delivery.

Low Power, Standard Frequency Oscillator



Dimensions and Patterns




8. Top marking: Y denotes manufacturing origin and XXXX denotes manufacturing lot number. The value of "Y" will depend on the assembly location of the device. 9. A capacitor of value 0.1 µF between Vdd and GND is required.

Low Power, Standard Frequency Oscillator



Dimensions and Patterns



Notes:


- 10. Top marking: Y denotes manufacturing origin and XXXX denotes manufacturing lot number. The value of "Y" will depend on the assembly location of the device.
- 11. A capacitor of value 0.1 µF between Vdd and GND is required.

Low Power, Standard Frequency Oscillator



Ordering Information

The Part No. Guide is for reference only. To customize and build an exact part number, use the SiTime Part Number Generator.



Supported Frequencies^[12]

3.57 MHz	4 MHz	4.096 MHz	6 MHz	7.3728 MHz	8.192 MHz	10 MHz	12 MHz	14 MHz
18.432 MHz	19.2 MHz	20 MHz	24 MHz	24.576 MHz	25 MHz	25.000625 MHz	26 MHz	27 MHz
28.6363 MHz	30 MHz	31.25 MHz	32.768 MHz	33 MHz	33.3 MHz	33.33 MHz	33.333 MHz	33.3333 MHz
33.33333 MHz	37.5 MHz	38 MHz	38.4 MHz	40 MHz	40.5 MHz	48 MHz	50 MHz	54 MHz
60 MHz	62.5 MHz	65 MHz	66 MHz	66.6 MHz	66.66 MHz	66.666 MHz	66.6666 MHz	66.66666 MHz
72 MHz	74.175824 MHz	74.176 MHz	74.25 MHz	75 MHz	77.76 MHz			

Note:

Ordering Codes for Supported Tape & Reel Packing Method^[13]

Device Size	8 mm T&R (3ku)	8 mm T&R (1ku)	12 mm T&R (3ku)	12 mm T&R (1ku)	16 mm T&R (3ku)	16 mm T&R (1ku)
2.0 x 1.6 mm	D	E	-	-	-	-
2.5 x 2.0 mm	D	E	-	-	-	-
3.2 x 2.5 mm	D	E	-	-	-	-
5.0 x 3.2 mm	-	-	Т	Y	-	-
7.0 x 5.0 mm	-	-	-	-	Т	Y

Note:

^{12.} Contact SiTime for frequencies that are not listed in the above table.

^{13.} For "-", contact SiTime for availability.

Low Power, Standard Frequency Oscillator



Additional Information

Document	Description	Download Link
Time Machine II	MEMS oscillator programmer	http://www.sitime.com/support/time-machine-oscillator-programmer
Field Programmable Oscillators	Devices that can be programmable in the field by Time Machine II	http://www.sitime.com/products/field-programmable-oscillators
Manufacturing Notes	Tape & Reel dimension, reflow profile and other manufacturing related info	http://www.sitime.com/component/docman/doc_download/85-manu facturing-notes-for-sitime-oscillators
Qualification Reports	RoHS report, reliability reports, composition reports	http://www.sitime.com/support/quality-and-reliability
Performance Reports	Additional performance data such as phase noise, current consumption and jitter for selected frequencies	http://www.sitime.com/support/performance-measurement-report
Termination Techniques	Termination design recommendations	http://www.sitime.com/support/application-notes
Layout Techniques	Layout recommendations	http://www.sitime.com/support/application-notes

Revision History

Version	Release Date	Change Summary
1.0	2/8/13	Preliminary Information
1.1	7/24/13	 Added programmable drive strength Added the Time Machine and FP device info Added performance plots Removed all footnotes related to softedge
1.2	3/26/15	Added 20 MHz to frequency selection

© SiTime Corporation 2015. The information contained herein is subject to change at any time without notice. SiTime assumes no responsibility or liability for any loss, damage or defect of a Product which is caused in whole or in part by (i) use of any circuitry other than circuitry embodied in a SiTime product, (ii) misuse or abuse including static discharge, neglect or accident, (iii) unauthorized modification or repairs which have been soldered or altered during assembly and are not capable of being tested by SiTime under its normal test conditions, or (iv) improper installation, storage, handling, warehousing or transportation, or (v) being subjected to unusual physical, thermal, or electrical stress.

Disclaimer: SiTime makes no warranty of any kind, express or implied, with regard to this material, and specifically disclaims any and all express or implied warranties, either in fact or by operation of law, statutory or otherwise, including the implied warranties of merchantability and fitness for use or a particular purpose, and any implied warranty arising from course of dealing or usage of trade, as well as any common-law duties relating to accuracy or lack of negligence, with respect to this material, any SiTime product and any product documentation. Products sold by SiTime are not suitable or intended to be used in a life support application or component, to operate nuclear facilities, or in other mission critical applications where human life may be involved or at stake. All sales are made conditioned upon compliance with the critical uses policy set forth below.

CRITICAL USE EXCLUSION POLICY

BUYER AGREES NOT TO USE SITIME'S PRODUCTS FOR ANY APPLICATION OR IN ANY COMPONENTS USED IN LIFE SUPPORT DEVICES OR TO OPERATE NUCLEAR FACILITIES OR FOR USE IN OTHER MISSION-CRITICAL APPLICATIONS OR COMPONENTS WHERE HUMAN LIFE OR PROPERTY MAY BE AT STAKE.

SiTime owns all rights, title and interest to the intellectual property related to SiTime's products, including any software, firmware, copyright, patent, or trademark. The sale of SiTime products does not convey or imply any license under patent or other rights. SiTime retains the copyright and trademark rights in all documents, catalogs and plans supplied pursuant to or ancillary to the sale of products or services by SiTime. Unless otherwise agreed to in writing by SiTime, any reproduction, modification, translation, compilation, or representation of this material shall be strictly prohibited.



Supplemental Information

The Supplemental Information section is not part of the datasheet and is for informational purposes only.



Silicon MEMS Outperforms Quartz

Silicon MEMS Outperforms Quartz



Best Reliability

Silicon is inherently more reliable than quartz. Unlike quartz suppliers, SiTime has in-house MEMS and analog CMOS expertise, which allows SiTime to develop the most reliable products. Figure 1 shows a comparison with quartz technology.

Why is SiTime Best in Class:

- SiTime's MEMS resonators are vacuum sealed using an advanced EpiSeal[™] process, which eliminates foreign particles and improves long term aging and reliability
- · World-class MEMS and CMOS design expertise




Figure 1. Reliability Comparison^[1]

Best Aging

Unlike quartz, MEMS oscillators have excellent long term aging performance which is why every new SiTime product specifies 10-year aging. A comparison is shown in Figure 2.

Why is SiTime Best in Class:

- SiTime's MEMS resonators are vacuum sealed using an advanced EpiSeal process, which eliminates foreign particles and improves long term aging and reliability
- Inherently better immunity of electrostatically driven MEMS resonator




Figure 2. Aging Comparison^[2]

Best Electro Magnetic Susceptibility (EMS)

SiTime's oscillators in plastic packages are up to 54 times more immune to external electromagnetic fields than quartz oscillators as shown in Figure 3.

Why is SiTime Best in Class:

- Internal differential architecture for best common mode noise rejection
- Electrostatically driven MEMS resonator is more immune to EMS




Figure 3. Electro Magnetic Susceptibility (EMS)[3]

Best Power Supply Noise Rejection

SiTime's MEMS oscillators are more resilient against noise on the power supply. A comparison is shown in Figure 4.

Why is SiTime Best in Class:

- On-chip regulators and internal differential architecture for common mode noise rejection
- · Best analog CMOS design expertise




Figure 4. Power Supply Noise Rejection^[4]

Silicon MEMS Outperforms Quartz



Best Vibration Robustness

High-vibration environments are all around us. All electronics, from handheld devices to enterprise servers and storage systems are subject to vibration. Figure 5 shows a comparison of vibration robustness.

Why is SiTime Best in Class:

- The moving mass of SiTime's MEMS resonators is up to 3000 times smaller than guartz
- Center-anchored MEMS resonator is the most robust design




Figure 5. Vibration Robustness^[5]

Notes:

- 1. Data Source: Reliability documents of named companies.
- 2. Data source: SiTime and quartz oscillator devices datasheets.
- 3. Test conditions for Electro Magnetic Susceptibility (EMS):
 - According to IEC EN61000-4.3 (Electromagnetic compatibility standard)
 - Field strength: 3V/m
 - Radiated signal modulation: AM 1 kHz at 80% depth
 - Carrier frequency scan: 80 MHz 1 GHz in 1% steps
 - · Antenna polarization: Vertical
 - DUT position: Center aligned to antenna

Devices used in this test:

SiTime, SiT9120AC-1D2-33E156.250000 - MEMS based - 156.25 MHz

Epson, EG-2102CA 156.2500M-PHPAL3 - SAW based - 156.25 MHz

TXC, BB-156.250MBE-T - 3rd Overtone quartz based - 156.25 MHz

Kyocera, KC7050T156.250P30E00 - SAW based - 156.25 MHz

Connor Winfield (CW), P123-156.25M - 3rd overtone quartz based - 156.25 MHz

SiLabs, Si590AB-BDG - 3rd overtone quartz based - 156.25 MHz

4. 50 mV pk-pk Sinusoidal voltage.

Devices used in this test:

SiTime, SiT8208AI-33-33E-25.000000, MEMS based - 25 MHz

NDK, NZ2523SB-25.6M - quartz based - 25.6 MHz

Kyocera, KC2016B25M0C1GE00 - quartz based - 25 MHz

Epson, SG-310SCF-25M0-MB3 - quartz based - 25 MHz

- 5. Devices used in this test: same as EMS test stated in Note 3.
- 6. Test conditions for shock test:
 - MIL-STD-883F Method 2002
 - Condition A: half sine wave shock pulse, 500-g, 1ms
 - \bullet Continuous frequency measurement in 100 μs gate time for 10 seconds

Devices used in this test: same as EMS test stated in Note 3

7. Additional data, including setup and detailed results, is available upon request to qualified customers. Please contact productsupport@sitime.com.

Best Shock Robustness

SiTime's oscillators can withstand at least $50,000\ g$ shock. They all maintain their electrical performance in operation during shock events. A comparison with quartz devices is shown in Figure 6.

Why is SiTime Best in Class:

- The moving mass of SiTime's MEMS resonators is up to 3000 times smaller than guartz
- Center-anchored MEMS resonator is the most robust design




Figure 6. Shock Robustness^[6]

Document Feedback Form



SiTime values your input in improving our documentation. Click <u>here</u> for our online feedback form or fill out and email the form below to <u>productsupport@sitime.com</u>.

1. Does the Electrical	Yes	No				
If No, what parameters are missing?						
2. Is the organization of this document easy to follow?			Yes	No		
If "No," please sugges	st improvements that we can make:					
3. Is there any applica	ation specific information that you would lik	ke to see in this o	document? (Che	eck all that apply	/)	
EMI	Termination recommendations	Shock an	d vibration perfe	Other		
If "Other," please spec	cify:					
4. Are there any errors in this document? Yes			No			
If "Yes", please specif	y (what and where):					
5. Do you have addition	onal recommendations for this document?	,				
Name						
Title						
Company						
Address						
City / State or Province	e / Postal Code / Country					
Telephone						
Application						
Would you like a reply	? Yes No					

Thank you for your feedback. Please click the email icon in your Adobe Reader tool bar and send to productsupport@sitime.com. Or you may use our online-feedback form.

Feedback Form Rev. 1.0 www.sitime.com