



3109 - MALE STUD ELBOW, BSPT AND NPT THREAD



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
vacuum capability	755 mm Hg
body	TECHNICAL POLYMER
sub-base	NICKEL PLATED BRASS
'O'-rings	NBR
gripping ring	STAINLESS STEEL
surface treatment	PTFE

Part Nb	ØD (MM)	C	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3109 04 10	4	R1/8	10	8.5	13.5	14	.006
3109 04 13	4	R1/4	14	8.5	14	14	.015
3109 04 17	4	R3/8	17	8.5	13.5	14	.019
3109 06 10	6	R1/8	10	10.5	15.5	16	.006
3109 06 13	6	R1/4	14	10.5	16	16	.015
3109 06 17	6	R3/8	17	10.5	16	16	.019
3109 06 21	6	R1/2	21	10.5	16.5	16	.034
3109 08 10	8	R1/8	10	13.5	19	23	.007
3109 08 13	8	R1/4	14	13.5	18	23	.014
3109 08 17	8	R3/8	17	13.5	18	23	.018
3109 08 21	8	R1/2	21	13.5	19.5	23	.032
3109 10 10	10	R1/8	15	16	23	26.5	.012
3109 10 13	10	R1/4	15	16	22	26.5	.014
3109 10 17	10	R3/8	17	16	22	26.5	.02
3109 10 21	10	R1/2	21	16	22	26.5	.034
3109 12 13	12	R1/4	15	19	25	31	.016
3109 12 17	12	R3/8	17	19	25	31	.022
3109 12 21	12	R1/2	21	19	25	31	.036
3109 14 17	14	R3/8	20	22	30.5	35.5	.031
3109 14 21	14	R1/2	24	22	28.5	35.5	.042
3109 16 17	16	R3/8	27	27	53	39	.106
3109 16 21	16	R1/2	27	27	53	39	.104