#### AC Filter for PCB Mounting in Flat Aluminum Housing





		See below: Approvals and Co	ompliances		
Description - Line filter in standard and medical version - 1-stage - standard attenuation		<ul> <li>Characteristics</li> <li>Aluminum case provides good shielding Designed for standard applications</li> <li>Protection against interference voltage from the mains Possible interferences generated in the equipment are strongly attenu- ated</li> <li>Universal line filter for standard applications</li> <li>Suitable for use in equipment according to IEC/UL 62368-1</li> </ul>			
		Other versions or - Medical Version (M			
		<b>References</b> Alternative: Standard	,		
		Weblinks pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Detailed request for product, Microsite			
Technical Data					
Ratings IEC	2 - 16A @ Ta 40 °C / 250 VAC; 50 Hz	Line Filter	Standard and Medical Version, IEC		
Ratings UL/CSA	2 - 16 A @ Ta 40 °C / 125 VAC; 60 Hz		60939, UL 1283, CSA C22.2 no. 8		
Leakage Current	standard < 0.5 mA (250 V / 60 Hz)		Technical Details		
Dielectric Strength	> 1.7 kVDC between L-N > 2.7 kVDC between L/N-PE Test voltage (2 sec)	MTBF	> 200'000 h acc. to MIL-HB-217 F		
Allowable Operation Tempe- rature	-25 °C to 100 °C				
Climatic Category	25/100/21 acc. to IEC 60068-1				
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140				
Temesia el					

#### **Approvals and Compliances**

Terminal Material: Housing

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

For PCB mounting , tin-plated

Aluminum

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

# FMAB-72

#### Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FMAB

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40004673
c <b>AL</b> us	UL Approvals	UL	UL File Number: E72928

#### **Product standards**

Product standards that are referenced

Organization	Design	Standard	Description				
IEC	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference				
(UL)	Designed according to	UL 1283	Electromagnetic interference filters				
CSA Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters				

### **Application standards**

Application standards where the product can be used

Organization	Design	Standard	Description
IEC.	Designed for applications acc.	IEC/UL 62368-1	IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.
IEC	Designed for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance


#### Compliances

The product complies with following Guide Lines

- [	5		
Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
<b>©</b>	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
Ť	Medical Equipment	SCHURTER AG	Suitable for use in medical equipment according to IEC/UL 60601-1


#### **Dimension** [mm]

Case 72




# Diagrams

Standard version





# Attenuation Loss

- - - - 50 $\Omega$  differential mode \_\_\_\_\_ 50 $\Omega$  common mode




16 A






16 A



# FMAB-72

# Medical version (M80)



16 A

0.01

2 A

dB

80


60

40

20

0

dB				
80				
60		1	·,	
40		1		
20 0 0.01	0.1	1	10	100 400 MHz



### All Variants

Rated Current [A]	Filter-Type	L [mH]	Cx (X2) [nF]	Cy (Y2) [nF]	<b>R [Μ</b> Ω]	Weight [g]	Housings	Order Number
2	Standard version	2 x 8	100	4.7	1	114g	72	5500.2021
4	Standard version	2 x 3.5	100	4.7	1	114 g	72	5500.2022
6	Standard version	2 x 1.8	100	4.7	1	115 g	72	5500.2023
10	Standard version	2 x 0.82	100	4.7	1	115g	72	5500.2024
16	Standard version	2 x 0.65	100	4.7	1	115g	72	5500.2025
2	Medical Version (M5)	2 x 8	100	-	1	114g	72	5500.2106
4	Medical Version (M5)	2 x 3.5	100	-	1	114 g	72	5500.2107
6	Medical Version (M5)	2 x 1.8	100	-	1	115 g	72	5500.2108
10	Medical Version (M5)	2 x 0.82	100	-	1	115g	72	5500.2109
16	Medical Version (M5)	2 x 0.65	100	-	1	115 g	72	5500.2110
2	Medical Version (M80)	-	-	-	-	114g	72	5500.2111
4	Medical Version (M80)	-	-	-	-	114g	72	5500.2112
6	Medical Version (M80)	-	-	-	-	115g	72	5500.2113
10	Medical Version (M80)	-	-	-	-	115g	72	5500.2114
16	Medical Version (M80)	-	-	-	-	115g	72	5500.2115

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging unit

10 Pcs

The specifications, descriptions and illustrations indicated in this document are based on current information. All content is subject to modifications and amendments. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability and test each product selected for their own applications.