


This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.



**MARKETING SALES DRAWING**  
**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**  
**DIMENSIONS IN METRIC - [ ]**




**Electrical Testing per Tusonix standard test plans and Mil-Std-202 Test Methods.**

Ø .190 [4.83] THRU (2) PLCS.

.200 [5.08] (2) PLCS.



GREEN INK DOT RoHS ONLY  
 #6-32 UNC-2A THD. COMBINATION HEAD SCREW WITH CLAMP WASHER (6) PLCS. TORQUE 10.8-13.2 in. lbs. [1.22-1.49] MAX.



SLEEVES SOLDERED TO GROUND PLATE .040 [1.02] MAX. FILLET

FILTER ENCAPSULATED IN SLEEVE

**NOTES:**

1. TUSONIX STANDARD PART NUMBER: 7606-501.  
TUSONIX RoHS COMPLIANT PART NUMBER: 7606-501 LF.  
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: MATTE TIN.
3. PLATE MATERIAL: .040" COPPER ALLOY, MATTE TIN FINISH.
4. PART MARKING: TRADEMARK, PART NUMBER, DATE CODE, AND UL RECOGNITION: WHITE INK. RoHS PART: GREEN INK DOT ON TOP OF GROUND PLATE AS SHOWN.
5. MAX. SOLDERING TEMPERATURE 500°F [260°C].
6. BLOCK MOUNTING: RECOMMENDED MOUNTING SCREWS (# 8 PAN HEAD). TORQUE 4.5-5.5 in. lbs. [0.51-0.62 Nm] MAX.
7. MOLDED MATERIAL: HIGH TEMPERATURE THERMOPLASTIC (PBT), UL RATED 94 V-O.
8. U.L. FILE NO. E201344.

Cx (pF)	WVAC -40°C TO +125°C	I <sub>DC</sub>	I.R. MIN. @ 100 (VDC.)	DWV (VAC)	TYPICAL NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220			
					10 MHz	100 MHz	1 GHz	10 GHz
2000 MIN.	250	20 Amps	10 G Ω	1500	5	50	60	65

REVISION RECORD Original Release C.O. <b>19990607-1-10</b> REVISED BLOCK & NOTE 3. ADDED NOTE 5. S.M. 01-28-00 <b>20000127-3-05</b> REVISED METRIC & NOTES. ADDED IR & DWV. S. M. 08-24-04 <b>20040819-2-03</b> ADDED NOTES 1-4 & RENUMBERED. S.M. 10-12-05 <b>20050926-5-13</b> NOTES 4 & 6 REVISED. ADDED INK DOT. REVISED TORQUE. S.M. 01-23-06 <b>20060103-1-05</b>	TOLERANCES unless otherwise specified 2 PLC. DECIMAL ± N/A 3 PLC. DECIMAL ± .030 [0.76]		Title <b>FILTERED TERMINAL BLOCK 6 POSITION, UL RECOGNIZED</b>	
	ANGLES ± N/A		Drawn S.M. 06-08-99	Scale FULL
	<b>TUSONIX</b> TUCSON, ARIZONA		Approved T.C. 06-08-99	
	<b>A</b>		<b>7606-501</b>	

X-2015 Rev-0

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[7606-501LF](#)