


- CONNECTOR 1
- 1. CONNECTOR 1: 854-004-203RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
- 2. CONNECTOR 2: 854-004-203RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
- 3. WIRE: 26AWG, 2 1/2TWISTED PAIRS, UL20276, FOIL/BRAID/DRAIN SHIELD, COLOR BLACK, 30V
- 4. CABLE DIAMETER: 4.60mm±0.15mm
- 5. SHIELDING: 360°
- 6. PIN DUT :

WIRING SCHEMATIC



CCA-000-MYYR205

01 = 1 METER ±12.00mm
02 = 2 METERS ±25.00mm
03 = 3 METERS ±25.00mm

**SEE PAGE 3 FOR CABLE SPECIFICATIONS

ROHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING

CONNECTOR 2



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NOrComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION


RAWN:	DATE:	
M. SIGMON		04-14-15


NorComp

SCALE:	SHEET		OF		
NTS		1		3	
511/6 116	•				

CCA-000-MYYR205

REV





ROHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
DATE:
04-14-15

NorComp DWG NO.

SCALE:	SHEET	_	OF			REV
NTS		2		3		6
DWG NO.	CCA-000-MYYR205					

DESCRIPTION: M8 - FEMALE TO FEMALE - 4 POSITION - CABLE ASSEMBLY

ELECTRICAL CHARACTERISTICS


VOLTAGE RATING: 30V TEMPERATURE RATING: 80°C


SPARK TEST: AC-500V/0.15 sec MIN.

DIELECTRIC STRENGTH: AC-750V/1 sec MIN.

INSULATION RESISTANCE: SR-PVC: DC-500V 10 MOHM/KM MIN. AT 20°C

CONDUCTOR RESISTANCE: 26AWG-153 OHM/KM MAX, AT 25°C





COLOR CODE

- 1. BLACK * BROWN (P570 & P571)
- 2. RED * ORANGE (P572 & P573)
- 3. YELLOW (574)

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NOrComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN.	Μ.	SIGMON

DATE: 04-14-15

NorComp

DWG NO.		000	
NTS		3	
SCALE:	SHEET		Ol

CCA-000-MYYR205

3

REV