

PRODUCT-DETAILS

S20/10M

GALV.STEEL S SUPERFLEX NC20 10MT



General Information

Extended Product Type	S20/10M
Product ID	7TCA296010R0057
EAN	5020963000584
Catalog Description	GALV.STEEL S SUPERFLEX NC20 10MT
Long Description	Inherent Low Fire Hazard Steel Conduit, Nominal Conduit Size 20mm, Outside Diameter 20.5mm, Inside Diameter 16.9mm, Static Bend Radius 45mm, Reel Length 10 Meters, Galvanised Steel General Purpose

Additional Information

Application	Indoors / Outdoors - Light Industrial, Buildings
Product Type	Low Fire Hazard Conduit

Ordering

EAN	5020963000584
UPC	786210260594
Customs Tariff Number	8307106000

Dimensions

Product Net Depth / Length	10 m
----------------------------	------

Technical

Number of Batteries	0
Material	Galvanized Steel

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Height	6 in 152 mm
Package Level 1 Depth / Length	9 in 229 mm
Package Level 1 Width	9 in 229 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	S20/10M
Instructions and Manuals	S20/10M
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

Classifications

ETIM 8	EC001179 - Protective metallic hose
UNSPSC	39131706

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

