

# Toroids (5943000911)



Part Number: 5943000911

43 TOROID PARYLENE COATED

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- 9th digit 1 = Parylene Coating, 2 = Thermo- Set Plastic Coating

**A ring configuration provides the ultimate utilization of the intrinsic ferrite material properties. Toroidal cores are used in a wide variety of applications such as power input filters, ground- fault interrupters, common- mode filters and in pulse and broadband transformers.**

All toroidal cores are supplied burnished to break sharp edges.

Coating Options:

- Toroids with an outside diameter of 9.5 mm (0.375") or smaller can be supplied Parylene C coated. The Parylene coating will increase the "A" and "C" dimensions and decrease the "B" dimension a maximum of 0.038 mm (0.0015"). The ninth digit of a Parylene coated toroid part number is a "1". See reference tables for the material characteristics of Parylene C. Parylene C coating is RoHS compliant.
- Toroids with an outside diameter of 9.5 mm (0.375") or larger can be supplied with a uniform coating of thermo- set plastic coating. This coating will increase the "A" and "C" dimensions and decrease the "B" dimension a maximum of 0.5 mm (0.020"). The 9th digit of the thermo- set plastic coated toroid part number is a "2". Thermo- set plastic coating is RoHS compliant.
- Thermo- set plastic coated parts can withstand a minimum breakdown voltage of 1000 Vrms, uniformly applied across the "C" dimension of the toroid.

**For any toroidal core requirement not listed in the catalog, please contact our customer service department for availability and pricing.**

[Catalog Drawing](#)  
[3D Model](#)

The C dimension may be modified to suit specific applications.

Weight: 0.29 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	5.99	Max	0.235	Max
B	2.91	Min	0.115	Min
C	3.22	Max	0.126	Max



**Chart Legend**  
 $\Sigma l / A$  : Core Constant,  $l_e$  : Effective Path Length,  $A_e$  : Effective Cross- Sectional Area,  $V_e$  : Effective Core Volume  
 $A_L$  : Inductance Factor 

Electrical Properties	
$A_L$ (nH)	315 ±20%
$A_e$ (cm <sup>2</sup> )	0.041
$\Sigma l / A$ (cm <sup>-1</sup> )	31.8
$l_e$ (cm)	1.3
$V_e$ (cm <sup>3</sup> )	0.053

Toroids are tested for  $A_L$  values at 10 kHz.

Fair- Rite Products Corp. • One Commercial Row, Wallkill, New York 12589-0288  
888-324-7748 • 845-895-2055 • Fax: 845-895-2629 • ferrites@fair-rite.com • www.fair-rite.com