


Circuit Diagram



P. C. B Holes Diagram
BOTTOM VIEW

Dimension Size	Tolerances
$L \leq 1$	± 0.15
$1 < L \leq 8$	± 0.20
$8 < L \leq 23$	± 0.25
$23 < L \leq 50$	± 0.30

NO.	PART NAME	Q' TY	MATERIAL (THICKNESS, COLOR)	REMARK
5	BRACKET	1	FE	CuSn-plated; RoHS COMPLIANT
4	SPRING	1	PHOSPHOR BRASS (QSn6.5-0.1Y)	Coating Silver; RoHS COMPLIANT
3	TERMINAL	2	BRASS (H65 Y 0.3t)	Ag-plated; RoHS COMPLIANT
2	STEM	1	(Black) PC 94HB	RoHS COMPLIANT
1	HOUSING	1	(Black) PA66 94HB	RoHS COMPLIANT

Dimension	DATE	DATE	DATE	Scale:	DESCRIPTION:
DWN	H. D. YANG	DATE	2006. 04. 20	Unscale	MODEL NO. :
DSND		DATE			
CHKD	Y. L. JI	DATE	2006. 04. 20		
APVD	Y. H. LONG	DATE	2006. 04. 20		

OPERATION FORCE SPECIFICATION				Hn
others	260±50gf	220±50gf	180±50gf	(Value)
				4.3-C
				4.3
				4.5
				4.7
				5.0
				5.3
				5.5
				6.0
				7.0
				7.3
				7.5
				8.0
				8.5
				9.0
				9.5
				10.0
				10.5
				11.0
				12.0
				12.5
				13.0
				13.5
				14.0
				14.5
				15.0
				15.3
				15.5
				16.0
				16.5
				17.0
				18.0
				19.0
				20.0
				21.0
				22.0
				others