

# EMI Suppression Beads (2643004801)



Part Number: 2643004801

43 SHIELD BEAD

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 1= Not Burnished 2 = Burnished
- The last digit of the Parylene coated part is a “4,” which is available upon request. The minimum coating thickness beads is 0.005 mm (0.0002”).

Fair- Rite offers a broad selection of ferrite EMI suppression beads with guaranteed minimum impedance specifications.

Our “Shield Bead Kit” (part number 0199000019) contains a selection of these beads.

**For any EMI suppression bead requirement not listed here, feel free to contact our customer service for availability and pricing.**

[Catalog Drawing](#)  
[3D Model](#)

The C dimension, the bead length, can be modified to suit specific applications.

Weight: 0.03 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	2.1	-0.15	0.08	—
B	0.85	+0.10	0.035	—
C	2.9	-0.45	0.105	—



**Chart Legend**

+ Test frequency

• The column "H (Oe)" gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of “H” times the actual NI (ampere- turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note □How to choose Ferrite Components for EMI Suppression□.


Typical Impedance (Ω)	
10 MHz	11
25 MHz <sup>+</sup>	17.5
100 MHz <sup>+</sup>	29
250 MHz	41

Electrical Properties	
H(Oe)	3.1

Suppression beads are controlled for impedances only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is listed on our catalog drawing.

[Catalog Drawing](#)

Single turn impedance tests for 73 and 43 material beads are performed on the E4990A Impedance Analyzer. The 61 material beads are tested on the E4991A / HP4291B Impedance Analyzer. Beads are tested with the shortest practical wire length.



[CSV Download](#)