


Z terminal with tension spring connection ZDUA 2.5-2 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



This range of small terminals with tension clamp connections enables the building of individual blocks with 2- and 4-pole terminals.

Individual blocks are made up from the middle terminals plus end plates on the open sides.

For a screw fixing, the first middle terminal plus the end plate are replaced by end terminals for the fixing. For the other types of fixing, middle terminals with a fixing option are included in the block or a mounting foot (MOFU) is fitted for attaching to the terminal rail.

General ordering data

Order No.	1720930000
Type	ZDUA 2.5-2 BL
Version	Z terminal with tension spring connection, Feed-through terminal, Rated cross-section: 2.5 mm ² , Tension clamp connection, Wemid, Blue
GTIN (EAN)	4008190376796
Qty.	100 pc(s).

Z terminal with tension spring connection ZDUA 2.5-2 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	35 mm	Width	5.1 mm
Height	30 mm	Height of lowest version	30.5 mm
Net weight	3.6 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Rated data IECEx/ATEX

Certificate No. (ATEX)	KEMA97ATEX4678U	ATEX certificate	KEMA97ATEX4678U_d.pdf
ATEX certificate	KEMA97ATEX4678U_e.pdf	Max. voltage (ATEX)	275 V
Current (ATEX)	20 A	Wire cross section max. (ATEX)	2.5 mm ²
Voltage, cross-connection		Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity
Marking EN 60079-7	CrossConnectionGuide.pdf Ex e II	Marking ATEX Directive 94/9/EC	II 2 G D

Additional technical data

Explosion-tested version	Yes	Open sides	right
Type of mounting	Snap-on	Version	End terminal

CSA ratings data

Certificate No. (CSA)	200039-1152892	Voltage size B (CSA)	600 V
Current size B (CSA)	20 A	Wire cross section max. (CSA)	12 AWG
Wire cross section min. (CSA)	26 AWG		

Clampable wires (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min.	0.5 mm ²	Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.	2.5 mm ²
---	---------------------	---	---------------------

Clampable wires (rated connection)

Type of connection	Tension clamp connection	Stripping length	10 mm
Blade size	0.6 x 3.5 mm	Connection direction	top
Number of connections	2	Clamping range, rated connection, min.	0.13 mm ²
Clamping range, rated connection, max.	4 mm ²	Gauge to IEC 60947-1	A2
Wire connection cross section, solid core, max. rated connection	0.5 mm ²	Wire connection cross section, solid core max. rated connection	4 mm ²
Wire connection cross section, finely stranded, max.	2.5 mm ²	Wire connection cross-section, finely stranded, min.	0.5 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	1.5 mm ²
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 12

Dimensions

TS 15 offset	17.5 mm
--------------	---------

Creation date March 8, 2013 4:51:23 PM CET

Z terminal with tension spring connection ZDUA 2.5-2 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Rated data

Rated cross-section	2.5 mm ²	Rated voltage	500 V
Rated impulse withstand voltage	6 kV	Rated current	24 A
Current at maximum wires	30 A	Standards	IEC 60947-7-1
Pollution severity	3		

UL ratings data

Certificate No. (UR)	E60693VOL1SEC52	Voltage size C (UR)	600 V
Current size C (UR)	20 A	Conductor size Factory wiring max. (UR)	12 AWG
Conductor size Factory wiring min. (UR)	26 AWG	Conductor size Field wiring max. (UR)	12 AWG

Material data

Insulating material	Wemid	Material	Wemid
Colour	Blue	UL 94 flammability rating	V-0

System specifications

Product family	Z terminal with tension spring connection	Type of connection	Tension clamp connection
Connection direction	top	Number of levels	1
Number of connections	2	No. of clamping points per level	2
Levels cross-connected internally	No	Mounting rail	TS 15
End cover plate required	Yes		

Classifications

ETIM 2.0	EC000897	ETIM 3.0	EC000897
UNSPSC	30-21-18-11	eClass 4.1	27-14-11-23
eClass 5.1	27-14-11-20	eClass 6.0	27-14-11-20
eClass 7.0	27-14-11-20		

Product information

Descriptive text technical data	TS 15 - sliced construction
---------------------------------	-----------------------------

Approvals

Approvals

