



## NC5FX

5 pole female cable connector with Nickel housing and silver contacts.

The "industry standard" XLR cable connector, easy to assemble with only 4 parts and no screws. Compact design with sturdy diecast shell, fibreglass reinforced hard plastic insert and chuck type strain relief for secure clamping of all cables.

### Features & Benefits

- Rugged zinc diecast shell, long lasting and durable
- Chuck type strain relief system for secure clamping of cables
- Boot with rubber gland gives high protection against bending stresses
- Coloured rings and boots available for coding and marking
- UL recognized components

**Technical Information**

Product	
<b>Title</b>	NC5FX
<b>Connection Type</b>	XLR
<b>Gender</b>	female

Electrical	
<b>Capacitance between contacts</b>	$\leq 7$ pF
<b>Contact resistance</b>	$\leq 3$ m $\Omega$
<b>Dielectric strength</b>	1,5 kVdc
<b>Insulation resistance</b>	$> 10$ G $\Omega$ (initial)
<b>Rated current per contact</b>	7,5 A
<b>Rated voltage</b>	$< 50$ V

Mechanical	
<b>Cable O.D.</b>	3.5 - 8.0 mm
<b>Insertion force</b>	$\leq 20$ N
<b>Withdrawal force</b>	$\leq 20$ N
<b>Lifetime</b>	$> 1000$ mating cycles
<b>Wiresize</b>	max. 1.0 mm <sup>2</sup>
<b>Wiresize</b>	max. 18 AWG
<b>Wiring</b>	Solder contacts
<b>Locking device</b>	Latch lock

Material	
<b>Boot</b>	Polyurethan
<b>Contact plating</b>	2 µm Ag
<b>Contacts</b>	Brass (CuZn39Pb3)
<b>Insert</b>	Polyamide (PA66)
<b>Locking element</b>	St3K32 (latch) / Ck 67 (spring)
<b>Shell</b>	Zinc diecast (ZnAl4Cu1)
<b>Shell plating</b>	Nickel
<b>Strain relief</b>	Polyacetal (POM)

Environmental	
<b>Approvals</b>	UL
<b>Flammability</b>	UL 94 V-0
<b>Standard compliance</b>	IEC 61076-2-103
<b>Protection class</b>	IP 40
<b>Solderability</b>	Complies with IEC 68-2-20
<b>Temperature range</b>	-30 °C to +80 °C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC5FX](#)