

## Coaxial Cable Connector 24\_N-50-2-4/133\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0352 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00009130
Catalogue drawing	DCA-00009132
Assembly instruction	DOC-0000179123

### Ordering Information

Tray package	24_N-50-2-4/133_NY
Single package	24_N-50-2-4/133_NE

### Additional Information

Suitable cables	RG_316_U, ENVIROFLEX_316, RG_188_A/U, RG_174_U
-----------------	--

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[24\\_N-50-2-4/133\\_NE](#)