


# ET-03I-08-15

## Peltier cooler module

### Data sheet







$I_{max}$	[A]	2.2
$V_{max}$	[Vdc]	3.8
$P_c \text{ max}$	[W]	5.3
$\Delta T_{max}$	[°C]	74
A	[mm]	13
A1	[mm]	13
B	[mm]	13
H	[mm]	3.8
L	[mm]	100
Wire	AWG	n/a

- (At hot side temperature  $T_h = 25^\circ\text{C} / 298\text{K}$ , under dry  $\text{N}_2$ )
- $P_c \text{ max}$  = Cooling power at  $\Delta T = 0$  and  $I = I_{max}$
- $\Delta T_{max}$  = Temperature difference at  $I = I_{max}$  and  $P_c = 0$
- Max hot side temperature  $T_h = 90^\circ\text{C}$  for best long term performance
- Max mounting pressure: 1.5MPa
- Wires: UL-style 1569, 105°C (Unstripped)







### Data sheet - At hot side temperature 25°C



\*Note - Waste heat = Heat out of hot side







### Data sheet - At hot side temperature 50°C



\*Note - Waste heat = Heat out of hot side



### Data sheet - At hot side temperature 75°C



\*Note - Waste heat = Heat out of hot side

