

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0346900080](#)  
**Status:** **Active**  
**Overview:** [Stac64 Single, Multi-Pocket and Hybrid Header System](#)  
**Description:** [Stac64 Vertical Header Assembly, 8 Circuits, Polarization A, Black, Tray](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34729-020-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-31300-892-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-34729-020-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 347290200-AS-CH-000 (PDF)</a>	

**General**

Product Family	PCB Headers
Series	<a href="#">34690</a>
Application	Automotive, Power, Wire-to-Board
Comments	Polarization A
Overview	<a href="#">Stac64 Single, Multi-Pocket and Hybrid Header System</a>
Product Name	Stac64
UPC	883906122607

**Physical**

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.528/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.33mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	10.0A
-------------------------------	-------



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[34690](#) Series

**Mates With**

[34729](#) 2.54mm (.100") Pitch Stac64 Right Angle Receptacle, [31408](#) USCAR 2.54mm (.100") Pitch Receptacle

Voltage - Maximum 500V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 040  
Lead-free Process Capability WAVE  
Max. Cycles at Max. Process Temperature 003  
Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Application Specification 347290200-AS-CH-000, AS-34729-020-001  
Packaging Specification PK-31300-892-001  
Product Specification PS-34729-020-001  
Sales Drawing 346900000-000

This document was generated on 06/22/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34690-0080](#)