

- Compact metal package
- Ultra wide 4:1 input voltage ranges  
9–36, 18–75, 43–160 VDC
- EN 50155 approval for railway applications
- Very high efficiency up to 91%
- No minimum load
- Soft start
- Adjustable output voltage +10 / -20%
- Sense line
- Remote On/Off input
- Under voltage lock-out circuit



The TEP 160WIR Series is a family of isolated high performance DC/DC converter modules with ultra-wide 4:1 input voltage ranges which come in a rugged, sealed industry standard half brick package. A very high efficiency allows full power operation without forced air cooling at 25°C. This temperature can be increased to 40°C with optional mounted heatsink or up to 60°C when mounted on an iron base plate. The very wide input voltage range and reverse input voltage protection make these converters an interesting solution for battery operated systems. Typical applications are in telecom/datacom, industry control and railway systems for on board power distribution. This series is available in many optional designs on demand --> see options.

Models				
Order Code	Input Voltage Range	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TEP 160-2412WIR	9 - 36 VDC (24 VDC nom.)	12 VDC (9.6 - 13.2 VDC)	12'000 mA	90 %
TEP 160-2413WIR		15 VDC (12.0 - 16.5 VDC)	9'500 mA	91 %
TEP 160-2415WIR		24 VDC (19.2 - 26.4 VDC)	6'000 mA	90 %
TEP 160-2416WIR		28 VDC (22.4 - 30.8 VDC)	5'000 mA	90 %
TEP 160-2418WIR		48 VDC (38.4 - 52.8 VDC)	3'000 mA	90 %
TEP 160-4812WIR	18 - 75 VDC (48 VDC nom.)	12 VDC (9.6 - 13.2 VDC)	13'000 mA	91 %
TEP 160-4813WIR		15 VDC (12.0 - 16.5 VDC)	10'000 mA	91 %
TEP 160-4815WIR		24 VDC (19.2 - 26.4 VDC)	6'500 mA	91 %
TEP 160-4816WIR		28 VDC (22.4 - 30.8 VDC)	5'500 mA	91 %
TEP 160-4818WIR		48 VDC (38.4 - 52.8 VDC)	3'200 mA	91 %
TEP 160-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC (9.6 - 13.2 VDC)	15'000 mA	90 %
TEP 160-7213WIR		15 VDC (12.0 - 16.5 VDC)	12'000 mA	90 %
TEP 160-7215WIR		24 VDC (19.2 - 26.4 VDC)	7'500 mA	90 %
TEP 160-7216WIR		28 VDC (22.4 - 30.8 VDC)	6'500 mA	90 %
TEP 160-7218WIR		48 VDC (38.4 - 52.8 VDC)	3'800 mA	90 %

Options	
<b>TEP-HS1</b>	- Optional Heat Sink: <a href="http://www.tracopower.com/products/tep-hs1.pdf">www.tracopower.com/products/tep-hs1.pdf</a>
<b>on demand</b> (backorder with MOQ non stocking item)	<ul style="list-style-type: none"> <li>- Optional model with 3.3 VDC / 40'000 mA Output and 9 - 36 VDC Input</li> <li>- Optional model with 5 VDC / 28'000 mA Output and 9 - 36 VDC Input</li> <li>- Optional model with 3.3 VDC / 40'000 mA Output and 18 - 75 VDC Input</li> <li>- Optional model with 5 VDC / 30'000 mA Output and 18 - 75 VDC Input</li> <li>- Optional model with 3.3 VDC / 43'000 mA Output and 43 - 160 VDC Input</li> <li>- Optional model with 5 VDC / 32'000 mA Output and 43 - 160 VDC Input</li> <li>- Optional models with Sync pin to synchronize switching frequency of up to 3 units (EMC reason)</li> <li>- Chassis mount models w/o filter: <a href="http://www.tracopower.com/products/tep160wircm.pdf">www.tracopower.com/products/tep160wircm.pdf</a></li> <li>- Chassis mount models w/ filter to meet EN 55032 class A: <a href="http://www.tracopower.com/products/tep160wircmf.pdf">www.tracopower.com/products/tep160wircmf.pdf</a></li> <li>- Optional models with inverse remote on/off function (passiv = off)</li> </ul>

Input Specifications	
Input Current	- At no load 24 Vin models: <b>25 mA typ.</b> 48 Vin models: <b>20 mA typ.</b> 110 Vin models: <b>10 mA typ.</b>
Surge Voltage	24 Vin models: <b>50 VDC max.</b> (1 s max.) 48 Vin models: <b>100 VDC max.</b> (1 s max.) 110 Vin models: <b>185 VDC max.</b> (1 s max.)
Under Voltage Lockout	24 Vin models: <b>7.3 VDC min. / 7.7 VDC typ. / 8.1 VDC max.</b> 48 Vin models: <b>15.5 VDC min. / 16 VDC typ. / 16.3 VDC max.</b> 110 Vin models: <b>33 VDC min. / 34.5 VDC typ. / 36 VDC max.</b>
Recommended Input Fuse	24 Vin models: <b>25'000 mA</b> (fast acting) 48 Vin models: <b>15'000 mA</b> (fast acting) 110 Vin models: <b>8'000 mA</b> (fast acting) (The need of an external fuse has to be assessed in the final application.)
Input Filter	<b>Internal Pi-Type</b>

Output Specifications	
Output Voltage Adjustment	-20% to +10% (By external trim resistor) See application note: <a href="http://www.tracopower.com/overview/tep160wir">www.tracopower.com/overview/tep160wir</a> Output power must not exceed rated power!
Voltage Set Accuracy	<b>±1% max.</b>
Regulation	- Input Variation (Vmin - Vmax) <b>0.1% max.</b> - Load Variation (0 - 100%) <b>0.1% max.</b>
Ripple and Noise (20 MHz Bandwidth)	3.3 Vout models: <b>75 mVp-p max.</b> (w/ 1 µF X7R // 25 µF poscap) 5 Vout models: <b>75 mVp-p max.</b> (w/ 1 µF X7R // 25 µF poscap) 12 Vout models: <b>100 mVp-p max.</b> (w/ 1 µF X7R // 25 µF poscap) 15 Vout models: <b>100 mVp-p max.</b> (w/ 1 µF X7R // 25 µF poscap) 24 Vout models: <b>200 mVp-p max.</b> (w/ 4.7 µF X7R) 28 Vout models: <b>200 mVp-p max.</b> (w/ 4.7 µF X7R) 48 Vout models: <b>300 mVp-p max.</b> (w/ 2.2 µF X7R)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Capacitive Load	- 24 Vin input	3.3 Vout models: 121'000 µF max. 5 Vout models: 56'000 µF max. 12 Vout models: 10'000 µF max. 15 Vout models: 6'300 µF max. 24 Vout models: 2'500 µF max. 28 Vout models: 1'700 µF max. 48 Vout models: 620 µF max.
	- 48 Vin input	3.3 Vout models: 121'000 µF max. 5 Vout models: 60'000 µF max. 12 Vout models: 10'800 µF max. 15 Vout models: 6'600 µF max. 24 Vout models: 2'700 µF max. 28 Vout models: 1'900 µF max. 48 Vout models: 660 µF max.
	- 110 Vin input	3.3 Vout models: 130'000 µF max. 5 Vout models: 64'000 µF max. 12 Vout models: 12'500 µF max. 15 Vout models: 8'000 µF max. 24 Vout models: 3'100 µF max. 28 Vout models: 2'300 µF max. 48 Vout models: 790 µF max.
	Minimum Load	Not required
	Temperature Coefficient	±0.02 %/K max.
	Start-up Time	75 ms typ.
	Short Circuit Protection	Continuous, Automatic recovery
	Output Current Limitation	120 - 150% of Iout max.
	Oversvoltage Protection	115 - 130% of Vout nom.
Transient Response	- Response Time	200 µs typ. / 250 µs max. (25% Load Step)

### Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Railway Applications - Certification Documents	EN 50155 <a href="http://www.tracopower.com/overview/tep160wir">www.tracopower.com/overview/tep160wir</a>
Pollution Degree		PD 2
Over Voltage Category		OVC II

### EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55011 class A (with external filter) EN 55011 class B (with external filter) EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55011 class A (with external filter) EN 55011 class B (with external filter) EN 55032 class A (with external filter) EN 55032 class B (with external filter)
		External filter proposal: <a href="http://www.tracopower.com/overview/tep160wir">www.tracopower.com/overview/tep160wir</a>

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

<b>EMS Immunity</b>		EN 50155 (Railway Applications) EN 50121-3-2 (EMC for Rolling Stock)
- Electrostatic Discharge	Air:	EN 61000-4-2, $\pm 8$ kV, perf. criteria A
	Contact:	EN 61000-4-2, $\pm 6$ kV, perf. criteria A EN 61000-4-3, 20 V/m, perf. criteria A EN 61000-4-4, $\pm 2$ kV, perf. criteria A EN 61000-4-5, $\pm 2$ kV, perf. criteria A
- RF Electromagnetic Field	Ext. input component:	24 & 48 Vin models: 2x KY 220 $\mu$ F 110 Vin models: 2x KXJ 150 $\mu$ F
- EFT (Burst) / Surge		EN 61000-4-6, 10 Vrms, perf. criteria A
	Continuous:	EN 61000-4-8, 100 A/m, perf. criteria A
- Conducted RF Disturbances	1 s:	EN 61000-4-8, 1000 A/m, perf. criteria A
- PF Magnetic Field		

### General Specifications

<b>Relative Humidity</b>		95% max. (non condensing)
<b>Temperature Ranges</b>	- Operating Temperature	-40°C to +75°C
	- Case Temperature	+115°C max.
	- Storage Temperature	-55°C to +125°C
<b>Power Derating</b>	- High Temperature	See application note: <a href="http://www.tracopower.com/overview/tep160wir">www.tracopower.com/overview/tep160wir</a>
<b>Over Temperature Protection Switch Off</b>	- Protection Mode	120°C typ. (Automatic recovery at 105°C typ.)
	- Measurement Point	Base-Plate
<b>Cooling System</b>		Natural convection (20 LFM)
<b>Sense Function</b>		10% max. of Vout nom. (Sense line to be connected to the output either at the module or at the load under regard of polarity.)
<b>Remote Control</b>	- Voltage Controlled Remote	On: 3.0 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to 'Remote' and '-Vin' Pin
	- Off Idle Input Current	3 mA typ.
	- Remote Pin Input Current	-0.5 to 1.0 mA
<b>Altitude During Operation</b>		2'000 m max. (for reinforced insulation) 5'000 m max. (for functional insulation)
<b>Switching Frequency</b>		225 - 275 kHz (PWM) 250 kHz typ. (PWM)
<b>Insulation System</b>		Reinforced Insulation
<b>Working Voltage (rated)</b>		145 VAC (3.3 and 5 Vout models) 185 VAC (48 Vout models) 172 VAC (other output models)
<b>Isolation Test Voltage</b>	- Input to Output, 60 s	3'000 VAC
	- Input to Case, 60 s	1'500 VAC
	- Output to Case, 60 s	1'500 VAC
<b>Isolation Resistance</b>	- Input to Output, 500 VDC	1'000 M $\Omega$ min.
<b>Isolation Capacitance</b>	- Input to Output, 100 kHz, 1 V	2'500 pF max.
<b>Reliability</b>	- Calculated MTBF	350'000 h (MIL-HDBK-217F, ground benign)
<b>Washing Process</b>		Allowed (hermetical product)
	See Cleaning Guideline:	<a href="http://www.tracopower.com/info/cleaning.pdf">www.tracopower.com/info/cleaning.pdf</a>
<b>Environment</b>	- Vibration	MIL-STD-810F EN 61373
	- Mechanical Shock	MIL-STD-810F EN 61373
	- Thermal Shock	MIL-STD-810F EN 50155
<b>Housing Material</b>		Alu base-plate w. metal case (24 and 48 Vin models) Alu base-plate w. plastic case (110 Vin models)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.


Base Material	Non-conductive FR4 (UL 94 V-0 rated) (24 and 48 Vin models only)
Potting Material	Silicone (UL 94 V-0 rated)
Pin Material	Copper
Pin Foundation Plating	Nickel (2 - 3 $\mu\text{m}$ )
Pin Surface Plating	Tin (3 - 5 $\mu\text{m}$ ), matte
Housing Type	Metal Case (24 and 48 Vin models) Plastic Case (110 Vin models)
Mounting Type	PCB Mount
Connection Type	THD (Through-Hole Device)
Footprint Type	Half-Brick
Weight	105 g
Thermal Impedance	- Case to Ambient 6.1 K/W typ. 4.6 K/W typ. (with Heat Sink)
Environmental Compliance	- REACH Declaration <a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a> REACH SVHC list compliant REACH Annex XVII compliant - RoHS Declaration <a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a> Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule). The SCIP number is provided on request.) - Flammability (EN 45545-2) <a href="http://www.tracopower.com/info/en45545-declaration.pdf">www.tracopower.com/info/en45545-declaration.pdf</a>

### Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/tep160wir](http://www.tracopower.com/overview/tep160wir)

### Outline Dimensions



### Pinout

Pin	Single	Pin Diameter
1	-Vin (GND)	1.0 mm (0.04 inch)
2	Case	1.0 mm (0.04 inch)
3	Remote On/Off	1.0 mm (0.04 inch)
4	+Vin (Vcc)	1.0 mm (0.04 inch)
5	-Vout	2.0 mm (0.08 inch)
6	-Sense	1.0 mm (0.04 inch)
7	Trim	1.0 mm (0.04 inch)
8	+Sense	1.0 mm (0.04 inch)
9	+Vout	2.0 mm (0.08 inch)
10	Sync (on demand)	1.0 mm (0.04 inch)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TRACO Power:

[TEP 160-4815WIR](#) [TEP 160-2415WIR](#) [TEP 160-4816WIR](#) [TEP 160-4818WIR](#) [TEP 160-2413WIR](#) [TEP 160-2412WIR](#) [TEP 160-7218WIR](#) [TEP 160-4812WIR](#) [TEP 160-7212WIR](#) [TEP 160-4813WIR](#) [TEP 160-2418WIR](#) [TEP 160-7213WIR](#) [TEP 160-7215WIR](#) [TEP 160-2416WIR](#) [TEP 160-7216WIR](#)