


All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of Rosenberger Hochfrequenztechnik.

Montagebohrung
panel piercing
 B 12
 M 1:1



Die angegebenen Masse und Toleranzen sind nur Empfehlungen.
The stated dimensions are only recommendations.

Formzahl: 1C_C0_06_02_AS Montagebohrung
 U3_00B-FRM
 Datum: AS
 1.1

ISO-Projektion
 Methode E
 -METRIC-

Rosenberger
 Hochfrequenztechnik
 84526 Tittmoning Pro/ENGINEER

title:
**Montagebohrung
*panel piercing***

					date	name	part-no.:
				drawn	14.02.2001	A_Nobis	MB_12
				check.	30.09.03	<i>Kna. J.</i>	sheet/of: 1/1
				appr.			general tolerance
							ISO 2768
							m-H
c00	02-0124	A_Nobis	14.05.2002	distribu-	FE	AZ	QSM
b00	01-0266	V_Spitzauer	13.06.2001	tion to:	.	.	RMT
rev.	change-no	name	date	remarks:	.	.	.